



**High-impact, precision
full color that lasts**



BradyJet Color Label Printers

High-impact, precision full color that lasts

Printing logos, icons, pictures and complex procedures means you need a lot of two things: one is materials and two is time. That is, if you're using the wrong printer. What you need is an inkjet printer that can balance the complexity of safety and compliance labels with the demands of an industrial environment. Say hello to the BradyJet family of industrial inkjet printers.

Get photo-quality, full-color labels whenever you need them while reducing your inventory of labeling supplies and material waste. BradyJet printers let you create the compliant, long-lasting labels, signs and tags you need to create a safer, more efficient workplace.

- **Create compliant labels and signs** — Trust your regulatory labeling offers the colors needed for ANSI, GHS, ISO, BS5609 and arc flash
- **Extend label performance** — Rely on specially formulated materials and ink designed to stand up to harsh environments
- **Maximize impact, improve efficiency and reduce waste** — Stock and print only what you need, when you need, in photo-quality full-color every time



Going the distance

At Brady, we go the distance to make sure you get what you need. Whether it's field work or lab work, we've got materials for every application.

Barcodes, images, small text — your most important information needs to stay put, in any type of environment. From freezing temperatures to blistering heat, when used with solvents or in outer space, simply put, Brady materials are all about high performance. Our scientists make sure of it. Brady's R&D program focuses on solutions that bring durability, flexibility and efficiency to every workday. We offer hundreds of labels, so be sure to browse through the entire collection. And, as always, let us know if you need more.



BradyJet J2000 Color Label Printer

Smaller labels and volume don’t lessen the impactful color identification you need. The BradyJet J2000 quickly and easily creates any color you need for specific regulations and effective identification — but not at the expense of productivity. This compact mid-volume inkjet solution is capable of producing up to 3,000 labels per day up to 4-in. wide to deliver the full-color labels and signs everywhere you need them.

- **Precise identification quickly** — More efficient printing means you keep your workplace running smoothly and safely
- **Fits your work style and space** — Thanks to its lightweight, compact footprint, the BradyJet J2000 can be moved easily wherever your work demands



Part numbers and specifications

Catalog #	
J2000	BradyJet J2000 Color Label Printer
J2000-BWSSFID	BradyJet J2000 Color Label Printer with Brady Workstation SFID Suite

Specifications			
Ink and Storage Caps		Printer Features	
J20-CMY	J20 Ink Cartridge CMY	Typical throughput	3,000 labels per day
J20-PAD	J20 Ink Pads	Printer technology	Thermal inkjet
J20-ROLL	J20 Material Roll for Print Head Alignment	Color capabilities	Single Cyan, Magenta, Yellow ink cartridge; process black
Software and Connectivity		Print resolution	4800 dpi
Connectivity options	USB	Print width	0.75" (19.00mm) to 4" (101.60mm)
Compatible PC software	Brady Workstation, Windows based driver for 3rd party software use	Media width	1.125" (28.58mm) to 4.25" (108mm)
PC connect or stand alone operation	PC connect	Print length	0.25" (6.35mm) to 24" (609.60mm)
Operating systems:	Windows® 10, Windows® 7, Windows® 8	Ink and Material installation	Material: 2" core roll loading Ink: Ink and Printhead Cartridge
Physical/Operational Characteristics		Print speeds:	2.5" per second
Dimensions	10.4"W x 7.1"H x 15.3"D (264.16mmW x 180.34mmH x 388.62mmD)	Printer includes	(1) BradyJet™ J2000 Printer (J2000);(1) Free Brady WorkStation Basic Design Suite Download;(1) J20 Ink Cartridge (J20-CMY);(1) J20 Material Roll for Printhead Alignment (J20-ROLL);(1) Power Cord;(1) Quick Start Guide;(1) USB Cable;(1) USB with Drivers and Manuals
Weight	7 lb (3.2 kg)	Indicator lights	Power, Ink

B-7425J Chemically Resistant Polypropylene Material

An economical solution for GHS labeling, this polypropylene material is ideal for full-color identification where resistance to harsh chemicals is required.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-260-7425J	2.17 in. (55.00mm)	3.35 in. (85.09mm)	340
J20-261-7425J	2.95 in. (75.00mm)	4.33 in. (109.98mm)	270
J20-262-7425J	4.13 in. (105.00mm)	6.10 in. (154.90mm)	200
J20C-1125-7425J	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-7425J	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-7425J	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-403 Water Dissolvable Paper Material

Ideal for process or flex-inventory identification projects, this 30-second, warm-water-dissolvable label leaves no residue behind.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-17-403	2 in. (50.80mm)	1 in. (25.40mm)	1,500
J20-19-403	3 in. (76.20mm)	2 in. (50.80mm)	350
J20-55-403	4 in. (101.60mm)	2 in. (50.80mm)	250
J20C-1125-403	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-403	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.

B-2595 Vinyl Material

Difficult-to-adhere-to surfaces are no match for this inkjet workhorse. Low-shrink vinyl with ultra-aggressive adhesive stays stuck and lasts up to two years outdoors.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-18-2595	3 in. (76.20mm)	1 in. (25.40mm)	1,000
J20-260-2595	2.17 in. (55.00mm)	3.35 in. (85.00mm)	340
J20-261-2595	2.95 in. (75.00mm)	4.33 in. (110.00mm)	270
J20-262-2595	4.13 in. (105.00mm)	6.10 in. (155.00mm)	200
J20C-1125-2595	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-2595	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-2595	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-2551 Polyester Tags

Your ticket to tag compliance, this material is OSHA 1910.145 compliant for accident prevention tags and OSHA 1910.147 compliant for lockout tagout tags.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-255-2551	3.25 in. (82.55mm)	5.75 in. (146.05mm)	100
J20C-2500-2551	2.50 in. (63.50mm)	50 ft. (15.24m)	Cont.
J20C-3250-2551	3.25 in. (82.55mm)	50 ft. (15.24m)	Cont.

B-2585 BS5609 Marine Material

BS5609 Sections 2 and 3 certified, this option is ideal for applications where chemical identification is needed.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-260-2585	2.17 in. (55.00mm)	3.35 in. (85.00mm)	340
J20-261-2585	2.95 in. (75.00mm)	4.33 in. (110.00mm)	270
J20-262-2585	4.13 in. (105.00mm)	6.10 in. (155.00mm)	200
J20C-2250-2585	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-2585	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-2569 Polyester Material

For general-purpose identification, this material fits the bill. It works best on smooth surfaces, making it ideal for use on rigid panels, and lasts up to two years outdoors.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-260-2569	2.17 in. (55.00mm)	3.35 in. (85.00mm)	340
J20-261-2569	2.95 in. (75.00mm)	4.33 in. (110.00mm)	270
J20-262-2569	4.13 in. (105.00mm)	6.10 in. (155.00mm)	200
J20C-1125-2569	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-2569	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-2569	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-2475 UL Listed Polyester Material

An ideal solution for products that require UL safety verification, these extra-durable labels are resistant to abrasions, chemicals, oils and solvents

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-136-2475	1.50 in. (38.10mm)	0.75 in. (19.05mm)	1000
J20-137-2475	2 in. (50.80mm)	1 in. (25.40mm)	750
J20-18-2475	3 in. (76.20mm)	1 in. (25.40mm)	750
J20-19-2475	3 in. (76.20mm)	2 in. (50.80mm)	250
J20-235-2475	1.50 in. (38.10mm)	1 in. (25.40mm)	750
J20-25-2475	4 in. (101.60mm)	6 in. (152.40mm)	80
J20-55-2475	4 in. (101.60mm)	2 in. (50.80mm)	250
J20-59-2475	1 in. (25.40mm)	0.50 in. (12.70mm)	2250
J20C-1125-2475	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-2475	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-2475	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-2581 Repositionable Vinyl Material

Stays stuck when you need it, easily removes when you don’t. Stick, unstick and reposition with ease with this material ideal for Lean / 5S and inventory labeling.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20C-1125-2581	1.125 in. (28.58mm)	100 ft. (30.48m)	Cont.
J20C-2250-2581	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J20C-4000-2581	4 in. (101.60mm)	100 ft. (30.48m)	Cont.

B-2509 Magnetic Material

Need a more permanent option with the ability to reuse? Look no further than this magnetic option that’s great for work-in-progress or flex-inventory labeling.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20C-2500-2509	2.50 in. (63.50mm)	25 ft. (7.62m)	Cont.

B-2550 General Purpose Paper Material

This light-duty paper label is low-cost and high-contrast with excellent smear resistance.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J20-25-2550	4 in. (101.60mm)	6 in. (152.40mm)	180
J20-53-2550	2 in. (50.80mm)	0.5 in. (12.70mm)	1,900
J20-55-2550	4 in. (101.60mm)	2 in. (50.80mm)	550
J20-77-2550	4 in. (101.60mm)	4 in. (101.60mm)	280
J20C-2000-2550	2 in. (50.80mm)	100 ft. (30.48m)	Cont.
J20C-3000-2550	3 in. (76.20mm)	100 ft. (30.48m)	Cont.
J20C-4000-2550	4 in. (101.60mm)	100 ft. (30.48m)	Cont.



BradyJet J2000

BRADY

BIG PRODUCTION DOWN TO THE SMALLEST DETAIL

BradyJet J4000 Color Label Printer

Complex, highly specific labels in high volumes could mean lower quality print resolution and ineffective identification with other printers. But not with the BradyJet J4000. Maximize productivity and impact with this industry workhorse built to handle the demands of your demanding label and signage needs. Create up to 5,000 impactful full-color labels per day up to 8-in. wide.

- **More time for critical tasks** — When the printer does the busy work, you have more time to focus on the important work needed to keep your operations running smoothly
- **Prints well with others** — Create however it works best for you, then easily print PDFs or from third-party software packages with the optimized Windows driver



Part numbers and specifications

Catalog #	
J4000	BradyJet J4000 Color Label Printer
J4000-AM-BWSSFID	BradyJet J4000 Color Label Printer with Brady Workstation SFID Suite
J4000-AM-BWSPWID	BradyJet J4000 Color Label Printer with Brady Workstation PWID Suite

Specifications			
Ink and Storage Caps		Printer Features	
J40-CMY	J4000 CMY Ink Tank Cartridge	Typical throughput	5,000 labels per day
J40-CAP	J4000 Ink Cartridge Storage Caps	Printer technology	Thermal inkjet
Software and Connectivity		Color capabilities	Single high capacity Cyan, Magenta, Yellow ink cartridge; process black
Connectivity options	Standard: USB 2.0, Ethernet 10/100	Print resolution	4800 dpi
Compatible PC software	Brady Workstation, Windows Driver with 3rd party software	Print width	0.5" (12.70mm) to 8" (203.20mm)
PC connect or stand alone operation	PC connect	Media width	1.5" (38.1mm) to 8.25" (209.55mm)
Operating systems:	Windows® 10, Windows® 7, Windows® 8	Print length	1.5" (38mm) to 24" (609.60mm)
Physical/Operational Characteristics		Ink and Material installation	Material: 3" core roll loading Ink: Ink and Printhead Cartridge
Dimensions	17.25"W x 9.1"H x 17.25"D (438.15mmW x 231.14H x 438.15mmD)	Print speeds:	Draft Mode: 4.5" per second Normal Mode: 1.8" per second High Quality Mode: 0.8" per second
Weight	36 lbs (16 kg)	Printer includes	(1) BradyJet J4000 Printer;(1) Power Cord;(1) CMY Ink Cartridge with built in Printhead;(1) Pack of 2 Ink Cartridge storage caps;(1) Media starter roll 4" wide B-2595 Vinyl;(1) USB cord;(1) USB Flash Drive with product information;(1) Free Brady Workstation Version
		Indicator lights	Power, Pause, Ink

B-7425J Chemically Resistant Polypropylene Material

An economical solution for GHS labeling, this polypropylene material is ideal for full-color identification where resistance to harsh chemicals is required.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J40-262-7425J	4.13 in. (104.90mm)	6.10 in. (154.94mm)	200
J40-265-7425J	7 in. (177.80mm)	10 in. (254.00mm)	100
J40-260-7425J	2.17 in. (55.12mm)	3.35 in. (85.09mm)	340
J40C-2250-7425J	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J40C-4000-7425J	4 in. (101.60mm)	100 ft. (30.48m)	Cont.
J40C-6000-7425J	6 in. (152.40mm)	100 ft. (30.48m)	Cont.
J40C-8000-7425J	8 in. (203.20mm)	100 ft. (30.48m)	Cont.
J40-321-7425J	8 in. (203.20mm)	5.25 in. (133.35mm)	100
J40-268-7425J	8 in. (203.20mm)	11 in. (279.40mm)	100

B-2585 BS5609 Marine Material

BS5609 Sections 2 and 3 certified, this option is ideal for applications where chemical identification is needed.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J50-260-2585	2.17 in. (55.00mm)	3.35 in. (85.00mm)	340
J50-261-2585	2.95 in. (75.00mm)	4.33 in. (110.00mm)	270
J50-262-2585	4.13 in. (105.00mm)	6.10 in. (155.00mm)	200
J50-267-2585	6.10 in. (154.90mm)	8.3 in. (210.00mm)	120
J50-268-2585	8 in. (203.00mm)	11 in. (280.00mm)	100
J50C-2250-2585	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J50C-4000-2585	4 in. (101.60mm)	100 ft. (30.48m)	Cont.
J50C-6000-2585	6 in. (152.40mm)	100 ft. (30.48m)	Cont.
J50C-8000-2585	8 in. (203.20mm)	100 ft. (30.48m)	Cont.

B-2595 Vinyl Material

Difficult-to-adhere-to surfaces are no match for this inkjet workhorse. Low-shrink vinyl with ultra-aggressive adhesive stays stuck and lasts up to two years outdoors.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J50-260-2595	2.17 in. (55.12mm)	3.35 in. (85.09mm)	340
J50-261-2595	2.95 in. (74.93mm)	4.33 in. (109.98mm)	270
J50-262-2595	4.13 in. (104.90mm)	6.10 in. (154.94mm)	200
J50-265-2595	7 in. (177.80mm)	10 in. (254.00mm)	100
J50-267-2595	6.10 in. (154.94mm)	8.3 in. (210.00mm)	120
J50C-2250-2595	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J50C-4000-2595	4 in. (101.00mm)	100 ft. (30.48m)	Cont.
J50C-6000-2595	6 in. (152.00mm)	100 ft. (30.48m)	Cont.
J50C-8000-2595	8 in. (203.20mm)	100 ft. (30.48m)	Cont.

B-2569 Polyester Material

For general-purpose identification, this material fits the bill. It works best on smooth surfaces, making it ideal for use on rigid panels, and lasts up to two years outdoors.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J50-260-2569	2.17 in. (55.12mm)	3.35 in. (85.09mm)	340
J50-261-2569	2.95 in. (74.93mm)	4.33 in. (109.98mm)	270
J50-262-2569	4.13 in. (104.90mm)	6.10 in. (154.94mm)	200
J50-265-2569	7 in. (177.80mm)	10 in. (254.00mm)	100
J50-267-2569	6.10 in. (154.94mm)	8.30 in (210.00mm)	120
J50C-2250-2569	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J50C-4000-2569	4 in. (101.60mm)	100 ft. (30.48m)	Cont.
J50C-6000-2569	6 in. (152.40mm)	100 ft. (30.48m)	Cont.
J50C-8000-2569	8 in. (203.20mm)	100 ft. (30.48m)	Cont.

B-2581 Repositionable Vinyl Material


Stays stuck when you need it, easily removes when you don't. Stick, unstick and reposition with ease with this material ideal for Lean / 5S and inventory labeling.

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J50C-2250-2581	2.25 in. (57.15mm)	100 ft. (30.48m)	Cont.
J50C-4000-2581	4 in. (101.60mm)	100 ft. (30.48m)	Cont.
J50C-6000-2581	6 in. (152.40mm)	100 ft. (30.48m)	Cont.
J50C-8000-2581	8 in. (203.20mm)	100 ft. (30.48m)	Cont.

B-2475 UL Listed Polyester Material

An ideal solution for products that require UL safety verification, these extra-durable labels are resistant to abrasions, chemicals, oils and solvents

Catalog #	Width in. (mm)	Height in. (mm)	Labels per roll
J40-136-2475	1.50 in. (38.10mm)	0.75 in. (19.05mm)	1000
J40-137-2475	2 in. (50.80mm)	1 in. (25.40mm)	750
J40-18-2475	3 in. (76.20mm)	1 in. (25.40mm)	750
J40-19-2475	3 in. (76.20mm)	2 in. (50.80mm)	250
J40-235-2475	1.50 in. (38.10mm)	1 in. (25.40mm)	750
J40-25-2475	4 in. (101.60mm)	6 in. (152.40mm)	80
J40-321-2475	8 in. (203.20mm)	5.25 in. (133.35mm)	100
J40-268-2475	8 in. (203.20mm)	11 in. (279.40mm)	100
J40-55-2475	4 in. (101.60mm)	2 in. (50.80mm)	250
J40-59-2475	1 in. (25.40mm)	0.5 in. (12.70mm)	2250
J40C-1125-2475	1.125 in. (28.58mm)	100 ft. (30.48 m)	Cont.
J40C-2250-2475	2.25 in. (57.15mm)	100 ft. (30.48 m)	Cont.
J40C-4000-2475	4 in. (101.60mm)	100 ft. (30.48 m)	Cont.
J40C-8000-2475	8 in. (203.20mm)	100 ft. (30.48 m)	Cont.



Design, print and manage your labeling with software

Brady Workstation Desktop Software

Design and print labels seamlessly with Brady Workstation software suites and apps specially designed for a variety of common industry-related tasks. Along with popular time-saving features like auto-formatting and built-in templates, Brady Workstation features an intuitive interface that integrates seamlessly with the work you do.



Other apps and suites are available:




1. Go to **BradyID.com/Workstation**.




2. Select the apps and suites you want

For more information and to get started, go to BradyID.com/Workstation.



Safety and Facility Identification Suite

Make colorful visuals to keep your facility safe and compliant. This group of apps helps you create signs, labels, pipe markers and lean visuals. Use predefined templates or customize to suit your needs.



GHS Chemical Identification App

Get a streamlined label creation process so you can easily enter the data just once from your SDS sheets, then create and print GHS labels on demand. You can also auto-populate your GHS label using the built-in chemical database.

We identify and protect people, products and places.

For more information or to learn more about our innovative products, visit BradyID.com or call 1-888-272-3946.



Y5064180 MS5064180

USA
Customer Service: 1-888-272-3946
BradyID.com

Canada
Customer Service: 1-800-263-6179
BradyCanada.ca

Mexico
Customer Service: 1-800-262-7777
Inside Sales: 1-800-262-7777 ext 177
BradyID.com.mx

