



# HYT 939 (Pressure Tight to 16Bar)


## Digital Humidity and Temperature Module

### Optimal for highly sophisticated, industrial applications

#### Benefits & Characteristics

- Calibrated and temperature compensated
- High chemical resistance
- Wide humidity and temperature range
- Very stable at high humidity
- Mechanically robust
- Excellent humidity/temperature accuracy and stability
- I<sup>2</sup>C protocol (address 0x28 or alternative address)
- Very low drift
- Interchangeable without adjustments
- Pressure-resistant version up to 16 bar upon request

#### Illustration<sup>1)</sup>



1) For actual size, see mechanical dimensions


#### Technical Data

Operating temperature range:	-40 °C to +125 °C
Operating humidity range:	0 % RH to 100 % RH
Hysteresis:	< ±1 % RH
Linearity error:	< ±1 % RH
Temperature error:	0.05 % RH/K (0 °C to +60 °C)
Operating voltage:	2.7 V to 5.5 V
Current consumption (nominal):	< 22 µA at 1 Hz measuring rate; 850 µA max.
Current consumption (sleep):	< 1 µA
Digital interface:	I <sup>2</sup> C, address 0x28 or alternative address
Operating voltage (limits):	-0.3 V to 6 V
Storage conditions:	-20 °C to +50 °C


	Humidity	Temperature
Accuracy:	±1.8 % RH at +23 °C (0 % RH to 90 % RH)	±0.2 K (0 °C to +60 °C)
Reproducibility:	±0.2 % RH	±0.1 K
Resolution:	0.02 % RH	0.015 °C
Response time $t_{63}$ :	< 10 s with metal mesh filter	< 10 s with metal mesh filter
Long-term drift:	< 0.5 % RH/a (at +23 °C and 30 % RH to 70 % RH - laboratory conditions)	< 0.05 K/a
Measuring principle:	Capacitive polymer humidity sensor	PTAT (integrated)




## Product Photo



## Mechanical Dimensions - HYT 939p



## Pin Assignment



1	2	3	4
SCL	VCC	GND	SDA



## Order Information

Description:	Item number:	Former main reference:
HYT 939 (Pressure Tight to 16Bar)	103941	150.00096

## Additional Electronics

Description:	Item number:	Former main reference:
HYT LabKit	103925	150.00073

## Additional Documents

Application Note:	Document name:
	AHHYTM_E

