

# Safety Data Sheet

According to U.S.A. Federal Hazcom 2012 and Canadian HPR - WHMIS 2015

## 1. Identification

### 1.1. Product identifier

Code **HI7010**  
Product name **pH 10.01 Buffer Solution**

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use **Calibration of pH Electrodes.**

### 1.3. Details of the supplier of the safety data sheet

Name **Hanna Instruments S.R.L.**  
Full address **str. Hanna Nr 1**  
District and Country **457260 loc. Nusfalau (Salaj) Romania**  
Tel. **+40 260607700**  
Fax **+40 260607700**

e-mail address of the competent person responsible for the Safety Data Sheet **sds@hannainst.com**

Product distribution by: **Hanna Instruments, Inc - 584 Park East Drive, Woonsocket, Rhode Island, USA 02895 - Technical Service Contact Information: +1 8004266287**

### 1.4. Emergency telephone number

For urgent inquiries refer to **USA Emergency Contact Information: +1 8004249300 - CHEMTREC 24 hours/365 days - International Emergency Contact Information: +1 7035273887 - CHEMTREC 24 hours/365 days**

## 2. Hazards identification

### 2.1. Classification of the substance or mixture

The product is not classified as hazardous pursuant to the provisions set forth in OSHA Hazard Communication Standard (HCS) (29 CFR 1910.1200).

Hazard pictograms: --  
Signal words: --

Hazard statements: --

Precautionary statements:  
Prevention: --

Response: --

Storage: --

Disposal: --

### 2.2. Other hazards

Information not available

## 3. Composition/information on ingredients

### 3.2. Mixtures

The product does not contain substances classified as being hazardous to human health or the environment pursuant to the provisions set forth in OSHA Hazard Communication Standard (HCS) (29 CFR 1910.1200).

## 4. First-aid measures

### 4.1. Description of first aid measures

Not specifically necessary. Observance of good industrial hygiene is recommended.

### 4.2. Most important symptoms and effects, both acute and delayed

Specific information on symptoms and effects caused by the product are unknown.

### 4.3. Indication of any immediate medical attention and special treatment needed

Information not available

## 5. Fire-fighting measures

### 5.1. Extinguishing media

#### SUITABLE EXTINGUISHING EQUIPMENT

The extinguishing equipment should be of the conventional kind: carbon dioxide, foam, powder and water spray.

#### UNSUITABLE EXTINGUISHING EQUIPMENT

None in particular.

### 5.2. Special hazards arising from the substance or mixture

#### HAZARDS CAUSED BY EXPOSURE IN THE EVENT OF FIRE

Do not breathe combustion products.

### 5.3. Advice for firefighters

#### GENERAL INFORMATION

Use jets of water to cool the containers to prevent product decomposition and the development of substances potentially hazardous for health. Always wear full fire prevention gear. Collect extinguishing water to prevent it from draining into the sewer system. Dispose of contaminated water used for extinction and the remains of the fire according to applicable regulations.

#### SPECIAL PROTECTIVE EQUIPMENT FOR FIRE-FIGHTERS

Normal fire fighting clothing i.e. fire kit (BS EN 469), gloves (BS EN 659) and boots (HO specification A29 and A30) in combination with self-contained open circuit positive pressure compressed air breathing apparatus (BS EN 137).

## 6. Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Use breathing equipment if fumes or powders are released into the air. These indications apply for both processing staff and those involved in emergency procedures.

### 6.2. Environmental precautions

The product must not penetrate into the sewer system or come into contact with surface water or ground water.

### 6.3. Methods and material for containment and cleaning up

Confine using earth or inert material. Collect as much material as possible and eliminate the rest using jets of water. Contaminated material should be disposed of in compliance with the provisions set forth in point 13.

### 6.4. Reference to other sections

Any information on personal protection and disposal is given in sections 8 and 13.

## 7. Handling and storage

### 7.1. Precautions for safe handling

Before handling the product, consult all the other sections of this material safety data sheet. Avoid leakage of the product into the environment. Do not eat, drink or smoke during use.

### 7.2. Conditions for safe storage, including any incompatibilities

Keep the product in clearly labelled containers. Keep containers away from any incompatible materials, see section 10 for details.

## 7. Handling and storage ... / >>

### 7.3. Specific end use(s)

Information not available

## 8. Exposure controls/personal protection

### 8.1. Control parameters

Information not available

### 8.2. Exposure controls

Comply with the safety measures usually applied when handling chemical substances.

#### HAND PROTECTION

None required.

#### SKIN PROTECTION

None required.

#### EYE PROTECTION

None required.

#### RESPIRATORY PROTECTION

None required, unless indicated otherwise in the chemical risk assessment.

#### ENVIRONMENTAL EXPOSURE CONTROLS

The emissions generated by manufacturing processes, including those generated by ventilation equipment, should be checked to ensure compliance with environmental standards.

## 9. Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	liquid
Colour	colourless
Odour	odourless
Odour threshold	Not available
pH	10
Melting point / freezing point	Not available
Initial boiling point	Not available
Boiling range	Not available
Flash point	Not applicable
Evaporation rate	Not available
Flammability (solid, gas)	Not available
Lower inflammability limit	Not available
Upper inflammability limit	Not available
Lower explosive limit	Not available
Upper explosive limit	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	1.00
Solubility	soluble in water
Partition coefficient: n-octanol/water	Not available
Auto-ignition temperature	Not available
Decomposition temperature	Not available
Viscosity	Not available
Explosive properties	not applicable
Oxidising properties	not applicable

### 9.2. Other information

Total solids (250°C / 482°F)	0,47 %
------------------------------	--------

## 10. Stability and reactivity

### 10.1. Reactivity

There are no particular risks of reaction with other substances in normal conditions of use.

### 10.2. Chemical stability

The product is stable in normal conditions of use and storage.

## 10. Stability and reactivity ... / >>

### 10.3. Possibility of hazardous reactions

No hazardous reactions are foreseeable in normal conditions of use and storage.

### 10.4. Conditions to avoid

None in particular. However the usual precautions used for chemical products should be respected.

### 10.5. Incompatible materials

Information not available

### 10.6. Hazardous decomposition products

Information not available

## 11. Toxicological information

According to currently available data, this product has not yet produced health damages. Anyway, it must be handled according to good industrial practices.

### 11.1. Information on toxicological effects

#### Metabolism, toxicokinetics, mechanism of action and other information

Information not available

#### Information on likely routes of exposure

Information not available

#### Delayed and immediate effects as well as chronic effects from short and long-term exposure

Information not available

#### Interactive effects

Information not available

#### ACUTE TOXICITY

Does not meet the classification criteria for this hazard class

#### SKIN CORROSION / IRRITATION

Does not meet the classification criteria for this hazard class

#### SERIOUS EYE DAMAGE / IRRITATION

Does not meet the classification criteria for this hazard class

#### RESPIRATORY OR SKIN SENSITISATION

Does not meet the classification criteria for this hazard class

#### GERM CELL MUTAGENICITY

Does not meet the classification criteria for this hazard class

#### CARCINOGENICITY

Does not meet the classification criteria for this hazard class

This product is not considered to be a carcinogen by IARC, ACGIH, NTP, and OSHA.

#### REPRODUCTIVE TOXICITY

Does not meet the classification criteria for this hazard class

#### STOT - SINGLE EXPOSURE

## 11. Toxicological information ... / >>

Does not meet the classification criteria for this hazard class

STOT - REPEATED EXPOSURE

Does not meet the classification criteria for this hazard class

ASPIRATION HAZARD

Does not meet the classification criteria for this hazard class

## 12. Ecological information

Use this product according to good working practices. Avoid littering. Inform the competent authorities, should the product reach waterways or contaminate soil or vegetation.

### 12.1. Toxicity

Information not available

### 12.2. Persistence and degradability

Information not available

### 12.3. Bioaccumulative potential

Information not available

### 12.4. Mobility in soil

Information not available

### 12.5. Results of PBT and vPvB assessment

On the basis of available data, the product does not contain any PBT or vPvB in percentage greater than 0,1%.

### 12.6. Other adverse effects

Information not available

## 13. Disposal considerations

### 13.1. Waste treatment methods

Reuse, when possible. Neat product residues should be considered special non-hazardous waste.

Disposal must be performed through an authorised waste management firm, in compliance with national and local regulations.

CONTAMINATED PACKAGING

Contaminated packaging must be recovered or disposed of in compliance with national waste management regulations.

## 14. Transport information

The product is not dangerous under current provisions of the Code of International Carriage of Dangerous Goods by Road (ADR) and by Rail (RID), of the International Maritime Dangerous Goods Code (IMDG), and of the International Air Transport Association (IATA) regulations.

### 14.1. UN number

Not applicable

### 14.2. UN proper shipping name

Not applicable

### 14.3. Transport hazard class(es)

Not applicable

## 14. Transport information ... / >>

### 14.4. Packing group

Not applicable

### 14.5. Environmental hazards

Not applicable

### 14.6. Special precautions for user

Not applicable

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Information not relevant

## 15. Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### U.S. Federal Regulations

##### TSCA:

All components are listed on TSCA Inventory.

##### Clean Air Act Section 112(b):

No component(s) listed.

##### Clean Air Act Section 602 Class I Substances:

No component(s) listed.

##### Clean Air Act Section 602 Class II Substances:

No component(s) listed.

##### Clean Water Act – Priority Pollutants:

No component(s) listed.

##### Clean Water Act – Toxic Pollutants:

No component(s) listed.

##### DEA List I Chemicals (Precursor Chemicals):

No component(s) listed.

##### DEA List II Chemicals (Essential Chemicals):

No component(s) listed.

##### EPA List of Lists:

##### 313 Category Code:

No component(s) listed.

##### EPCRA 302 EHS TPQ:

No component(s) listed.

##### EPCRA 304 EHS RQ:

No component(s) listed.

##### CERCLA RQ:

No component(s) listed.

##### EPCRA 313 TRI:

No component(s) listed.

##### RCRA Code:

No component(s) listed.

##### CAA 112 (r) RMP TQ:

No component(s) listed.

## 15. Regulatory information ... / >>

### State Regulations

#### Massachussets:

No component(s) listed.

#### Minnesota:

No component(s) listed.

#### New Jersey:

No component(s) listed.

#### New York:

No component(s) listed.

#### Pennsylvania:

No component(s) listed.

#### California:

No component(s) listed.

#### Proposition 65:

This product does not contain any substances know to the State of California to cause cancer, reproductive harm or birth defects.

### International Regulations

#### Substances subject to exportation reporting pursuant to (EC) Reg. 649/2012:

None

#### Substances subject to the Rotterdam Convention:

None

#### Substances subject to the Stockholm Convention:

None

#### Candadian WHMIS

Information not available

## 16. Other information

### LEGEND:

- 313 CATEGORY CODE: Emergency Planning and Community Right-to Know Act Section 313 Category Code
- ADR: European Agreement concerning the carriage of Dangerous goods by Road
- CAA 112 @ RMP TQ: Risk Management Plan Threshold Quantity (Clean Air Act Section 112@)
- CAS NUMBER: Chemical Abstract Service Number
- CE50: Effective concentration (required to induce a 50% effect)
- CERCLA RQ: Reportable Quantity (Comprehensive Environment Response, Compensation, and Liability Act)
- CLP: EC Regulation 1272/2008
- DEA: Drug Enforcement Administration
- EmS: Emergency Schedule
- EPA: US Environmental Protection Agency
- EPCRA: Emergency Planning and Community Right-to Know Act
- EPCRA 302 EHS TPQ: Extremely Hazardous Substance Threshold Planning Quantity (Section 302 Category Code)
- EPCRA 304 EHS RQ: Extremely Hazardous Substance Reportable Quantity (Section 304 Category Code)
- EPCRA 313 TRI: Toxics Release Inventory (Section 313 Category Code)
- GHS: Globally Harmonized System of classification and labeling of chemicals
- IATA DGR: International Air Transport Association Dangerous Goods Regulation
- IC50: Immobilization Concentration 50%
- IMDG: International Maritime Code for dangerous goods
- IMO: International Maritime Organization
- LC50: Lethal Concentration 50%
- LD50: Lethal dose 50%
- OEL: Occupational Exposure Level
- PEL: Predicted exposure level
- RCRA Code: Resource Conservation and Recovery Act Code
- REL: Recommended exposure limit
- RID: Regulation concerning the international transport of dangerous goods by train
- TLV: Threshold Limit Value
- TLV CEILING: Concentration that should not be exceeded during any time of occupational exposure.
- TSCA: Toxic Substances Control Act
- TWA STEL: Short-term exposure limit
- TWA: Time-weighted average exposure limit

## 16. Other information ... / >>

- VOC: Volatile organic Compounds- WHMIS: Workplace Hazardous Materials Information System.

### GENERAL BIBLIOGRAPHY:

- GHS rev. 3
- The Merck Index. 10th Edition
- Handling Chemical Safety
- Niosh - Registry of Toxic Effects of Chemical Substances
- INRS - Fiche Toxicologique (toxicological sheet)
- Patty - Industrial Hygiene and Toxicology
- N.I. Sax - Dangerous properties of Industrial Materials-7, 1989 Edition
- ECHA website
- Database of SDS models for chemicals - Ministry of Health and ISS (Istituto Superiore di Sanità) - Italy
  
- 6 NYCRR part 597
- Cal/OSHA website
- California Safe Drinking Water and Toxic Enforcement Act
- EPA website
- Hazard Communication Standard (HCS 2012)
- IARC website
- List Of Lists EPA: Consolidated List of Chemicals Subject to EPCRA, CERCLA and Section 112© of the Clean Air Act
- Massachusetts 105 CMR Department of public health 670.000: "Right to Know"
- Minensota Chapter 5206 Departemnt Of Labor and Industry Hazardous Substances, Employee "Right to Know".
- New Jersey Worker and Community Right to know Act N.J.S.A.
- NTP. 2011. Report on Carcinogens, 12th Edition.
- OSHA website
- Pennsylvania, Hazardous Substance List, Chapter 323

### Note for users:

The information contained in the present sheet are based on our own knowledge on the date of the last version. Users must verify the suitability and thoroughness of provided information according to each specific use of the product.

This document must not be regarded as a guarantee on any specific product property.

The use of this product is not subject to our direct control; therefore, users must, under their own responsibility, comply with the current health and safety laws and regulations. The producer is relieved from any liability arising from improper uses.

Provide appointed staff with adequate training on how to use chemical products.

### Changes to previous review:

The following sections were modified:

01 / 02 / 03 / 04 / 06 / 08 / 09 / 10 / 11 / 16.