



# Ledinaire floodlights gen3

## BVP165 LED120/840 PSU 100W SWB CE

- - 840 neutral white - - - Symmetrical

This Ledinaire floodlights range contains a selection of popular off-the-shelf LED luminaires that comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

### Product data

General Information	
Lamp family code	-
Light source colour	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	No [ -]
Driver included	Yes
Optical cover/lens type	G [ Glass]
Luminaire light beam spread	110° x 110°
Control interface	-
Connection	Flying leads/cables
Cable	Cable 2.0 m without plug (C2K)
Protection class IEC	Safety class I
Flammability mark	NO [ -]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Optic type outdoor	Symmetrical
Constant light output	No
Number of products on MCB (16 A type B)	22
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Light source engine type	LED
Light Technical	
Upward light output ratio	0
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input Voltage	220 to 240 V
Input frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	100 W
End CLO power consumption	- W
Inrush current	3.84 A

## Ledinaire floodlights gen3

Inrush time	0.0244 ms
Power factor (min.)	0.95

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Housing material	Aluminium die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover/lens material	Tempered glass
Fixation material	Steel
Mounting device	MBA [ Mounting bracket adjustable]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	220 mm
Overall width	312 mm
Overall height	32.5 mm
Effective projected area	0.045 m²
Colour	grey
Dimensions (height x width x depth)	33 x 312 x 220 mm (1.3 x 12.3 x 8.7 in)

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]
Surge protection (common/differential)	4/4 kV

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	12000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	120 lm/W

Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.380, 0.380) SDCM <5
Initial input power	100 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	80

### Application Conditions


Ambient temperature range	-25 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

### Product Data

Full product code	871951453351699
Order product name	BVP165 LED120/840 PSU 100W SWB CE
EAN/UPC – product	8719514533516
Order code	53351699
SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	911401856483
SAP net weight (piece)	1.760 kg



## Dimensional drawing



BVP165 LED120/840 PSU 100W SWB CE

## Ledinaire floodlights gen3

