



- Fully Rated to 13A
- Double Pole Switching
- Safety Shutter System
- Stainless Steel Finish
- Black Interior

Product Specification Data

Revision Date: 15/10/2021

Product Standard/s	BS 1363-2
Terminal Capacity L&N	3 x 1.5, 3 x 2.5, 2 x 4.0 mm ²
Terminal Capacity E	3 x 1.5, 3 x 2.5, 2 x 4.0 mm ²
Frequency	50 Hz
CE Conformity	Yes
WEEE Symbol	Yes
G Mark	Yes
UKCA Conformity	Yes
Model	British Standard
Protective contact	No
Protective earth pin round	No
Number of active Pins (round)	0
Number of active Pins (flat)	3
With signal lamp	No
With built-in USB power supply	No
Number of units	1
Number of modules (module system)	0
Number of socket outlets switchable	2
Number of phases	2
Imprint/indication	Other
Connection type	Screwed terminal
With hinged lid	No
With child-protection	Yes
Label space/information surface	Yes
Colour	Stainless Steel
Lockable	No
Insulated mounting	No
With function lighting	No
Fault current protection	No

Product Specification Data (cont)		Revision Date: 15/10/2021
Special power supply	No special power supply	
Mounting method	Surface mounted (plaster)	
Type of fastening	Mounting With screw	
Material	Metal	
Material quality	Stainless steel	
Halogen free	Yes	
Surface protection	Brushed	
Surface finishing	Matt	
Antibacterial treatment	No	
With on/off switch	Yes	
Nominal current	13 A	
Nominal voltage	250 V	
Suitable for degree of protection (IP)	IP2X	
Impact strength	IK02	
Width of device	145 mm	
Height of device	85 mm	
Depth of device	31 mm	
Min. depth of built-in installation box	25 mm	

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.



Electrium Sales Limited, Walkmill Lane, Cannock WS11 0XE
01543 455000 www.electrium.co.uk info@electrium.co.uk