

Flammable Gas Leak Detector



Features

- Detects traces of gas
- Detects static electricity
- Audible & visual warnings
- Easy to use
- Clip & wrist cord for easy handling

Specifications

Operating Voltage	: 3V DC (2x micro batteries, alkaline)
Function	: Detecting the gas leakage and absorbing static electricity
Power Consumption	: Approx. 200mA
Detectable Gas	: Propane and Natural gas (LPG, LNG)
Sensitivity	: Propane: Min. 500ppm, Max. 6500ppm Natural gas: Min> 1000ppm, Max. 6500ppm
Operating Life	: Depending on type of battery use approx. 4 hours
Working Temperature	: +10°C to +50°C
Relative Humidity	: <95%(not condensing)
Storage Temperature	: +5°C to +55°C
Power	: 2x AAA batteries (supplied)
Dimensions (W×H×D)	: 18mm×175mm×24mm
Weight	: 25g

Part Number Table

Description	Part Number
Flammable Gas Leak Detector	TEN01068

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

