



PS3V

Switching Power Supplies



# Compact & Reliable Power Supplies

Flexible installation allows mounting in four directions



**IDEC CORPORATION** 

## Suitable for downsizing of equipm **Compact & efficient switching power supplies**



products,

we provide total solutions and related PLCs & HMI products



Operates in temperatures ranging from -25 to +70°C. Ideal for use in various storage facilities such as freezers and refridgerators.

Complies with safety standards for various facilities other than factories.



- Mold injection machines
- · Food and packaging machines
- Multilevel parking garage
- Car facilities
- Logistics and transport facilities
- Agricultural facilities
- Energy-related facilities, others

Vibration-resistant and maintenance-free (no retightening of screws). Push-in improves efficiency in limited spaces.




IDEC's reliable technology enable stable power supply and its compact size allows installation in small equipment.

## **PS3V** Switching Power Supplies

3V				Р	ackage quantity:
	Horizontal terminal type	Push-in terminal type (*1)	lanut veltere	Output valte se	Outrout ourroad
Output capacity	Part no.	Part no.	Input voltage	Output voltage	Output curren
	PS3V-015AF05C	_		5V	3.0A
15W	PS3V-015AF12C	_		12V	1.3A
	PS3V-015AF24C	_		24V	0.63A
	PS3V-030AF05C	PS3V-030AF05P	]	5V	6.0A
30W	PS3V-030AF12C	PS3V-030AF12P		12V	2.5A
	PS3V-030AF24C	PS3V-030AF24P	100 to 240V AC 24V	1.3A	
5014	PS3V-050AF12C	PS3V-050AF12P	]	12V	4.5A
50W	PS3V-050AF24C	PS3V-050AF24P	1	24V	2.3A
100W	PS3V-100AF24C	PS3V-100AF24P		24V	4.5A
150W	PS3V-150AF24C	PS3V-150AF24P	1	24V	6.5A

\*1) Push-in models available in June 2021

#### Part no. configuration



#### **Accessories**

Name	Applicable model	Part no. (Ordering no.)	Package quantity	Remarks		
	PS3V-015AF	PS9Z-3N3A				
L-shaped mounting bracket (*2)	PS3V-030AF		1	L-shaped mounting brackets for PS3X switching power		
	PS3V-050AF	PS9Z-3E3B		supplies can be used.		
	PS3V-100AF					
	PS3V-015AF	PS9Z-3N4B				
DIN rail mounting bracket	PS3V-030AF	PS9Z-3E4C		DIN roll mounting brockets for DCOV power supplies can be		
	PS3V-050AF	F39Z-3E40		DIN rail mounting brackets for PS3X power supplies can be used.		
	PS3V-100AF	PS9Z-3E4D		useu.		
	PS3V-150AF	F 392-3E4D				

\*2) PS3X L-shaped mounting brackets (PS9Z-3N3B) cannot be used.

L-shaped mounting bracket is not available for PS3V-150AF. PS9Z-3N3B L-shaped mounting brackets cannot be used for PS3V-150AF.

#### **DIN rail/End clip/Tools**

DIN rail/End clip/Tools Specify the Ordering no. when ordering.						
Name	Part No.	Ordering No.	Package quantity	Remarks		
35mm DIN rail	BAA1000	BAA1000PN10	10	Material: Aluminum Weight: 200g Length: 1,000mm		
End alia	BNL5	BNL5PN10		Weight: 15g Material: Steel Plating: Trivalent zinc chromate M4 screw used		
End clip	BNL6	BNL6PN10		Weight: 15.2g Material: Steel Plating: Trivalent zinc chromate M4 screw used		
Crimping tool (for ferrules)	S3TL-CR06D	S3TL-CR06D		Applicable ferrule: With/without insulated cover Crimping shape		
Auto-adjust stripping tool	S3TL-ST06	S3TL-ST06	1	PVC-insulated thin stranded and solid wires 0.08 to 6mm² (28AWG to 10AWG)		
Insulated driver	S3TL-D04-25-75	S3TL-D04-25-75	1	Blade size (dimensions: mm) $1.4 \times 1.5 \times 75$		

#### **Specifications**

	mou	luons			500115	1=010				
ltem			Part no.	[15W] PS3V-015AF 05C / 12C / 24C	[30W] PS3V-030AF 05□ / 12□ / 24□	[50W] PS3V-050AF 12□ / 24□	[100W] <b>PS3V-100AF2</b> 4□	[150W] P <b>S3V-150AF</b> 24□		
	Rated	input voltage		100 to 240V AC			4			
		ge range) (*1)		85 to 264V AC (Single phase 2 wire)						
	Frequency			47 to 63Hz						
	Input current (at rated output)		100V: 0.32A (typ) 230V: 0.2A (typ)	100V: 0.66A (typ) 230V: 0.35A (typ)	100V: 1.1A (typ) 230V: 0.6A (typ)	100V: 1.3A (typ) 230V: 0.6A (typ)	100V: 1.9A (typ) 230V: 0.9A (typ)			
_	Inrush (Ta =	n current	at 100V AC	40A typ.	18A typ.	18A typ.	18A typ.	18A typ.		
1put	cold s	- /	at 230V AC	60A typ.	45A typ.	45A typ.	45A typ.	45A typ.		
Con	Leaka	ige current		120V: 0.5mA max., 24	DV: 1mA max.			1		
Input conditions		-	5V	77% (100VAC) 76% (230VAC)	77% (100VAC) 77% (230VAC)	_	_	-		
-	Efficie (TYP.)		12V	82% (100VAC) 81% (230VAC)	83% (100VAC) 83% (230VAC)	84% (100VAC) 84% (230VAC)	_	-		
	(at rate	ed output)	24V	84% (100VAC) 83% (230VAC)	85% (100VAC) 84% (230VAC)	87% (100VAC) 87% (230VAC)	85% (100VAC) 88% (230VAC)	85% (100VAC) 88% (230VAC)		
		r factor (TYP.) ed output)		_	_	_	0.98 (100V AC) 0.9 (230V AC)	0.98 (100V AC) 0.95 (230V AC)		
		. ,		5V / 3A	5V / 6A	-	-	-		
	Outpu	t voltage/Curren	t	12V / 1.3A	12V / 2.5A	12V / 4.5A	_	_		
				24V / 0.63A	24V / 1.3A	24V / 2.3A	24V / 4.5A	24V / 6.5A		
	Adjus	table voltage rar	ige 5V	$\pm 10\%$ (Front, adjustab	e using V.ADJ volume)	_	_	_		
	Outou	t holding time	5V 12V	15ms typ. (100V AC) 120ms typ. (230V AC)	18ms typ. (100V AC)			-		
		ted output)	24V	20ms typ. (100V AC) 130ms typ. (230V AC)	110ms typ. (230V AC)	17ms typ. (100V AC) 125ms typ. (230V AC)	35ms typ. (100V AC) 35ms typ. (230V AC)	24ms typ. (100V A0 24ms typ. (230V A0		
Start time				650ms max. (at rated i	nput/output)			2 mo typ. (2007) k		
Rise Time Condition Load fluctuation Temperature fluctuation				300ms max. (at rated input/output) 200ms max. (at rated input/output)						
con		Input fluctuatio	n	0.4% max.						
ditio		Load fluctuatio	n	1% max.						
ß	Jons	Temperature fl	uctuation	0.05%/°C max. (-10 to +50°C)						
	stant vol		–25 to –10°C	5V: 8%p-p max. 12V: 6%p-p max. 24V: 4%p-p max.	5V: 8%p-p max. 12V: 6%p-p max. 24V: 4%p-p max.	12V: 6%p-p max. 24V: 4%p-p max.	24V: 4%p-p max.			
	Constant voltage accuracy	Ripple (including noise)	-10 to 0°C	5V: 5%p-p max. 12V: 2.5%p-p max. 24V: 1.5%p-p max.	5V: 5%p-p max. 12V: 2.5%p-p max. 24V: 1.5%p-p max.	12V: 2.5%p-p max. 24V: 1.5%p-p max.	24V: 1.5%p-p max.			
	acy		0 to 50°C	5V: 2.5%p-p max. 12V: 1.5%p-p max. 24V: 1%p-p max.	5V: 2.5%p-p max. 12V: 1.5%p-p max. 24V: 1%p-p max.	12V: 1.5%p-p max. 24V: 1%p-p max.	24V: 1%p-p max.			
Suppl	Overc	urrent protectior	ı	105% min. (auto reset)	(*2)					
plementary	Overv	oltage protection	ı	120% min. (intermittent, auto reset)	Output off at 120% mi	n, reset when re-input				
Itary	Opera	tion indicator		LED (green)						
	Betwe	en input and ou	tput terminals	3000V AC, 1 minute						
Dielectric		en input and gr		2000V AC, 1 minute						
ŧ tric	Betwe	en output and g	round terminals	500V AC, 1 minute						
		resistance 100MΩ min. 500V DC megger (at 25°C, 70% RH) (between input and output terminals, between input and ground term					out and ground termina			
	<u> </u>	nperature			zing, output derating av	ailable)				
	ting hu e temr	midity perature		20 to 90% RH (no cond						
~ ~	je territ je hum			-25 to +75°C (no freezing) 20 to 90% RH (no condensation)						
		istance		10 to 55 Hz, 2G constant, 2 hours each in 3 axes						
hock	resista	ance		200M/s <sup>2</sup> , 11ms, 1 shoo	k each in 6 axes					
xpect	ted life	(reference value			ut, load factor 50%, ope	rating temperature +40°	C, standard mounting)			
мс			EMI	EN61204-3 Class B	\					
afety	standa	ards	EMS		62368-1 2-201, CSA C22.2 No.61	1010-1, CSA C22.2 No.6	1010-2-201 (Listing, SE	ELV *all models pendi		
imon	sione (m	nm) (terminal part	evcent		2 No.62368-1-14 (Recog	<u> </u>		1		
rotrus		ing terminal part		50.8H×34W×65D	68.5H×34.5W×95.5D	80H×36W×99D	93H×39W×108D	95H×39W×159D		
	t (appr			135g	190g	230g	380g	510g		
		ew (horizontal ty		M3	M3.5					

\*1) Not subjected to safety standards. Output delay also available.
\*2) If overload continues for over 30 seconds, the internal elements may be damaged.


PS3V-015AF is equipped with a thermal shutdown function. When thermal shutdown operates, auto reset does not function until the temperature inside the power supply drops.

\*3)Calculation of the expected life is based on the actual life of the aluminum electrolytic capacitor. The expected life depends on operating conditions.


#### **Block diagram**



PS3V-030AF, PS3V-050AF




#### PS3V-100AF, PS3V-150AF




#### Characteristics

Output current - Operating temperature characteristics (Output derating) \*Conditions: Natural air cooling (operating temperature is the temperature around the power supply)




**Overcurrent protection characteristics** 




Output current - Input voltage characteristics (Output derating) (Ta=25°C)

#### PS3V-015AF / -030AF

PS3V-050AF









#### Operating temperature by safety standards

UL / c-UL / TÜV	A mount	50°C
0270-027100	B mount	40°C


6





(standard mount)





upward Λ


B mount

C mount D mount

#### **Parts Description**


Note) Note the terminal arrangement when wiring.

#### Horizontal terminal type




#### **Dimensions**

#### Horizontal terminal type PS3V-015AF C



PS3V-030AF C



General tolerance: ±1 mm

#### Dimensions

#### PS3V-050AF□C



5-M3.5 (Terminal Screw)

ള

2

(123.5) 108

<del>3</del>80

76

۲

All dimensions in mm. General tolerance:  $\pm 1$  mm

2-M3 (Depth 6mm max)


5

<u>8</u>


<u>3-M3</u> (Depth 6mm max)

12.5.

. ان ان




#### PS3V-150AF24C




#### Push-in terminal type


PS3V-030AF□P




#### PS3V-100AF24P



PS3V-050AF□P



PS3V-150AF24P




8

#### Mounting bracket (L-shaped bracket) Dimensions

All dimensions in mm.

PS9Z-3N3A (applicable model: 15W)




#### Dimensions when mounting bracket is used

#### L-mount bracket



#### DIN-rail mount bracket



Part no.	Applicable model	L2
PS9Z-3N3A	PS3V-015AF C	83.5
	PS3V-030AF□C	118.5
	PS3V-030AF□P	108.5
PS9Z-3E3B	PS3V-050AF□C	125.5
P392-3E3D	PS3V-050AF□P	115.5
	PS3V-100AF□C	130.5
	PS3V-100AF□P	120.5

Part no.	Applicable model	L1	L2	L3	H1	H2	H3
PS9Z-3N4B	PS3V-015AF□C	93	107	35	5.2	21	50.8
	PS3V-030AF□C	134	136	35	5.2	21	68.5
PS9Z-3E4C	PS3V-030AF□P	134	125	35	5.2	21	68.5
	PS3V-050AF□C	134	134	35	5.2	21	80
	PS3V-050AF□P	134	124	35	5.2	21	80
PS9Z-3E4D	PS3V-100AF C	186	186	39.5	5.2	20	93
	PS3V-100AF□P	186	176	39.5	5.2	20	93
	PS3V-150AF□C	186	192	39.5	5.2	20	95
	PS3V-150AF□P	186	182	39.5	5.2	20	95

PS9Z-3E3B (applicable model: 30W/50W/100W)

5-ø3.5 hole

77±0.

80<sup>±0.3</sup> 103

A par

#### ▲ Safety Precautions

This product is for use in control panels and inside products and cannot be externally connected.

Do not use the product alone as an Electric Facilities for General Use.

• When using the product, follow the following precautions.

#### [Precautions on switching power supplies]

- This product is for industrial or general electronic equipment (such as communication, measurement, and industrial electronic equipment). Do not use for devices that may cause malfunction or may harm the body or threaten human life.
- Make sure that the input voltage and output current do not exceed the ratings. Otherwise, electric shock, fire, or malfunction may occur.
- Do not touch the terminals of the switching power supply while input voltage is applied, otherwise electric shock may occur.
- Take protective measures with the final product to prevent malfunctions caused by the switching power supply.

- Operating temperatures should not exceed the ratings. Be sure to note the derating characteristics. Otherwise, electric shock, fire, or malfunction may occur.
- Blown fuses indicate that the internal circuits are damaged. Contact IDEC for repair. If only the fuse is replaced, electric shock, fire, or malfunction may occur.
- Do not use the switching power supplies to charge rechargeable batteries.
- Do not overload or short-circuit the switching power supply for a long period of time, otherwise the internal elements may be damaged.
- Do not disassemble, repair, or modify the power supplies, otherwise the high voltage internal part may cause electric shock, fire, or malfunction.

### 93.5 Mouling hole

6.5×4.5 nounting hole

All dimensions in mm.


#### Instructions

For details on mounting, wiring, and circuit examples, see the instruction manual from the below URL. URL: https://product.idec.com/?product=PS3V



#### Notes for installation

- 1. When mounting the PS3V, see page 7.
- 2. See page 7 and 8 for mounting hole layout.
- 3. Use M3 or M4 screw as mounting screws. The tightening torque of the mounting screw is 0.49N·m.



- Do not close the openings of the switching power supply. Ensure proper heat dissipation by convection.
- Maintain a minimum of 20 mm clearance around the switching power supply.
- When derating of the output does not work, provide forced aircooling.
- 7. Make sure to wire the ground terminal correctly.
- 8. Use copper wire only. In addition, refer to the below table to select wire types and number of wires.

Terminal	Wire size (Allowable current)	Wire type
Input	AWG18 to 14	
Output	AWG18 to 14 (AWG18-7A, AWG16-10A, AWG14-15A	Copper, solid/stranded

- Cross section AWG18: 0.82mm<sup>2</sup>, AWG16: 1.31mm<sup>2</sup>, AWG14: 2.08mm<sup>2</sup>
  See page 11 for Push-in type
- 9. Recommended tightening torque of terminal screws: 0.8 N·m (PS3V-015 : 0.5 N·m)

#### Adjustment of output voltage

The output voltage can be adjusted within  $\pm 10\%$  of the rated output voltage by using the V.ADJ control. Turning the V.ADJ clockwise increases the output voltage. Turning counterclockwise decreases the output voltage. Note that overvoltage protection may function when output voltage is increased.

#### **Overcurrent protection**

The output voltage drops automatically when an overcurrent flows, resulting in intermittent operation. Normal voltage is automatically restored when the load returns to normal condition. However, overcurrent for a prolonged period of time or short-circuit causes the internal elements to deteriorate or break down.

#### **Overvoltage protection**

#### • PS3V-015□:

Voltage limit and auto-recovery method. The switching power supplies operate normally when voltage returns to normal.

• PS3X-030□, -050□, -100□, -150□:

The output is turned off or intermittent operation when an overvoltage is applied. When the output voltage has dropped due to an overvoltage, turn the input off, and after one minute, turn the input on again.

#### Insulation/Dielectric test


When performing an insulation/dielectric test, short the input (between AC) and output (between + and -). Do not apply or interrupt the voltage suddenly, otherwise surge voltage may be generated and the power supply may be damaged.

#### Noise

Small acoustic noise inside the PS3V may be heard depending on the input voltage and load, but the performance of the PS3V is not affected.


#### Series operation

The following series operation is allowed. In (b) series operation, connect Schottky barrier diodes. Choose (a) series operation when using the PS3V as positive and negative output power supply. Insert a Shottky barrier diode for loads such as operational amplifier where outputs of two power supplies may be connected in series (Load 3). Select a Schottky diode in consideration of the rated current.



#### **Parallel operation**

Parallel operation is not possible to increase the output capacity, because the internal elements and load may be damaged. Backup operation is a connection method of two switching power supplies in parallel for emergency. Normally one switching power supply has a sufficient output. If one switching power supply fails, another one operates to continue the output. Make sure that the sum of power consumption by load and diode is not greater than the rated wattage (rated voltage × rated current) of one switching power supply. The current of the diode that is used must be more than double the output current of PS3V. Take heat dissipation into consideration.



#### Rust and scratches on metal parts

Hot-dip galvanized steel and bonderized steel are used for the PS3V. Rust on the edge and scratches on the surfaces may be developed depending on the storage condition, but the performance of the PS3V is not affected.

10 **IDEC** 

#### Accessories and wiring for Push-in terminals

#### Wire size and recommended ferrules (Push-in terminal type only)


#### Ferrules with insulated covers

		ble Wire ed Wire)	Wire Strip Length	Part No. (Ordering No.)
	AWG	mm <sup>2</sup>	(mm)	(Ordening No.)
_	18	0.75	12	S3TL-H075-16WW
For 1 wire	17	1.0	12	S3TL-H10-16WY
wire	16	1.5	12	S3TL-H15-16WR
For 2 wires	18	0.75	21	S3TL-J075-19WWS

#### Recommended tools (Optional. See page 4 for details)

Name	Part No. (Ordering No.)
Crimping tool	S3TL-CR06D
Auto-adjust stripping tool	S3TL-ST06
Insulated screwdriver	S3TL-D04-25-75

Note) Use a flat blade screwdriver with a blade size of  $0.4 \times 2$  to 2.5 mm.



#### Wiring procedure

#### Wiring

- (1) Insert the solid wire or stranded wire with ferrule into the terminal entrance.
  - \* If the shape of the ferrule becomes trapezoidal after the clamping, insert the ferrule with the long side of the clamped part parallel to the pusher.
  - \* When inserting stranded wires directly, make sure that the pusher in pressed down and there are no loose wires.

Note) When inserting a ferrule terminal with two wires, insert the insulated cover part vertically to the pusher.



Insulated cover part

(2) After wiring, tug lightly to make sure that the wire is properly connected.

#### Removing the wire

(1) Press the pusher using a insulated screwdriver.



Pushe

(2) Remove the wire by pressing the pusher.



#### Warranty

#### Warranty

IDEC warranties the PS3V switching power supplies for a period of five years from the date of shipment.

#### Scope

In the event of a failure caused by our responsibility within the above period, we will replace the product. However, if the product is used under the following conditions, the warranty may not apply even within the warranty period.

- 1. Average operating temperature (ambient temperature of switching power supply) is 40°C maximum.
- 2. The load is 60% maximum.
- 3. Input voltage is the rated input voltage.
- 4. Standard mounting style

If we are responsible for a failure that occurs during the warranty period described at left, we will repair the product or replace it with an alternative product.

Please note that we will not be liable for any damage caused by the failure of the delivered product. In addition, please note that the warranty does not apply to the following cases.

- 1. Inappropriate handling, or operation beyond the specifications.
- 2. Modification or repair by other than IDEC.
- 3. Failure caused by reasons other than the switching power supply.
- 4. Failure caused by natural disasters.

#### **Ordering Terms and Conditions**

Thank you for using IDEC Products.

By purchasing products listed in our catalogs, datasheets, and the like (hereinafter referred to as "Catalogs") you agree to be bound by these terms and conditions. Please read and agree to the terms and conditions before placing your order.

#### 1. Notes on contents of Catalogs

(1) Rated values, performance values, and specification values of IDEC products listed in this Catalog are values acquired under respective conditions in independent testing, and do not guarantee values gained in combined conditions.

Also, durability varies depending on the usage environment and usage conditions.

- (2) Reference data and reference values listed in Catalogs are for reference purposes only, and do not guarantee that the product will always operate appropriately in that range.
- (3) The specifications / appearance and accessories of IDEC products listed in Catalogs are subject to change or termination of sales without notice, for improvement or other reasons.
- (4) The content of Catalogs is subject to change without notice.

#### 2. Note on applications

- If using IDEC products in combination with other products, confirm the applicable laws / regulations and standards. Also, confirm that IDEC products are compatible with your systems, machines.
  - Also, confirm that IDEC products are compatible with your systems, machines, devices, and the like by using under the actual conditions. IDEC shall bear no liability whatsoever regarding the compatibility with IDEC products.
- (2) The usage examples and application examples listed in Catalogs are for reference purposes only. Therefore, when introducing a product, confirm the performance and safety of the instruments, devices, and the like before use. Furthermore, regarding these examples, IDEC does not grant license to use IDEC products to you, and IDEC offers no warranties regarding the ownership of intellectual property rights or non-infringement upon the intellectual property rights of third parties.
- (3) When using IDEC products, be cautious when implementing the following.
   i. Use of IDEC products with sufficient allowance for rating and performance
  - Safety design, including redundant design and malfunction prevention design that prevents other danger and damage even in the event that an IDEC product fails
  - Wiring and installation that ensures the IDEC product used in your system, machine, device, or the like can perform and function according to its specifications
- (4) Continuing to use an IDEC product even after the performance has deteriorated can result in abnormal heat, smoke, fires, and the like due to insulation deterioration or the like. Perform periodic maintenance for IDEC products and the systems, machines, devices, and the like in which they are used.
- (5) IDEC products are developed and manufactured as general-purpose products for general industrial products. They are not intended for use in the following applications, and in the event that you use an IDEC product for these applications, unless otherwise agreed upon between you and IDEC, IDEC shall provide no guarantees whatsoever regarding IDEC products.
  - i. Use in applications that require a high degree of safety, including nuclear power control equipment, transportation equipment (railroads / airplanes / ships / vehicles / vehicle instruments, etc.), equipment for use in outer space, elevating equipment, medical instruments, safety devices, or any other equipment, instruments, or the like that could endanger life or human health
  - ii. Use in applications that require a high degree of reliability, such as provision systems for gas / waterworks / electricity, etc., systems that operate continuously for 24 hours, and settlement systems
  - iii. Use in applications where the product may be handled or used deviating from the specifications or conditions / environment listed in the Catalogs, such as equipment used outdoors or applications in environments subject to chemical pollution or electromagnetic interference If you would like to use IDEC products in the above applications, be sure to consult with an IDEC sales representative.

## IDEC CORPORATION

#### Head Office

6-64, Nishi-Miyahara-2-Chome, Yodogawa-ku, Osaka 532-0004, Japan

USA	IDEC Corporation	Tel: +1-408-747-0550	opencontact@idec.com	Hong Kong
Germany	APEM GmbH	Tel: +49-40-25 30 54-0	service@eu.idec.com	China
Singapore	IDEC Izumi Asia Pte. Ltd.	Tel: +65-6746-1155	info@sg.idec.com	
Thailand	IDEC Asia (Thailand) Co., Ltd	Tel: +66-2-392-9765	sales@th.idec.com	
India	IDEC Controls India Private Limited	Tel: +91-80679-35328	info_india@idec.com	Japan
Taiwan	IDEC Taiwan Corporation	Tel: +886-2-2577-6938	service@tw.idec.com	

Specifications and other descriptions in this brochure are subject to change without notice. Information in this brochure is current as of May, 2021. 2021 IDEC Corporation, All Rights Reserved.

#### 3. Inspections

We ask that you implement inspections for IDEC products you purchase without delay, as well as thoroughly keep in mind management/maintenance regarding handling of the product before and during the inspection.

#### 4. Warranty

(1) Warranty period

The warranty period for IDEC products shall be five (5) years after purchase or delivery to the specified location. However, this shall not apply in cases where there is a different specification in the Catalogs or there is another agreement in place between you and IDEC.

(2) Warranty scope

Should a failure occur in an IDEC product during the above warranty period for reasons attributable to IDEC, then IDEC shall replace or repair that product, free of charge, at the purchase location / delivery location of the product, or an IDEC service base. However, failures caused by the following reasons shall be deemed outside the scope of this warranty.

i. The product was handled or used deviating from the conditions / environment listed in the Catalogs

- ii. The failure was caused by reasons other than an IDEC product
- iii. Modification or repair was performed by a party other than IDEC

iv. The failure was caused by a software program of a party other than IDEC

- v. The product was used outside of its original purpose
- vi. Replacement of maintenance parts, installation of accessories, or the like was not performed properly in accordance with the user's manual and Catalogs

vii. The failure could not have been predicted with the scientific and technical standards at the time when the product was shipped from IDEC

viii. The failure was due to other causes not attributable to IDEC (including cases of force majeure such as natural disasters and other disasters)

Furthermore, the warranty described here refers to a warranty on the IDEC product as a unit, and damages induced by the failure of an IDEC product are excluded from this warranty.

#### 5. Limitation of liability

The warranty listed in this Agreement is the full and complete warranty for IDEC products, and IDEC shall bear no liability whatsoever regarding special damages, indirect damages, incidental damages, or passive damages that occurred due to an IDEC product.

#### 6. Service scope

The prices of IDEC products do not include the cost of services, such as dispatching technicians. Therefore, separate fees are required in the following cases.

- Instructions for installation / adjustment and accompaniment at test operation (including creating application software and testing operation, etc.)
- (2) Maintenance inspections, adjustments, and repairs
- (3) Technical instructions and technical training
- (4) Product tests or inspections specified by you

IDEC Izumi (H.K.) Co., Ltd.

IDEC (Shanghai) Corporation

**IDEC** Corporation

Beijing Branch

Guangzhou Branch

The above content assumes transactions and usage within your region. Please consult with an IDEC sales representative regarding transactions and usage outside of your region. Also, IDEC provides no guarantees whatsoever regarding IDEC products sold outside your region.



Tel: +852-2803-8989

Tel: +86-21-6135-1515

Tel: +86-10-6581-6131

Tel: +86-20-8362-2394

Tel: +81-6-6398-2527

info@hk.idec.com idec@cn.idec.com idec@cn.idec.com idec@cn.idec.com jp marketing@idec.com

