


# Product data sheet

Specifications



Harmony XVS, Electronic alarm, white, NPN, mounting support DIN 72, 0...90 dB, 16 tones, 4 channels, 12...24 V AC/DC

XVS72BMWN

## Main

|                           |                  |
|---------------------------|------------------|
| Range of product          | Harmony XVS      |
| Product or component type | Electronic alarm |
| Device short name         | XVS              |

## Complementary

|  |   |
|--|---|
| Colour                                 | White   |
| Material                               | ABS (acrylonitrile butadiene-styrene): body<br>PC (polycarbonate): terminal cover |
| Net weight                             | 0.18 kg   |
| Marking                                | CE  |
| Overvoltage category                   | Class II conforming to EN/IEC 61140   |
| Mounting support                       | 72 mm DIN rail  |
| [Us] rated supply voltage              | 12...24 V DC  |
| [Uimp] rated impulse withstand voltage | 0.8 kV  |
| Current consumption                    | 117 mA at 12 V<br>125 mA at 24 V<br>158 mA at 12 V<br>200 mA at 24 V              |
| Clamping connection capacity           | $\leq 1 \times 1.5 \text{ mm}^2$  |
| Width                                  | 72 mm   |
| Height                                 | 72 mm   |
| Depth                                  | 69.3 mm   |

## Environment

|                                     |  |
|-------------------------------------|--|
| Discrete output type                | NPN  |
| Signalling type                     | 16 tones alarm                                 |
| Standards                           | EN/IEC 61000-6-2<br>UL 464<br>EN/IEC 61000-6-3 |
| Product certifications              | UR   |
| Protective treatment                | TC   |
| Ambient air temperature for storage | -35...70 °C                                    |

|  |  |
|--|--|
| <b>Ambient air temperature for operation</b> | -10...50 °C  |
| <b>IP degree of protection</b>               | Panel mounted: IP54 conforming to EN/IEC 60529     |
| <b>Noise level</b>                           | 0...90 dB (continuous or intermittent tone) at 1 m |

## Packing Units

|                                     |           |
|-------------------------------------|-----------|
| <b>Unit Type of Package 1</b>       | PCE       |
| <b>Number of Units in Package 1</b> | 1         |
| <b>Package 1 Weight</b>             | 264 g     |
| <b>Package 1 Height</b>             | 10.4 cm   |
| <b>Package 1 width</b>              | 9.4 cm    |
| <b>Package 1 Length</b>             | 9.4 cm    |
| <b>Unit Type of Package 2</b>       | S03       |
| <b>Number of Units in Package 2</b> | 16        |
| <b>Package 2 Weight</b>             | 4.937 kg  |
| <b>Package 2 Height</b>             | 30 cm     |
| <b>Package 2 width</b>              | 30 cm     |
| <b>Package 2 Length</b>             | 40 cm     |
| <b>Unit Type of Package 3</b>       | PAL       |
| <b>Number of Units in Package 3</b> | 128       |
| <b>Package 3 Weight</b>             | 34.048 kg |
| <b>Package 3 Height</b>             | 60 cm     |
| <b>Package 3 width</b>              | 80 cm     |
| <b>Package 3 Length</b>             | 128 cm    |

## Offer Sustainability

|                                   |   |
|-----------------------------------|---|
| <b>Sustainable offer status</b>   | Green Premium product   |
| <b>REACH Regulation</b>           | <a href="#">REACH Declaration</a>   |
| <b>EU RoHS Directive</b>          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>   |
| <b>Mercury free</b>               | Yes   |
| <b>RoHS exemption information</b> | <a href="#">Yes</a>   |
| <b>China RoHS Regulation</b>      | <a href="#">China RoHS declaration</a>  |
| <b>Environmental Disclosure</b>   | <a href="#">Product Environmental Profile</a>   |
| <b>Circularity Profile</b>        | <a href="#">End of Life Information</a>   |
| <b>California proposition 65</b>  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

Electronic Alarm

---

Dimensions

