





CLIFF

SLIM BNC 75 Ohm FRONT MOUNTING METAL FRAME FEEDTHROUGH



2x HOLE VARIANTS
Ø3.2mm CSK 90° x Ø5.85
'X1' PLAIN Ø3.2 HOLES



VARIANTS

Part No.

CP30638M

SLIM BNC 75Ω Nickel frame, CSK holes

CP30638MB

SLIM BNC 75Ω Black metal frame, CSK holes

CP30638MX1

SLIM BNC 75Ω Nickel frame, Ø3.2 PLAIN holes

CP30638MBX1

SLIM BNC 75Ω Black metal frame, Ø3.2 PLAIN holes

Feedthrough Features

- Fits standard rectangular cutout.
- Various hole mounting options.
- No soldering or punch termination. Use standard cable for each connector style.
- Low rear profile.

Material:

1. SLIM Frame: Diecast, Nickel or black plated
2. BNC Frame: ABS UL94 V2
3. BNC Body: Brass - Nickel Plated
4. BNC Centre: Brass - Copper Plated
5. BNC Insulator: PP UL94 V2

General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.