

TOS 16 SC, 16-way PLC Splitter

Art. Number 307906



The optical splitter uses a planar light wave circuit (PLC) based on silica optical waveguide technology. It features small size, high reliability, wide operating wavelength range and good channel-to-channel uniformity.

The splitter circuit is packaged in a plastic cassette and are terminated with SC/APC connectors. The cassette can be mounted:

- on the wall
- in 19" 3HU rack
- in Fibre Distribution Cabinet TOS-Cab16 (307910) or TOS-Cab32 (307911)

The TOS xxSC splitters are recommended for optical signal distribution in:

- FTTX systems
- PON networks
- CATV and SAT-IF fibre links

Technical Specifications

ORDER INFORMATION

EAN Number 5702663079069

CHARACTERISTICS

Coupling Ratio (OPTO) | % 16 x 6.25 %
 Type TOS 16 SC/APC
 Wavelength | nm 1260...1650 nm

LOSS

Insertion loss (typ.) | dB 13.0 dB

OPERATIONAL

Temperature - operating | °C -40...85 °C
 Temperature - storage | °C -40...85 °C

CONNECTORS

Connector Type SC/APC



TRIAx

connecting the future

Technical Specifications

Number of inputs	1
Number of outputs	16

MECHANICAL

Colour	RAL 7035 - Light grey
Dimensions product (H x D x W) mm	130x113x52 mm
Packaging Depth m	0.052 m
Packaging Height m	0.130 m
Total Weight kg	0.215 kg
Packaging Width m	0.113 m
Net Weight kg	0.185 kg
Tara Weight kg	0.030 kg
Packaging Volume m3	0.001 m3