

Aspect

Intelligent Dimmers

2 WAY SINGLE 230V
A.C. 50HZ 40W/VA MIN.
300W/240VA MAX.

2 WAY DOUBLE 230V
A.C. 50HZ 40W/VA MIN.
300W/240VA MAX.
FOR EACH DIMMER

Grid Plus Modular Frontplates

SUPPLIED WITH MOUNTING FRAME

1 MODULE

2 MODULE

				
FINISHES				
BRUSHED STAINLESS STEEL	K24521BSS1	K24522BSS1	K24331BSS1	K24332BSS1
LACQUERED BRUSHED STEEL	K24521LBS1	K24522LBS1	K24331LBS1	K24332LBS1
BRUSHED CHROME	K24521BRC1	K24522BRC1	K24331BRC1	K24332BRC1
POLISHED CHROME	K24521POC1	K24522POC1	K24331POC1	K24332POC1
SATIN GOLD	K24521SAG1	K24522SAG1	K24331SAG1	K24332SAG1
PORCELAIN WHITE	K24521WHI1	K24522WHI1	K24331WHI1	K24332WHI1
LUSTROUS IVORY	K24521LIV1	K24522LIV1	K24331LIV1	K24332LIV1
LUSTROUS BLACK	K24521LBK1	K24522LBK1	K24331LBK1	K24332LBK1
POLISHED BRASS	K24521PBR1	K24522PBR1	K24331PBR1	K24332PBR1
TEXTURED IRON	K24521TIR1	K24522TIR1	K24331TIR1	K24332TIR1
DESERT BRONZE	K24521DBZ1	K24522DBZ1	K24331DBZ1	K24332DBZ1
ANTIQUE BRASS	K24521ABS1	K24522ABS1	K24331ABS1	K24332ABS1
TEXTURED COPPER	K24521TCO1	K24522TCO1	K24331TCO1	K24332TCO1

LEAD TIMES
Please contact our Customer
Services Department on
01268 563 404

MOUNTING BOXES
FLUSH 35MM
866ZIC
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm

MOUNTING BOXES
FLUSH 35MM
866ZIC
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm

MOUNTING BOX
FLUSH
891ALM
DIMENSIONS
86 x 86mm
BS 5733:2010

MOUNTING BOX
FLUSH
891ALM
DIMENSIONS
86 x 86mm
BS 5733:2010

These dimmers employ the latest micro-controller based circuitry to provide electronic soft-start and overload protection. They are suitable for use with good quality electronic or wire-wound transformers. Can also be used with good quality halogen lamps incorporating GU10 bases. Please check with lamp manufacturer to determine suitability.

NOT SUITABLE FOR FLUORESCENT LOADS.

Conform to latest standards BS EN 60669-2-1.

All intelligent dimmers have a combined push-on/push-off switch and rotary dimmer control, and are suitable for one or two-way switching. Only one dimmer can be used in a two way switching circuit.