



Technical Hotline
+44 (0)1268 563720

Switch Modules 20 Amp

DP 1 WAY PUSH TO BREAK RETRACTIVE 20 AMP	DP 1 WAY RED ROCKER PUSH TO BREAK RETRACTIVE 20 AMP	SP 2 WAY 20 AMP	SP 2 WAY RED ROCKER 20 AMP	SP 2 WAY WITH INTEGRAL NEON LOCATOR 20 AMP	SP 2 WAY & CENTRE OFF 20 AMP
---	---	--------------------	----------------------------------	---	------------------------------------



K4915WHI 10 K4915BLK 10	K4915RED 10 K4915REDB 1	K4892BSS* 1	K4892RED 10 K4892REDB 10	K4892LWHI 10 K4892LBLK 1	K4899BSS* 1
		K4892LBS* 1			K4899LBS* 1
		K4892BRC* 1			K4899BRC* 1
		K4892POC* 1			K4899POC* 1
		K4892SAG* 1			K4899SAG* 1
		K4892WHI 10			K4899WHI 10
		K4892LIVW 1			K4899LIVW 1
		K4892LBKB 1			K4899LBKB 1
		K4892PBR* 1			K4899PBR* 1
		K4892TIRB 1			K4899TIRB 1
		K4892DBZB 1			K4899DBZB 1
		K4892ABSB 1			K4899ABSB 1
		K4892TCOB 1			K4899TCOB 1

NOTE
Push switches are not designed for fluorescent loads.
BS EN 60669-1:1999

NOTE
Push switches are not designed for fluorescent loads.
BS EN 60669-1:1999

These switches do NOT have to be derated when used with fluorescent or inductive loads.
BS EN 60669-1:1999

These switches do NOT have to be derated when used with fluorescent or inductive loads.
Additional information on printed modules available in Grid Plus Section, pages 175.
BS EN 60669-1:1999

These switches do NOT have to be derated when used with fluorescent or inductive loads.
BS EN 60669-1:1999

* Available with the option of either White or Black inserts. Add Suffix 'W' or 'B' to part number when ordering, E.g. KxxxxBSSW.
Where there is no asterisk, the final suffix W = White Insert, B = Black Insert, E.g. KxxxxLIVW Lustrous Ivory finish with white inserts.

Matching metal capped rockers available as standard (excluding porcelain white finish).

Matching metal capped rockers available as standard (excluding porcelain white finish).