

TOS-Cab16 Fibre Distribution Cabinet

Art. Number 307910



Distribution box for TRIAX PLC splitters TOS xxSC, splice trays, layout pigtailed to match trunk and drop fibre cables.

Can be used as fibre optic terminations of optic access network or sub-distribution points in and outdoor.

- Plastic enclosure, flame retardant, ageing and UV resistant
- Special screw and key for its door lock
- Mounting on wall or on pole
- Bi-layer structure of the box: bottom for splicing and upper layer for splitting and distribution
- Special lock device for outlet of drop cables
- 2 standard slots for TOS xxSC PLC splitter cassettes--> max splitting factor: 16

Technical Specifications

ORDER INFORMATION

EAN Number 5702663079106

CHARACTERISTICS

Place of Usage Splitter cassettes: 1 x 1:16 or 2 x 1:8 + 2 x splice trays

Type TOS-Cab16

OPERATIONAL

IP Housing protection class IP 65

Temperature - operating | °C -40...+80 °C

Temperature - storage | °C -40...+80 °C

MECHANICAL

Colour RAL 7035 - Light grey

Product Depth | mm 130 mm

Packaging Depth | m 0.143 m

Packaging Height | m 0.304 m



TRIAx

connecting the future

Technical Specifications

Total Weight kg	1.690 kg
Packaging Width m	0.355 m
Product Height mm	335 mm
Main material	Plastic
Net Weight kg	1.550 kg
Tara Weight kg	0.140 kg
Packaging Volume m3	0.015 m3
Product Width mm	295 mm