

3M™ Adhesive Transfer Tape 950

Last Revision Date: Dec, 2020



Product Description

3M™ Adhesive Transfer Tapes with 3M™ Adhesive 300 offer excellent adhesion to a wide variety of surfaces, including low surface energy plastics and foam. This pressure sensitive medium firm acrylic adhesive family features very high initial adhesion with good holding power and is available in several thicknesses for a wide variety of surface bonding and provides a variety of liner configurations to help ensure excellent process flexibility.






Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

| Property | Values | Additional Information |
|-------------------------|--------------------|------------------------|
| Adhesive Type | Acrylic | |
| Liner | 58# Glassine paper | |
| Liner Thickness | 0.08 mm (3.2 mil) | |
| Liner Color | Tan, No Print | View |
| Test Name: Primary | | |
| Total Tape Thickness | 5 mil (0.13 mm) | View |
| Test Method: ASTM D3652 | | |
| Total Tape Thickness | 0.13 mm | View |
| Test Method: ASTM D3652 | | |
| Liner Print | None | |
| Liner Thickness | 3.2 mil | |

Typical Performance Characteristics

| Property | Values | Additional Information |
|--|---------------------|--|
| 90° Peel Adhesion | 8.1 N/cm | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 15.0 Dwell Time Units: min Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: Stainless Steel Backing: 2 mil Aluminum Foil</p> | | |
| 90° Peel Adhesion | 74 oz/in | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 15.0 Dwell Time Units: min Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: Stainless Steel Backing: 2 mil Aluminum Foil</p> <p>Notes: 12 in/min (300 mm/min)</p> | | |
| 90° Peel Adhesion | 3.7 N/cm (34 oz/in) | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 15.0 Dwell Time Units: min Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: ABS Backing: 2 mil Aluminum Foil</p> <p>Notes: 12 in/min (300 mm/min)</p> | | |
| 90° Peel Adhesion | 34 oz/in | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 15.0 Dwell Time Units: min Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: ABS Backing: 2 mil Aluminum Foil</p> <p>Notes: 12 in/min (300 mm/min)</p> | | |
| 90° Peel Adhesion | 6.6 N/cm (60 oz/in) | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 15.0 Dwell Time Units: min Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: Polypropylene (PP) Backing: 2 mil Aluminum Foil</p> <p>Notes: 12 in/min (300 mm/min)</p> | | |
| 90° Peel Adhesion | 60 oz/in | |

View 

Test Method: ASTM D3330

Dwell/Cure Time: 15.0

Dwell Time Units: min

Temp C: 23C

Temp F: 72F

Environmental Condition: 50%RH


Substrate: Polypropylene (PP)

Backing: 2 mil Aluminum Foil

Notes: 12 in/min (300 mm/min)

90° Peel Adhesion

9.4 N/cm

View 

Test Method: ASTM D3330

Backing: 2 mil Aluminum Foil

Notes: 12 in/min (300 mm/min)

90° Peel Adhesion

86 oz/in

View 

Test Method: ASTM D3330

Dwell/Cure Time: 72.0

Dwell Time Units: hr

Temp C: 23C

Temp F: 72F

Environmental Condition: 50%RH

Substrate: Stainless Steel

Backing: 2 mil Aluminum Foil

Notes: 12 in/min (300 mm/min)

90° Peel Adhesion

4.4 N/cm (40 oz/in)

View 

Test Method: ASTM D3330

Dwell/Cure Time: 72.0

Dwell Time Units: hr

Temp C: 23C

Temp F: 72F

Environmental Condition: 50%RH

Substrate: ABS

Backing: 2 mil Aluminum Foil

Notes: 12 in/min (300 mm/min)

90° Peel Adhesion

40 oz/in

View 

Test Method: ASTM D3330

Dwell/Cure Time: 72.0

Dwell Time Units: hr

Temp C: 23C

Temp F: 72F

Environmental Condition: 50%RH

Substrate: ABS

Backing: 2 mil Aluminum Foil

Notes: 12 in/min (300 mm/min)

90° Peel Adhesion

6.8 N/cm (62 oz/in)

View 

Test Method: ASTM D3330

Dwell/Cure Time: 72.0

Dwell Time Units: hr


Temp C: 23C

Temp F: 72F

Environmental Condition: 50%RH

Substrate: Polypropylene (PP)
Backing: 2 mil Aluminum Foil




Notes: 12 in/min (300 mm/min)

| | | |
|---|-----------------|--|
| 90° Peel Adhesion | 62 oz/in | View  |
| <p>Test Method: ASTM D3330</p> <p>Dwell/Cure Time: 72.0 Dwell Time Units: hr Temp C: 23C Temp F: 72F Environmental Condition: 50%RH Substrate: Polypropylene (PP) Backing: 2 mil Aluminum Foil</p> <p>Notes: 12 in/min (300 mm/min)</p> | | |
| Short Term Temperature Resistance | 250 °F (121 °C) | |
| Short Term Temperature Resistance | 121 °C | |
| Long Term Temperature Resistance | 70 °C (158 °F) | |
| Long Term Temperature Resistance | 158 °F | |

Available Sizes

48

Electrical and Thermal Properties

| Property | Values | Additional Information |
|--|---|--|
| Dielectric Constant 1KHz | 3.21 | View  |
| <p>Test Method: ASTM D150</p> <p>Temp C: 23C Temp F: 72F</p> | | |
| Dissipation Factor | 0.04 | |
| Dielectric Strength | 340 V/mil | View  |
| <p>Test Method: ASTM D149</p> | | |
| Coefficient of Thermal Expansion | 20 x 10 ⁻⁵ m/m/°C (58 x 10 ⁻⁵ m/m/°C) | View  |
| <p>Test Method: ASTM D696</p> | | |

Coefficient of Thermal Expansion

58 x 10⁻⁵ m/m/°CView 

Test Method: ASTM D696

Typical Environmental Performance

Humidity Resistance – High humidity has a minimal effect on adhesive performance. Bond strength (is generally higher/shows no significant reduction) after exposure for 7 days at 90°F (32°C) and 90% relative humidity.

UV Resistance – When properly applied, nameplates and decorative trim parts are not adversely affected by outdoor exposure.

Water Resistance – Immersion in water has no appreciable effect on the bond strength. After 100 hours at room temperature, the high bond strength (increases/is maintained).

Temperature Cycling Resistance – High bond strength (is maintained /increases) after cycling four times through:

4 hours at 158°F (70°C)

4 hours at -20°F (-29°C)

4 hours at 73°F (22°C)

Chemical Resistance – When properly applied, nameplate and decorative trim parts will hold securely after exposure to numerous chemicals including oil, mild acids and alkalis.

Bond Build-up: The bond strength of 3M™ Adhesive 300 increases as a function of time and temperature

Temperature/Heat Resistance: Adhesive 300 is usable for short periods (minutes, hours) at temperatures up to 250°F (120°C) and for intermittent longer periods (days, weeks) up to 150°F (65°C).

Lower Temperature Service Limit: -40F (-40°C).

Storage and Shelf Life

It is suggested that products are stored at room temperature conditions of 70°F (21°C) and 50% relative humidity.

If stored properly, product retains its performance and properties for 24 months from date of manufacture.

Industry Specifications

[EN 45545 test report for details \(ISO 5658-2, ISO 5660-1\)](#)

Recognition/Certification

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements

SDS: 3M has not prepared a SDS for this product which is not subjected to the SDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R.1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, this product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

UL: These products have been recognized by Underwriters Laboratories, Inc. under UL 969, Marking and Labeling Systems Materials Component. For more information on the UL Certification, please visit the website at <http://www.3M.com/converter>, select UL Recognized Materials, then select the specific product area.

Military: Meets Mil-P 19834B Type 1.

Note: One of 3M's core values is to respect our social and physical environment. 3M is committed to comply with ever-changing, global, regulatory and consumer environmental, health, and safety (EHS) requirements. As a service to our customers, 3M is providing information on the regulatory status of many 3M products. Further regulation information including that for OSHA, USCPSI, FDA, California Proposition 65, READY and RoHS, can be found at 3M.com/regs.

Bottom Matter

| Property | Values | Additional Information |
|--------------------------------|---|------------------------|
| Bottom Matter Logo and Address | 3M Industrial Adhesives & Tapes Division Converter Markets 3M Center, Building 225-3S-06 St. Paul, MN 55144-1000 800-223-7427 651-778-4244 (fax) www.3M.com | |
| Bottom Matter Images | [Image 4] | |

[Image 5]

Trademarks

3M is a trademark of 3M Company

Handling/Application Information

Application Examples

- Long term bonding of graphic nameplates and overlays to surfaces such as metal and low surface energy plastics in the aerospace, medical and industrial equipment, automotive, appliance and electronic markets.
- Bonding metal nameplates and rating plates in the aerospace, medical and industrial equipment, automotive, appliance and electronic markets.
- Lamination to foam for gasket application.

Application Techniques

For maximum bond strength (during installation of the final part) the surface should be thoroughly cleaned and dried. Typical cleaning solvents are heptane (for oily surfaces) or isopropyl alcohol for plastics. Use reagent grade solvents since common household materials like rubbing alcohol frequently contain oils to minimize the drying effect on skin. These oils can interfere with the performance of a pressure-sensitive adhesive.

Consult solvent manufacturers MSDS for proper handling and storage instructions. Also, use disposable wipes that do not contain oils, to remove the cleaning solvents.

It is necessary to provide pressure during lamination (1.5-20 PLI recommended) and during final part installation (10-15 PLI) to allow the adhesive to come into direct contact with the substrate. Using a hard edged plastic tool, which is the full width of the laminated part, helps to provide the necessary pressure at the point of lamination. Heat can increase bond strength when bonding to metal parts (generally this same increase is observed at room temperature over longer times, weeks). For plastic parts, the bond strength is not enhanced with the addition of heat.

The ideal adhesive application temperature range is 70°F (21°C) to 100°F (38°C). Application is not recommended if the surface temperature is below 50°F (10°C) because the adhesive becomes too firm to adhere readily. Once properly applied, at the recommended application temperature, low temperature holding is generally satisfactory (please refer to the Typical Physical Properties and Performance Characteristics section).

When bonding a thin, smooth, flexible material to a smooth surface, it is generally acceptable to use 2 mils of adhesive. If a texture is visible on one or both surfaces, the 5 mil adhesive would be suggested. If both materials are rigid, it may be necessary to use a thicker adhesive to successfully bond the components. 3M™ VHB™ Acrylic Foam Tapes may be required (please refer to data page 70-0709-3863-7).

Application Equipment

To apply adhesives in a wide web format, lamination equipment is required to ensure acceptable quality. To learn more about working with pressure-sensitive adhesives please refer to technical bulletin, Lamination Techniques for Converters of Laminating Adhesives (70-0704-1430-8).

For additional dispenser information, contact your local 3M sales representative, or the toll free 3M sales assistance number at 1-800-362-3550.

References

| Property | Values |
|-----------------------|---|
| 3m.com Product Page | https://www.3m.com/3M/en_US/company-us/all-3m-products/~//3M-Adhesive-Transfer-Tape-950/?N=5002385+3293241837&rt=rud |
| Safety Data Sheet SDS | https://www.3m.com/3M/en_US/company-us/SDS-search/results/?gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=950 |

Family Group

Link Tags:

• [927](#) • [950](#) • [950EK](#) • [9458](#) • [9471](#) • [9472](#) • [9671](#) • [9672](#) • [9459W](#)

| Products | Adhesive Type | Liner | Liner Thickness | Liner Color | Total Tape Thickness | Short Term Temperature Resistance | Long Term Temperature Resistance | Color |
|----------|----------------------------|---|-----------------|------------------------|----------------------|-----------------------------------|----------------------------------|-------|
| 950 | Acrylic | 58# Glassine paper | 0.08 mm | Tan, No Print | 0.13 mm | 121 °C | 158 °F | N/A |
| 9471 | Acrylic | 60# Densified Kraft, tan with green "3M" print | 0.09 mm | Tan, Green Print, "3M" | 0.05 mm | 121 °C | 158 °F | N/A |
| 9472 | Acrylic | 60# Densified Kraft, tan with green "3M" print | 0.09 mm | Tan, Green Print, "3M" | 0.13 mm | 121 °C | 158 °F | N/A |
| 950EK | Acrylic | 78# Extensible Kraft | 0.14 mm | White, No Print | 0.13 mm | 121 °C | 158 °F | N/A |
| 927 | Acrylic | 60# Densified Kraft | 0.09 mm | Tan, No Print | 0.05 mm | 121 °C | 158 °F | N/A |
| 9458 | Acrylic | 55# Densified Kraft | 0.08 mm | White, No Print | 0.025 mm | 121 °C | 158 °F | N/A |
| 9671 | Acrylic | 83# Polycoated Kraft, tan with green "3M" print | 0.16 mm | Tan, Green Print, "3M" | 0.05 mm | 121 °C | 158 °F | N/A |
| 9459W | #300 "Hi-Strength" Acrylic | 55# Densified Kraft | 0.08 mm | N/A | 0.0375 mm | 121 °C | 158 °F | White |
| 9672 | Acrylic | 83# Polycoated Kraft, tan with green "3M" print | 0.16 mm | Tan, Green Print, "3M" | 0.13 mm | 121 °C | 158 °F | N/A |

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.