



MASTER Value GLASS LED bulbs



MASTER VLE LEDBulb D7.8-75W E27 927 A60 FRG

Featuring a classic heritage design, classic filament LED lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. The product offers more energy saving compared with normal LED bulbs, and also provides the customer with a good light experience and superior dimming performance. MASTER Value Glass Led Bulbs deliver significant energy savings, offering 30% more compared to normal LEDs. They provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.


Product data

General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere
Light Technical	
Colour Code	927 [CCT of 2,700 K]
Luminous flux (nom.)	1055 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	135.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	90

LLMF at end of nominal lifetime (nom.) 70 %	
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7.8 W
Lamp current (nom.)	46 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C

MASTER Value GLASS LED bulbs

Photometric data




LEDbulb MAS A60 7,8W E27 927 FR-LDD

Lifetime



15K LED



15K LMP

