

# Neodymium Block Magnet



### Typical Applications

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp.
- High resistance to de-magnetisation
- Anisotropic
- N35 grade



| Eclipse Magnetics<br>Part Number | Description                              | Weight (g) | Pull Force (kg) |
|----------------------------------|------------------------------------------|------------|-----------------|
| N859                             | 25mm x 8mm x 3mm Neodymium block magnet  | 22.5       | 2.57            |
| N860                             | 10mm x 5mm x 2mm Neodymium block magnet  | 3.8        | 0.74            |
| N861                             | 10mm x 10mm x 5mm Neodymium block magnet | 19         | 2.57            |
| N862                             | 20mm x 10mm x 2mm Neodymium block magnet | 15.2       | 1.85            |
| N863                             | 20mm x 10mm x 5mm Neodymium block magnet | 38         | 5               |