

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name

edding paint marker ink (other colors) contained in: edding 790, edding 791

1.2 Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture

Ink for use in felt pens

Uses advised against

No data available.

1.3 Details of the supplier of the safety data sheet

Address

edding International GmbH

Bookkoppel 7

D-22926 Ahrensburg

Telephone no. +49 (0) 41 02 / 80 8-0

Information provided by / telephone

+49 (0)4102 - 808-0

Advice on Safety Data Sheet

sdb_info@umco.de

1.4 Emergency telephone number

For medical advice (in German and English):

+49 (0)30 30686 790 (Giftnotruf Berlin)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification in accordance with Regulation (EC) No 1272/2008 (CLP)

Flam. Liq. 3; H226

STOT SE 3; H336

Classification information

This product is assessed and classified using the methods and criteria below referred to in Article 9 of Regulation (EC) n° 1272/2008:

Physical hazards: determined through assessment data based on the methods or standards referred to in part 2 of Annex I to CLP

Health hazards and environmental hazards: determined through toxicological and ecotoxicological assessment data based on the methods or standards referred to in Part 3, 4 and 5 of Annex I to CLP.

2.2 Label elements

Labelling according to Regulation (EC) No 1272/2008 (CLP Regulation)

Hazard pictograms



GHS02



GHS07

Signal word

Warning

Hazardous component(s) to be indicated on label:

1-methoxy-2-propanol

Hazard statement(s)

H226

Flammable liquid and vapour.

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

H336	May cause drowsiness or dizziness.
Precautionary statement(s)	
P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P271	Use only outdoors or in a well-ventilated area.
P370+P378	In case of fire: Use water spray, extinguishing powder, foam or CO2 to extinguish.
P405	Store locked up.
P501	Dispose of contents/container to a facility in accordance with local and national regulations.

2.3 Other hazards

No data available.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable. The product is not a substance.

3.2 Mixtures

Chemical characterization

Solution of dyes and resins in organic solvents

Hazardous ingredients

No	Substance name	Additional information	
	CAS / EC / Index / REACH no	Classification (EC) 1272/2008 (CLP)	Concentration %
1	1-methoxy-2-propanol		
	107-98-2 203-539-1 603-064-00-3 -	Flam. Liq. 3; H226 STOT SE 3; H336	>= 50.00 - < 90.00 wt%

Full Text for all H-phrases and EUH-phrases: pls. see section 16

3.3 Other information

The data subject of this Material Safety Data sheet refer to the ink contained in this product (marker).

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

In case of persisting adverse effects, consult a physician. Remove contaminated clothing and shoes immediately, and launder thoroughly before reusing.

After inhalation

Ensure supply of fresh air. Remove affected person from the immediate area.

After skin contact

Wash off immediately with soap and water.

After eye contact

Remove contact lenses. Rinse eye thoroughly under running water keeping eyelids wide open and protecting the unaffected eye (at least 10 to 15 minutes). Seek medical assistance.

After ingestion

Rinse the mouth thoroughly with water. Seek medical advice immediately. Do not induce vomiting. Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

No data available.

4.3 Indication of any immediate medical attention and special treatment needed

No data available.

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

Foam; Extinguishing powder; Carbon dioxide; Water spray jet

Unsuitable extinguishing media

High power water jet

5.2 Special hazards arising from the substance or mixture

In the event of fire, the following can be released: Carbon dioxide (CO₂); Carbon monoxide (CO)

5.3 Advice for firefighters

Cool endangered containers with water spray jet. Use self-contained breathing apparatus. Wear protective clothing.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Refer to protective measures listed in sections 7 and 8. Avoid contact with skin, eyes and clothing. Ensure adequate ventilation. Keep away from ignition sources.

For emergency responders

No data available. Personal protective equipment (PPE) - see Section 8.

6.2 Environmental precautions

Do not discharge into the drains/surface waters/groundwater. Do not discharge into the subsoil/soil.

6.3 Methods and material for containment and cleaning up

Take up with absorbent material (e.g., sand, kieselguhr, universal binder). When collected, handle material as described under the section heading "Disposal considerations".

6.4 Reference to other sections

No data available.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling

Provide good ventilation at the work area (local exhaust ventilation, if necessary). If workplace exposure limits are exceeded, respiratory protection approved for this particular job must be worn. Risks inherent to handling the product must be minimised by applying the appropriate protective and preventive measures. Working processes should - so far as possible, according to the state of the art - be designed to rule out bodily contact or the release of hazardous substances.

General protective and hygiene measures

Keep away from foodstuffs and beverages. Avoid contact with eyes and skin. Remove soiled or soaked clothing immediately. Do not inhale vapours.

Advice on protection against fire and explosion

Vapours can form an explosive mixture with air. Take precautionary measures against static charges. Keep away from sources of heat and ignition.

7.2 Conditions for safe storage, including any incompatibilities

Technical measures and storage conditions

Keep container tightly closed and dry in a cool, well-ventilated place. Protect from heat and direct sunlight.

Requirements for storage rooms and vessels

Containers which are opened must be carefully closed and kept upright to prevent leakage.

Incompatible products

Do not store together with: oxidizing agents

7.3 Specific end use(s)

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

No data available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limit values

No	Substance name	CAS no.	EC no.
1	1-methoxy-2-propanol	107-98-2	203-539-1
	2000/39/EC		
	1-Methoxypropanol-2		
	WEL short-term (15 min reference period)	568 mg/m ³	150 ppm
	WEL long-term (8-hr TWA reference period)	375 mg/m ³	100 ppm
	Skin resorption / sensibilisation	Skin	
	List of approved workplace exposure limits (WELs) / EH40		
	1-Methoxypropan-2-ol		
	WEL short-term (15 min reference period)	560 mg/m ³	150 ppm
	WEL long-term (8-hr TWA reference period)	375 mg/m ³	100 ppm
	Comments	Sk	

8.2 Exposure controls

Appropriate engineering controls

No data available.

Personal protective equipment

Respiratory protection

If workplace exposure limits are exceeded, a respiration protection approved for this particular job must be worn. In case of aerosol and mist formation, take appropriate measures for breathing protection in the event workplace threshold values are not specified.

Respiratory filter (gas) : A

Eye / face protection

Safety glasses (EN 166)

Hand protection

In case of intensive contact, wear protective gloves (EN 374). Before use, the protective gloves should be tested in any case for its specific work-station suitability (i.e. mechanical resistance, product compatibility and antistatic properties). Adhere to the manufacturer's instructions and information relating to the use, storage, care and replacement of protective gloves. Protective gloves shall be replaced immediately when physically damaged or worn. Design operations thus to avoid permanent use of protective gloves.

Appropriate Material butyl rubber

Material thickness 0.5 mm

Breakthrough time > 480 min

Other

Normal chemical work clothing.

Environmental exposure controls

No data available.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

State of aggregation
liquid
Form/Colour
liquid
various
Odour
ether-like

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

pH value			
No data available			
Boiling point / boiling range			
Value	appr.	120	°C
Melting point/freezing point			
No data available			
Decomposition temperature			
No data available			
Flash point			
Value		31	°C
Method	DIN EN 456		
Ignition temperature			
Value	>	250	°C
Source	Literature value		
Flammability			
No data available			
Lower explosion limit			
Value		1.7	% vol
Upper explosion limit			
Value		11.5	% vol
Vapour pressure			
Value		12	mbar
Reference temperature		20	°C
Relative vapour density			
No data available			
Relative density			
No data available			
Density			
Value	0.9	- 1.3	g/cm³
Reference temperature		20	°C
Solubility in water			
Comments	partially miscible		
Solubility			
No data available			
Partition coefficient n-octanol/water (log value)			
No data available			
Viscosity			
Value	appr.	30	sec
Method	DIN cup 3 mm		
Solvent content			
Value	<	82	%
Particle characteristics			
No data available			

9.2 Other information

Other information			
No data available.			

SECTION 10: Stability and reactivity

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

10.1 Reactivity

No data available.

10.2 Chemical stability

Stable under recommended storage and handling conditions (See section 7).

10.3 Possibility of hazardous reactions

None, when used as directed.

10.4 Conditions to avoid

Heat, naked flames and other ignition sources.

10.5 Incompatible materials

Oxidizing agents

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information
11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity			
No	Substance name	CAS no.	EC no.
1	1-methoxy-2-propanol	107-98-2	203-539-1
LD50		5660	mg/kg bodyweight
Species	rat		
Source	Manufacturer		

Acute dermal toxicity			
No	Substance name	CAS no.	EC no.
1	1-methoxy-2-propanol	107-98-2	203-539-1
LD50		9999.99	mg/kg bodyweight
Species	rabbit		
Source	Manufacturer		

Acute inhalational toxicity			
No data available			

Skin corrosion/irritation			
No data available			

Serious eye damage/irritation			
No data available			

Respiratory or skin sensitisation			
No data available			

Germ cell mutagenicity			
No data available			

Reproduction toxicity			
No data available			

Carcinogenicity			
No data available			

STOT - single exposure			
No data available			

STOT - repeated exposure			
No data available			

Aspiration hazard			
No data available			

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Inhalation of solvent vapours in higher concentration may lead to nausea, headache, drowsiness and dizziness.
Repeated and prolonged skin contact may cause removal of natural fat from the skin and irritation of the skin.

11.2 Information on other hazards

Endocrine disrupting properties

No data available.

Other information

No data available.

SECTION 12: Ecological information

12.1 Toxicity

Toxicity to fish (acute)

No data available

Toxicity to fish (chronic)

No data available

Toxicity to Daphnia (acute)

No data available

Toxicity to Daphnia (chronic)

No data available

Toxicity to algae (acute)

No data available

Toxicity to algae (chronic)

No data available

Bacteria toxicity

No data available

12.2 Persistence and degradability

No data available.

12.3 Bioaccumulative potential

No data available.

12.4 Mobility in soil

No data available.

12.5 Results of PBT and vPvB assessment

No data available.

12.6 Endocrine disrupting properties

No data available.

12.7 Other adverse effects

No data available.

12.8 Other information

Other information

Do not discharge product unmonitored into the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Allocation of a waste code number, according to the European Waste Catalogue, should be carried out in agreement with the regional waste disposal company.

Packaging

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791

Current version : 3.1.2, issued: 14.12.2021

Replaced version: 3.1.2, issued: 15.09.2021

Region: GB

Residues must be removed from packaging and when emptied completely disposed of in accordance with the regulations for waste removal. Incompletely emptied packaging must be disposed of in the form of disposal specified by the regional disposer.

SECTION 14: Transport information

14.1 Transport ADR/RID/ADN

Class	3
Classification code	F1
Packing group	III
Hazard identification no.	30
UN number	UN1263
Proper shipping name	PAINT
Tunnel restriction code	D/E
Label	3

14.2 Transport IMDG

Class	3
Packing group	III
UN number	UN1263
Proper shipping name	PAINT
EmS	F-E, S-E
Label	3

14.3 Transport ICAO-TI / IATA

Class	3
Packing group	III
UN number	UN1263
Proper shipping name	Paint
Label	3

14.4 Other information

No data available.

14.5 Environmental hazards

Information on environmental hazards, if relevant, please see 14.1 - 14.3.

14.6 Special precautions for user

No data available.

14.7 Maritime transport in bulk according to IMO instruments

Not relevant

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU regulations

Regulation (EC) No 1907/2006 (REACH) Annex XIV (List of substances subject to authorisation)

According to the data available and/or specifications supplied by upstream suppliers, this product does not contain any substances considered as substances requiring authorisation as listed on Annex XIV of the REACH regulation (EC) 1907/2006.

REACH candidate list of substances of very high concern (SVHC) for authorisation

According to available data and the information provided by preliminary suppliers, the product does not contain substances that are considered substances meeting the criteria for inclusion in annex XIV (List of Substances Subject to Authorisation) as laid down in Article 57 and article 59 of REACH (EC) 1907/2006.

Regulation (EC) No 1907/2006 (REACH) Annex XVII: RESTRICTIONS ON THE MANUFACTURE, PLACING ON THE MARKET AND USE OF CERTAIN DANGEROUS SUBSTANCES, MIXTURES AND ARTICLES

The product is considered being subject to REACH regulation (EC) 1907/2006 annex XVII.	No 3, 40
--	----------

Trade name: edding paint marker ink (other colors) contained in: edding 790, edding 791**Current version :** 3.1.2, issued: 14.12.2021**Replaced version:** 3.1.2, issued: 15.09.2021**Region:** GB**Directive 2012/18/EU on the control of major-accident hazards involving dangerous substances**

This product is subject to Part I of Annex I, risk category: P5c

Directive 2010/75/EU on industrial emissions (integrated pollution prevention and control)

VOC content <82 %

15.2 Chemical safety assessment

A chemical safety assessment has not been carried out for this mixture.

SECTION 16: Other information**Sources of key data used to compile the data sheet:**

Regulation (EC) No 1907/2006 (REACH), 1272/2008 (CLP) as amended in each case.

Directives 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164.

National Threshold Limit Values of the corresponding countries as amended in each case.

Transport regulations according to ADR, RID, IMDG, IATA as amended in each case.

The data sources used to determine physical, toxic and ecotoxic data, are indicated directly in the corresponding section.

Creation of the safety data sheet

UMCO GmbH

Georg-Wilhelm-Str. 187, D-21107 Hamburg

Tel.: +49 40 / 555 546 300 Fax: +49 40 / 555 546 357 e-mail: umco@umco.de

This information is based on our present knowledge and experience.

The safety data sheet describes products with a view to safety requirements.

It does not however, constitute a guarantee for any specific product properties and shall not establish a legally valid contractual relationship.

Document protected by copyright. Alterations or reproductions require the express written permission of UMCO GmbH.

Prod-ID 19418