



## 3M™ Dual Lock™ Reclosable Fastener SJ387B, Black, 25 mm x 2.5 m, 6.1 mm, Blister

Part Number: SJ387B, Black, 2.5M X 25MM, 3M ID 7100123347

### Product Overview:

- Black fastener with mushroom shaped stems, backed with a modified acrylic pressure sensitive adhesive
- Type 250 mates to Type 170, 250 or 400. Closes with an audible snap
- Five times the tensile strength of typical hook-and-loop fasteners
- Opens and closes 1000 times before losing 50% of its original tensile strength.



### Details:

- Black fastener with mushroom shaped stems, backed with a modified acrylic pressure sensitive adhesive
- Type 250 mates to Type 170, 250 or 400. Closes with an audible snap
- Five times the tensile strength of typical hook-and-loop fasteners
- Opens and closes 1000 times before losing 50% of its original tensile strength
- Modified acrylic adhesive bonds to many plastics, powder coated paints, and medium to low surface energy materials
- Ideal for indoor and outdoor use to attach doors, flexible solar panels, headliners, access panels, signs and display components

3M™ Dual Lock™ Reclosable Fastener SJ3870 is the convenient alternative to traditional fastening methods, such as screws, nuts or bolts. It is designed to deliver a durable, reclosable fastening solution (which can be opened and closed multiple times) that bonds to a variety of substrates including metals, powder-coated paints and plastics such as acrylics, polycarbonate and ABS.

The 3M™ Dual Lock™ Reclosable Fastener SJ3870 has a modified acrylic adhesive on the back of a black polypropylene reclosable fastener. This product can be used both indoors and outside in a variety of applications; and has a slim 0.24" engaged thickness and long service life. • Snap-in-place installation replaces screws, nails, snaps and rivets • Black fastener is hidden when closed, providing a clean, smooth appearance • Modified acrylic adhesive bonds to many plastics, powder coated paints and medium to low surface energy materials with little or no surface preparation • Ideal for indoor and outdoor use to attach doors, flexible solar panels, headliners, access panels, signs and display components • Medium temperature resistance – up to 60°C • 10 times stronger than traditional hook and cord attachments • Can be opened and closed again up to 1000 times

## Suggested Applications:

- Panel and cover plate attachment
- Interior signage
- Decorative trim
- Office partitions
- Graphic attachment
- Access panels
- Specialty vehicles (interior attachments)
- L-bracket edging, repositionable shelving
- Hang signage.