Phono Sockets

pro-**signal**





PSG08302


PSG08303

PSG08305

Specifications

No. of Contacts	: 2 Contacts
Gender	: Socket
Contact Resistance	: 50mΩ Max.
Insertion Force	: 30N Max.
Extraction Force	: 3~30N
Rating	: 12V DC, 1A
Insulation Resistance	: 100M Ω Min. at 500V DC
Dielectric Strength	: 250V AC for one Minute

Diagram



No.	Part Name	Material	Finish	Qty
1	Body	BSBM	Au	
2	Insulator A	ABS	-	
3	Insulator B	ABS	-	
4	Contact	BSR	Au	1
5	Ring	ABS	-	
6	Washer	Steel t=0.5	Ni	
7	Terminal	Steel t=0.4	Ni	
8	Hex, Nut	BSBM	Ni	

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-SIGNAL is the registered trademark of Premier Farnell Limited 2019.

Part Number Table

Description

Phono Socket, Black / Gold Phono Socket, Red / Gold

Phono Socket, White / Gold

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



Part Number

PSG08302

PSG08303

PSG08305