

Product information

34 12 130

Precision Electronics Gripping Pliers

DIN ISO 9655



- For very precise assembly work, e.g. in electronics and fine mechanics
- For gripping, holding and bending
- Smoothly ground gripping surfaces, edges finely rounded
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint and carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Flat, wide jaws
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

Article No.	34 12 130
EAN	4003773061458
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	61 g
Dimensions	135 x 62 x 19 mm
Standard	DIN ISO 9655
Reach	no
RohS	no

Technical details

Jaw length (B)	21.9 mm
Jaw thickness (joint) (D)	6.5 mm
Tips width (E)	1.4 mm
Tips thickness (F)	3.5 mm
Head width (A)	11.2 mm



Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAA840c015
UNSPSC 13.1	27112149

technical change and errors excepted

