

Product information

78 06 125

Electronic Super Knips® VDE

DIN ISO 9654 IEC 60900 DIN EN 60900



For ultra-fine work up to 1000 V: precision cutter with more performance and VDE-tested safety

- VDE-tested precision pliers for ultra fine cutting work, e.g. in electronics and fine mechanics
- Complete your set of VDE-tools
- Ground, very sharp cutting edges without bevel
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Precisely shaped tips cut wires close to a surface from Ø 0.2 mm
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Cutting edge hardness approx. 54 HRC
- Made of INOX tool steel




General

Article No.	78 06 125
EAN	4003773084099
Head	polished
Handles	insulated with multi-component grips, VDE-tested
Weight	60 g
Dimensions	125 x 78 x 18 mm
Standard	DIN ISO 9654 DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
Jaw length (B)	9 mm
Jaw thickness (joint) (D)	7.5 mm
Head width (A)	13.5 mm



Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004

technical change and errors excepted



For use on live parts of up to 1000 V



