



Product: [TT-SDK-024-LIN](#)

Transit, In+Outdoor, DN, OS2, 24f, Unitized, AIA, Dbl Jkt - LSZH, OFCR-ST1

Product Description

Transit Grade, Indoor/Outdoor, Distribution, OS2, 24 Fibers, Unitized (12f/unit) 900um, Aluminum Interlock Armor, Double Jacket - LSZH, OFCR-ST1

Technical Specifications

Product Overview

|                        |                                                                                                                             |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Product Category:      | Fiber Distribution Cable                                                                                                    |
| Suitable Applications: | Extended Distance Horizontal & Backbone Data/Telco Network, Noisy Environment, Indoor/Outdoor & Wet Locations, Rodent Proof |

Fiber Specifications

|                      |                               |
|----------------------|-------------------------------|
| Fiber Type:          | OS2                           |
| Fiber Core Diameter: | 8.2/125 µm                    |
| Fiber Diameter:      | 250 µm                        |
| Buffer Material:     | LSZH - Low Smoke Zero Halogen |
| Buffer Diameter:     | 900 µm                        |
| Fiber Count:         | 24                            |
| Fiber Color Coding:  | TIA-598-D                     |

Cable Construction

|                            |                           |
|----------------------------|---------------------------|
| Number of Active Subunits: | 2                         |
| Number of Fillers:         | 2                         |
| Fibers Per Subunit:        | 12                        |
| Subunit Diameter:          | 0.230 in (5.8 mm)         |
| Subunit Color:             | Yellow                    |
| Subunit Strength Members:  | Waterblocking Aramid Yarn |
| Central Strength Member:   | Upjacketed GRP            |
| Core Wrap:                 | Waterblocking Tape        |

Inner Jacket Specifications

|                     |                                                 |
|---------------------|-------------------------------------------------|
| Strength Member:    | Waterblocking Aramid Yarns                      |
| Material:           | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter:      | 0.688 in (17.5 mm)                              |
| Color:              | Black                                           |
| Number of Ripcords: | 1                                               |

Armor Specifications

|                          |                                |
|--------------------------|--------------------------------|
| Armor Type and Material: | AIA - Aluminum Interlock Armor |
|--------------------------|--------------------------------|

Outer Jacket Specifications

|                |                                                 |
|----------------|-------------------------------------------------|
| Material:      | LSZH - Low Smoke Zero Halogen (Flame Retardant) |
| Nom. Diameter: | 1.100 in (27.9 mm)                              |

Optical Characteristics

| Wavelength                      | 1310 nm    | 1550 nm    |
|---------------------------------|------------|------------|
| Max. Attenuation                | 0.50 dB/km | 0.50 dB/km |
| Mode Field Diameter             | 9.2 µm     | 10.4 µm    |
| 1 Gigabit Ethernet Performance  | 5,000 m    | -          |
| 10 Gigabit Ethernet Performance | 10,000 m   | 40,000 m   |

Mechanical Characteristics

|                                            |                         |
|--------------------------------------------|-------------------------|
| Min. Bend Radius During Installation:      | 20x Cable OD            |
| Min. Bend Radius During Operation:         | 10x Cable OD            |
| Max. Tensile Strength During Installation: | 1335 N (300 lbf)        |
| Max. Tensile Strength During Operation:    | 400 N (90 lbf)          |
| Crush Resistance:                          | 440 N/cm                |
| Bulk Cable Weight:                         | 398 lbs/kft (592 kg/km) |

Temperature Range

|                          |                |
|--------------------------|----------------|
| Installation Temp Range: | -10°C to +60°C |
| Operating Temp Range:    | -40°C to +70°C |
| Storage Temp Range:      | -40°C to +70°C |

Standards and Compliance

|                                  |                                             |
|----------------------------------|---------------------------------------------|
| Environmental Suitability:       | Indoor/Outdoor, Sunlight Resistance, Burial |
| Sustainability:                  | CA Prop 65                                  |
| Flammability / Reaction to Fire: | OFCR-ST1, FT4                               |
| ICEA Compliance:                 | S-104-696                                   |
| Other Standard Compliance(s):    | NFPA 130, NFPA 502                          |

History

|                      |                                                 |
|----------------------|-------------------------------------------------|
| Update and Revision: | Revision Number: 0.22 Revision Date: 12-15-2021 |
|----------------------|-------------------------------------------------|

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.