

产品名称: 6V 2.2kg 数码舵机  
Product Name: 6V 2.2kg.cm Digital Servo

产品型号 Model No. FS90MG-CL

### 1. 使用环境条件 Apply Environmental Condition

No.	Item	Specification
1-1	存储温度 Storage Temperature Range	-30°C~80°C
1-2	运行温度 Operating Temperature Range	-15°C~70°C

### 2. 测试环境 Standard Test Environment

No.	Item	Specification
2-1	温度 Temperature range	25°C ±5°C
2-2	湿度 Humidity range	65%±10%

### 3. 机械特性 Mechanical Specification

No.	Item	Specification
3-1	尺寸 Size	A: 22.5mm B: 12.1mm C: 26.7mm
3-2	重量 Weight	12.5g
3-3	齿轮类型 Gear type	Metal Gear
3-6	机构极限角度 Limit angle	180degree
3-7	轴承 Bearing	NO Ball bearings
3-8	出力轴 Horn gear spline	21T
3-9	摆臂 Horn type	Plastic, POM
3-10	外壳 Case	ABS
3-11	舵机线 Connector wire	250mm+aligator clips(Custom Made)
3-12	马达 Motor	Metal brush motor
3-13	防水性能 Splash water resistance	NO

### 4. 电气特性 Electrical Specification (Function of the Performance)

No.	工作电压 Operating Voltage Range	4.8V	6V
4-1*	静态电流 Idle current(at stopped)	5mA	6mA
4-2*	空载速度 No load speed	0.10sec/60degree	0.09sec/60degree
4-3*	空载电流 Runnig current(at no load)	190 mA	220mA
4-4	堵转扭矩 Peak stall torque	1.8kg.cm	2.2kg.cm
		25.04oz.in	30.6oz.in
4-5	堵转电流 Stall current	700 mA	800mA

Note: "\*"definition is average value when the servo runing with no load

# 产品规格书

## Specification of Product

V1.0 Page 2/2

产品名称: 6V 2.2kg 数码舵机  
Product Name: 6V 2.2kg.cm Digital Servo

产品型号 Model No. FS90MG-CL

### 5. 控制特性 Control Specification:

No.	Item	Specification
5-1	控制信号 Command signal	Pulse width modification
5-2	放大器类型 Amplifier type	Digital comparator
5-3	脉冲宽度范围 Pulse width range	500~2500μsec
5-4	中立位置 Neutral position	1500μsec
5-5	旋转角度 Running degree	180° (when 500~2500 μ sec)
5-6	死区宽度 Dead band width	8 μsec
5-7	旋转方向 Rotating direction	CW(when 1500~900 μsec) CCW(when 1500~2100 μsec)