

Product information

97 43 200

Crimp System Pliers

For exchangeable crimping dies



- Comes in a plastic case; foam insert with recesses for crimping dies and locators; with service tool (Allen key), screws and nuts
- Without crimping dies
- Just one tool for almost 1000 crimping applications
- Almost parallel crimping motion
- Consistently high crimping quality thanks to precision dies and forced locking mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Ergonomically designed handles
- Different locators for precise positioning of the connectors
- Crimping dies for applications not covered in the range offered here, may be available on request
- Chrome vanadium electric steel in special quality, oil-hardened

MM

General	
Article No.	97 43 200
EAN	4003773030812
Pliers	burnished
Handles	with multi-component grips
Weight	988 g
Dimensions	200 x 220 x 50 mm
Reach	yes
RohS	no
Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147
Accessories	
97 49 04	Crimping die for non-insulated open plug-type connectors 2.8 + 4.8 mm,
97 49 05	Crimping die for non-insulated open plug-type connectors 4.8 + 6.3 mm,
97 49 06	Crimping die for insulated terminals + plug connectors,
97 49 08	Crimping die for insulated and non-insulated wire ferrules,
97 49 09	Crimping die for wire ferrules,

Accessories	
97 49 10	Crimping die for non-insulated tubular cable lugs and crimp terminals and non-insulated butt and crimp connectors in accordance with DIN 46341,
97 49 11	Crimping die for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267,
97 49 14	Crimping die for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267,
97 49 15	Crimping die for plug connectors and non-insulated open plug-type connectors,
97 49 16	Crimping die for insulated terminals + plug connectors,
97 49 18	Crimping die for twin wire ferrules,
97 49 19	Crimping die for wire ferrules,
97 49 20	Crimping die for F-connectors for TV and satellite connections,
97 49 23	Crimping die for non-insulated terminals + cable connectors,
97 49 24	Crimping die for D-Sub-plugs,
97 49 30	Crimping die for non-insulated butt connectors,
	Crimping die for non-insulated butt connectors,
97 49 35	Crimping die for spark plug connectors and distributors,
97 49 40	Crimping die for coax connectors,
97 49 44	Crimping die Phoenix contact module connector,
97 49 50	Crimping die for coax connectors / car phone,
97 49 54	Crimping die for Junior Power Timer,
97 49 60	Crimping die for turned contacts (HTS + Harting),
97 49 61	Crimping die for turned contacts (Harting),
97 49 62	Crimping die for solar cable connectors (Huber + Suhner),
97 49 63	Crimping die for solar cable connectors (Huber + Suhner),
97 49 64	Crimping die for ABS connectors,
97 49 65	Crimping die for solar cable connectors MC3 (Multi-Contact),
97 49 66	Crimping die for solar cable connectors MC4 (Multi-Contact),
97 49 67	Crimping die for solar cable connectors SunCon (Hirschmann),
97 49 68	Crimping die Solar cable connectors (Tyco),
97 49 70	Crimping die for Western plugs,
97 49 71	Crimping die for solar cable connectors MC4 (Multi-Contact),
97 49 74	Crimping die for unshielded Molex plugs,
97 49 76	Crimping die for shielded Stewart plugs,
97 49 81	Crimping die for Harting connectors for fibre optics,
97 49 82	Crimping die for Telegärtner connectors for fibre optics,
97 49 83	Crimping die for FSMA, ST, SC, STSC/K connectors,
97 49 84	Crimping die for Huber/Suhner connectors for fibre optics,
97 49 87	Crimping die for FSMA, ST and MIC connectors for fibre optics,
97 49 65 1	Locator for 97 49 65 (solar cable connectors MC3),
97 49 66 1	Locator for 97 49 66 (solar cable connectors MC4),

Accessories

97 49 68 1	Locator for 97 49 68 (solar cable connectors Solarlok),
97 49 90	Locator for 97 49 60 (HTS+Harting),
97 49 93	Locator for 97 49 24 (D-Sub-plugs),
97 49 94	Locator for 97 49 04,
97 49 95	Locator for 97 49 05 ,
97 49 91	Locator for 97 49 61 (Harting),
97 49 13	Crimping die for non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267,
97 49 06 PI	Crimping die for insulated PIDG connectors,
97 49 21	Crimping die for insulated and non-insulated connectors,

technical change and errors excepted





