

## MIGHTY M-CLASS INDUSTRIAL DUST EXTRACTOR – Due to high demand, the Original, Robust M Class Vac is back on site!



CLASS



HEPA 99.99% EFFICIENCY



WET & DRY



240 VOLT



110 VOLT



TWIN TURBINE

### ACCESSORIES INCLUDED

1. 3 METRE HEAVY DUTY YELLOW 32MM HOSE
2. 32MM STAINLESS STEEL TUBES & ELBOW
3. 420MM WIDE WET & DRY FLOOR HEAD
4. 10 X LARGE DUST BAGS
5. 32MM ROUND BRUSH
6. 32MM HIGH VOLUME CREVICE TOOL
7. 32MM UPHOLSTERY TOOL WITH BRUSH
8. H CLASS HEPA ESSENTIAL FILTER
9. UNIVERSAL POWER TOOL ADAPTER



### WHY BUY?

- ✓ HIGH LEVEL OF PROTECTION AGAINST HARMFUL DUST
- ✓ NON-MARKING WHEELS
- ✓ 1250W INDUSTRIAL, BYPASS, TWIN-TURBINE MOTOR
- ✓ WASHABLE FILTERS
- ✓ AFFORDABLE COMPLIANCE AND PROTECTION
- ✓ EXTRACTION VELOCITY MONITOR
- ✓ ROBUST AND EASY TO CLEAN POLYPROPYLENE DESIGN
- ✓ H13 HEPA FILTER: (99.9% FILTRATION EFFICIENCY)

### SPECIFICATION

M CLASS (H13) 99.99% HEPA FILTRATION  
 MOTOR POWER: 1250W INDUSTRIAL WITH TWIN TURBINE BYPASS  
 VOLTAGE: 110 & 240 VOLTAGE – 50/60Hz  
 AIR FLOW: 72 L/SEC (250 cbm/HOUR)  
 EXTRACTION VELOCITY MONITOR  
 SUCTION: 250 mbar  
 TANK SIZE: 21 LITRES. (BAG CAPACITY 18 LITRES)  
 WEIGHT: NETT: 8kg (GROSS: 23kg PACKAGE WEIGHT)  
 OPERATING NOISE LEVEL (DB9A): 58  
 CABLE LENGTH: 3m  
 DIMENSIONS (H x W x D): MACHINE: 56 x 41 x 38cm  
 (PACKAGE: 58 x 41 x 40cm)

Item No.	Description
MIGHTY240	M-CLASS INDUSTRIAL DUST EXTRACTOR 240V
MIGHTY110	M-CLASS INDUSTRIAL DUST EXTRACTOR 110V



V-TUF.CO.UK  
 T +44(0) 1522 51 57 67  
 E ENQUIRIES@V-TUF.COM

**V-TUF**  
 COMBAT DUST