

Product information

97 53 04

Self-Adjusting Crimping Pliers for wire ferrules

With lateral access



- Narrow handle width and improved ergonomics
- Square compression now for wire ferrules up to 16 mm²
- Square compression for ideal contact surfaces in the clamp connection
- Suitable in particular for all twin wire ferrules up to 2 x 4 mm² or 2 x AWG 12
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjustment to the size of wire ferrules required
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened



General	
Article No.	97 53 04
EAN	4003773028017
Pliers	burnished
Handles	with multi-component grips
Weight	459 g
Dimensions	180 x 77 x 21 mm
Reach	yes
RohS	no

Technical details	
	
Applications	Wire ferrules
Capacity in square millimetres	0.08 — 10 / 16 mm ²
Number of crimping positions	1
AWG	28 — 6

Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Spare Parts	
97 59 30	Extension spring for 97 53 4/5/8/9/14, thin (Handle)
97 59 31	Extension spring for 97 53 4/5/8/9/14, thick (Head)

Spare Parts

97 59 32

Circlips for model 97 53 for 97 53 XX,

technical change and errors excepted



Crimping capacity can be switched over simply from 10 mm² to 16 mm².