



Digital monitoring relay Current monitoring, 22.5 mm from 0.05-10 A AC/DC  
Overshoot and undershoot 24 to 240 V AC/DC 50 to 60 Hz DC and AC ON  
delay and noise pulses delay 0.1 to 20 s Hysteresis 0.01 to 5 A 1 change-  
over contact with or without fault buffer screw terminal Successor product  
for 3UG3522-1AL20, 3UG3522-1AG20 and 3UG3522-1AC48-0AA1

<b>product brand name</b>	SIRIUS
<b>product designation</b>	Current monitoring relay with digital setting
<b>product type designation</b>	3UG4
<b>General technical data</b>	
<b>product function</b>	Current monitoring relay
<b>design of the display</b>	LCD
insulation voltage for overvoltage category III according to IEC 60664	
• with degree of pollution 3 rated value	690 V
<b>degree of pollution</b>	3
<b>surge voltage resistance rated value</b>	4 kV
<b>maximum permissible voltage for safe isolation</b>	
• between auxiliary and auxiliary circuit	300 V
• between control and auxiliary circuit	300 V
<b>protection class IP</b>	IP20
shock resistance acc. to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance acc. to IEC 60068-2-6	1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
mechanical service life (switching cycles) typical	10 000 000
electrical endurance (switching cycles) at AC-15 at 230 V typical	100 000
<b>thermal current of the switching element with contacts maximum</b>	5 A
<b>reference code acc. to IEC 81346-2</b>	K
<b>relative repeat accuracy</b>	1 %
<b>Substance Prohibitance (Date)</b>	01.05.2012
<b>Product Function</b>	
<b>product function</b>	
• overcurrent detection 1 phase	Yes
• overcurrent detection 3 phase	No
• undercurrent detection 1 phase	Yes
• undercurrent detection 3 phases	No
• overcurrent detection DC	Yes
• undercurrent detection DC	Yes
• current window recognition DC	Yes
• voltage window recognition 1 phase	No
• voltage window recognition 3 phase	No
• adjustable open/closed-circuit current principle	Yes
• external reset	Yes
• auto-RESET	Yes
<b>Supply voltage</b>	

<b>type of voltage of the supply voltage</b>	AC/DC
<b>supply voltage 1 at AC</b>	
• at 50 Hz	20.4 ... 264 V
• at 60 Hz	20.4 ... 264 V
<b>supply voltage 1 at DC</b>	20.4 ... 264 V
<b>Measuring circuit</b>	
<b>type of current for monitoring</b>	AC/DC
<b>measurable current</b>	0.05 ... 15 A
<b>measurable line frequency</b>	40 ... 500 Hz
<b>adjustable current response value current</b>	
• 1	0.05 ... 10 A
• 2	0.05 ... 10 A
<b>adjustable response delay time</b>	
• when starting	0.1 ... 20 s
• with lower or upper limit violation	0.1 ... 20 s
<b>adjustable switching hysteresis for measured current value</b>	10 ... 5 000 mA
<b>buffering time in the event of power failure minimum</b>	10 ms
<b>accuracy of digital display</b>	+/-1 digit
<b>relative temperature-related measurement deviation</b>	5 %
<b>internal resistance of the measuring circuit</b>	5 mΩ
<b>Precision</b>	
<b>relative metering precision</b>	5 %
<b>temperature drift per °C</b>	0.1 %/°C
<b>Auxiliary circuit</b>	
number of NC contacts delayed switching	0
number of NO contacts delayed switching	0
number of CO contacts delayed switching	1
<b>operating frequency with 3RT2 contactor maximum</b>	5 000 1/h
<b>Main circuit</b>	
<b>number of poles for main current circuit</b>	1
operating voltage rated value	24 ... 240 V
<b>ampacity of the output relay at AC-15</b>	
• at 250 V at 50/60 Hz	3 A
• at 400 V at 50/60 Hz	3 A
<b>ampacity of the output relay at DC-13</b>	
• at 24 V	1 A
• at 125 V	0.2 A
• at 250 V	0.1 A
<b>operational current at 17 V minimum</b>	0.005 A
<b>continuous current of the DIAZED fuse link of the output relay</b>	4 A
<b>Electromagnetic compatibility</b>	
<b>conducted interference</b>	
• due to burst acc. to IEC 61000-4-4	2 kV
• due to conductor-earth surge acc. to IEC 61000-4-5	2 kV
• due to conductor-conductor surge acc. to IEC 61000-4-5	1 kV
<b>field-based interference acc. to IEC 61000-4-3</b>	10 V/m
<b>electrostatic discharge acc. to IEC 61000-4-2</b>	6 kV contact discharge / 8 kV air discharge
<b>Galvanic isolation</b>	
<b>design of the electrical isolation</b>	Protective separation
<b>galvanic isolation</b>	
• between input and output	Yes
• between the outputs	Yes
• between the voltage supply and other circuits	Yes
<b>Connections/ Terminals</b>	
<b>product component removable terminal for main circuit</b>	Yes
<b>product component removable terminal for auxiliary</b>	Yes

and control circuit			
type of electrical connection <ul style="list-style-type: none"><li>for main current circuit</li><li>for auxiliary and control circuit</li></ul>	screw-type terminals screw-type terminals		
type of connectable conductor cross-sections <ul style="list-style-type: none"><li>solid</li><li>finely stranded with core end processing</li><li>at AWG cables solid</li><li>at AWG cables stranded</li></ul>	1x (0.5 ... 4.0 mm²), 2x (0.5 ... 2.5 mm²) 1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1.5 mm²) 2x (20 ... 14) 2x (20 ... 14)		
connectable conductor cross-section <ul style="list-style-type: none"><li>solid</li><li>finely stranded with core end processing</li></ul>	0.5 ... 4 mm² 0.5 ... 2.5 mm²		
AWG number as coded connectable conductor cross section <ul style="list-style-type: none"><li>solid</li><li>stranded</li></ul>	20 ... 14 20 ... 14		
tightening torque with screw-type terminals	0.8 ... 1.2 N·m		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	snap-on mounting		
height	92 mm		
width	22.5 mm		
depth	91 mm		
required spacing <ul style="list-style-type: none"><li>with side-by-side mounting<ul style="list-style-type: none"><li>forwards</li><li>backwards</li><li>upwards</li><li>downwards</li><li>at the side</li></ul></li><li>for grounded parts<ul style="list-style-type: none"><li>forwards</li><li>backwards</li><li>upwards</li><li>at the side</li><li>downwards</li></ul></li><li>for live parts<ul style="list-style-type: none"><li>forwards</li><li>backwards</li><li>upwards</li><li>downwards</li><li>at the side</li></ul></li></ul>	0 mm 0 mm 0 mm 0 mm 0 mm  0 mm 0 mm 0 mm 0 mm 0 mm  0 mm 0 mm 0 mm 0 mm 0 mm		
Ambient conditions			
installation altitude at height above sea level maximum	2 000 m		
ambient temperature <ul style="list-style-type: none"><li>during operation</li><li>during storage</li><li>during transport</li></ul>	-25 ... +60 °C -40 ... +85 °C -40 ... +85 °C		
Certificates/ approvals			
General Product Approval	EMC	Declaration of Conformity	Test Certificates



[Type Test Certificates/Test Report](#)

Test Certificates	Marine / Shipping	other	Railway
-------------------	-------------------	-------	---------

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UG4622-1AW30>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UG4622-1AW30>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3UG4622-1AW30>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3UG4622-1AW30&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UG4622-1AW30&lang=en)

**Characteristic: Derating**

<https://support.industry.siemens.com/cs/ww/en/ps/3UG4622-1AW30/manual>

last modified:

12/21/2020 