


KNIPEX Quality – Made in Germany



Electricians' shears

Universal shears with crimp area for electricians

New: with crimp function for end sleeves (ferrules)



Precision ground finely serrated cutting edges for a clean and non-slip cut

Recess for the simple cutting of fine stranded cable

Crimping of end sleeves (ferrules) (up to 6.0 mm²)

Electricians' shears



Universal shears with crimp area for electricians

95


► New: with crimp function for end sleeves (ferrules)

- > Precisely ground blades with fine serration for clean, non-slip (nonskid) cut
- > Crimp zone for crimping end sleeves (ferrules) up to a diameter of 6.0 mm
- > With plastic belt pouch
- > Handles with multi-component grips, glass fibre reinforced
- > Cutting edges made from stainless steel, hardness of cutting edges 56 HRC


Product video



No slipping thanks to micro-serration



Integrated cable cutter



Fast, easy crimping



Safely stored and ready to hand at all times

Article No.	EAN	↔ mm	⚖ g
95 05 10 SB	4003773-082125	160	144