




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**

PCB Thickness (Recommended): 2.36 – 3.18 mm [.093 – .125 in]

Mating Tab Width: 6.35 mm [.25 in]

Mating Tab Thickness: .81 mm [.032 in]

PCB Hole Diameter: 1.4 mm [.06 in]

### Features

#### Configuration Features

Stud Hole	No
Terminal Angle	180 °

#### Body Features

Plating Thickness	5 μm[199.85 μin]
-------------------	------------------

#### Contact Features

PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Terminal Size	6.35
Terminal Orientation	Straight

#### Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
Product Terminates To	Printed Circuit Board

### Dimensions

Extension Below Board	4 mm[.157 in]
PCB Thickness (Recommended)	2.36 – 3.18 mm[.093 – .125 in]
PCB Hole Diameter	1.4 mm[.06 in]
Profile Height from PCB	10 mm[.394 in]

### Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

### Packaging Features

Packaging Quantity	5000
Packaging Method	Box

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 140814-2  
250 FASTON,TAB,TPBR



TE Part # 726387-2  
250 FASTON TAB TPBR



TE Part # 726388-2  
187 FASTON TAB TPBR



TE Part # 1-726388-2  
187 FASTON,TAB,TPBR



TE Part # 141878-2  
250 FASTON,TAB,TPBR



TE Part # 725964-2  
250 FASTON TAB TPBR



TE Part # 216926-1  
POSITIVE LOCK 250 TAB PHBRZ



TE Part # 140598  
250 FASTON,TAB,TPBR



TE Part # 1-726386-2  
250 FASTON,TAB,TPBR



TE Part # 142241-2  
250 FASTON,TAB,TPBR



TE Part # 140596  
250 FASTON,TAB,TPBR




TE Part # 394705  
250 FASTON,TAB,TPBR




TE Part # 726386-1  
250 FASTON TAB BR


## Also in the Series | FASTON 250



Compression Connectors(4)



Crimp Terminal Housings(143)




Insertion & Extraction Tools(6)



Magnet Wire Terminals(1)



PCB Terminals(144)






Quick Disconnects(456)



Splices(4)

## Customers Also Bought

TE Part #646273-1  
2MM HM REC PWR/GRD MODULETE Part #2-647123-4  
04P MTA156 SHRD HDR ASSY SQ SNTE Part #533065-6  
HDI POWER CONTACT ASSYTE Part #8-1879352-7  
RR02 5% 1K2 AMMOTE Part #2176316-6  
MELF SMA\_A 270R 0.1% 15PPM 0207  
1WTE Part #5-1624116-5  
BMB-P 0603 470R N8TE Part #6-2176386-3  
RQ 1206 54K9 0.1% 10PPM 1K RL

## Documents

### Product Drawings

#### 250 FASTON TAB TPBR

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_CVM\\_726386-2\\_G.2d\\_dxf.zip](#)

English

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_726386-2\\_G.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_726386-2\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



---

## Product Specifications

### Product Specification

English

---

## Product Environmental Compliance

### MD\_726386-2\_0628201819\_dmtec

English

### MD\_726386-2\_0628201819\_dmtec

English