



MICROWAVE SENSOR CONTROLS

DETECTION AREA				
	1	2	3	
I	ON	ON	ON	100%
II	-	ON	ON	75%
III	ON	-	ON	50%
IV	-	-	ON	25%
V	-	-	-	10%

HOLD TIME				
	4	5	6	
I	ON	ON	ON	5s
II	-	ON	ON	30s
III	ON	-	ON	90s
IV	-	-	ON	3 mins
V	ON	ON	-	20 mins
VI	-	-	-	30 mins

DAYLIGHT SENSOR				
	7	8	9	
I	ON	ON	ON	2Lux
II	ON	ON	-	10Lux
III	-	ON	-	25Lux
IV	ON	-	-	50Lux
V	-	-	-	Disable*



MICROWAVE SENSOR

This sensor can either be wired directly into an existing fitting providing there is sufficient space to do so or alternatively it can be installed inside a separate unobtrusive enclosure, see Eterna part code MWCASE

- Polycarbonate construction
- Rated Load - 800W (resistive), 400W (inductive), 270W (LED)
- Adjustable detection angle: up to 150°
- Power consumption: <0.5W
- Adjustable detection range: Max. 6m
- Adjustable time setting: 5 seconds - 30 minutes
- Adjustable Lux control: 2-50 lux
- Push connect terminals: for ease of connection

ENCLOSURE FOR MICROWAVE SENSOR

- Polycarbonate construction
- Compact & discreet design: for housing Eterna part code SENSORMW
- IP65, ceiling or wall mounted: giving versatile fixing options, suitable for bathroom, internal and external use
- Supplied with two mounting screws to install SENSORMW and has 2 x 20mm gland entry holes: facilitating easy installation
- Screw fit cover to maintain IP rating, with clip on bezel: meaning enclosure cannot be tampered with easily

- **SENSORMW** = M.O.M: 1 / O.P.Q: 150
- **MWCASE** = M.O.M: 1 / O.P.Q: 100

Code	Version	Colour	IP Rating
SENSORMW	Sensor	White	-
MWCASE	Case	White	IP65

