


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2132050002](#)
Status: **Active**
Overview: PowerPlane Busbar Power Connectors
Description: PowerPlane Busbar Receptacle Assembly, Small Size, Right-Angle, Through-Hole, 3.00mm and 3.18mm Bus Bar Thickness

Documents:

[Drawing \(PDF\)](#) [Packaging Specification 2131910002-PK-000 \(PDF\)](#)
[Product Specification 2131910001-PS-000 \(PDF\)](#) [Datasheet \(PDF\)](#)
[Application Specification 2131910001-AS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)



Series image - Reference only

General

Product Family	PCB Receptacles
Series	213205
Application	Power
Overview	PowerPlane Busbar Power Connectors
Product Name	PowerPlane
UPC	195842395947

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Resin	Liquid Crystal Polymer
Net Weight	7.657/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	130.0A
Voltage - Maximum	600V AC

Material Info

Reference - Drawing Numbers

Application Specification	2131910001-AS-000
Packaging Specification	2131910002-PK-000
Product Specification	2131910001-PS-000
Sales Drawing	2132050002-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[213205 Series](#)

This document was generated on 05/10/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION