Product data sheet



<u>+44 (0)1946 816600</u> brannan.co.uk

NON-CONTACT, AUTOMATIC, INFRARED TEMPERATURE SCANNER

 Long measuring distance High temperature alarm

Automatic temperature scanner specifically designed to assist in current battle against COVID-19 and other infections. The thermometer can be wall mounted or positioned on a tripod, situated in a position where a high number of people are entering a premises and capable of taking multiple temperature readings within a short period of time.

Ideally suited for the entrance to schools, office buildings, retail shops, gyms, etc, and eliminates the need for a member of staff to approach visitors.

Please note: This is not a medical device and should not be used for diagnostic purposes. We recommend the use of a medical body thermometer to confirm high temperature readings.

Product features:

- Automatic temperature measurement High accuracy and fast response time •
- Easy and safe
- Energy saving
- Large, high definition LCD
 - · Hanging hook or adhesive fixture Connects to PC for remote reading and measurement storage
- Supplied with USB cable and standard UK 3-pin plug •
- Tripod stand available* •

Product specifications:

Infrared range: Response time: Measuring distance: Accuracy: Operating temperature:	+34 to +43°C 0.5 seconds 5cm to 10cm +/- 0.2°C +10 to +40°C (recommended +15 to +35°C)
Alarm (body mode only):	Normal: 1 beep + green flashing light
	High (Hi) >37.5°C: 3 beeps + red flashing light
Measurement:	Automatic, non-contact measurement
LCD dimensions:	24mm x 58mm
Power source:	USB cable and plug (cable length: 200cm)
Compatible battery:	Suitable for use with lithium 18650 battery*
	Average battery charge life: Approx one week
Installation methods:	Hook, double sided adhesive or tripod stand*
Product dimensions:	Net: 171mm x 115mm x 140mm
	Gross: 140mm x 180mm x 115mm
Product weight:	Net: 263g
Ū	Gross: 400g

* Tripod and rechargeable battery not included as standard - additional charges applicable







Product data sheet



Tripod for use with Brannan Automatic, Non Contact, Rapid Test, **Infrared Temperature Scanner**

Product specifications:

Product Weight: Product dimensions (closed): 780mm x 65mm x 65mm Max height when open: Box dimensions:

Net: 578g Gross: 681g Approx 1.5m 790mm x 70mm x 65mm



Description	Barcode	Product No
Non-contact, infrared temperature scanner	5 011405 141002	14/100/0
Tripod for scanner	5 011405 141002	14/100/1
Rechargeable lithium battery for scanner	N/A	14/100/2

View me on the website



Brannan

brannan.co.uk

Measurement for life.