



## TECHNICAL INFORMATION

Watts:	17
Lumens:	1400
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color Temperature:	4000K
Dimension:	Ø320x100mm
Emergency Standby Watts:	>1.5W
Battery Type:	Ni-Cd 9.6V, 1.0Ah

## BULKHEAD EMERGENCY PACK | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 806 - 1558 940

[View more details](#)

## STYLISH & MODERN DESIGN

Sleek appearance with round and circular edges that goes well with any contemporary interior or outdoor areas



## FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- These IP65 LED bulkheads are equipped with Ni-Cad batteries that automatically charges while in use.
- (3) hrs on emergency situations - Green LED Charging indicator
- Including battery protection circuit & inhibiting mode
- 100% PC for endurance & durability - Quick connector for easy wiring
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

## PACKAGING

Gross Weight (Kgs): 1.39  
Unit CBM: 0.011979  
Dimension: Ø320x100mm

## MASTER BOX PACKAGING

Box Qty: 10  
Qty Per Pallet: 100  
Length (Box) mm: 330  
Width (Box) mm: 330  
Height (Box) mm: 110

## LISTING DETAILS

Commodity Code: 9405114090  
Ean Code: 3800157636773

CE/EMC

CE/LVD

