

# ADX-800 LINK

## Active 2-Channel DI-Box & Splitter

ADX-800 LINK is a DI-Box (Direct Injection Box) that converts up to two unbalanced audio signals (e.g. electric and / or acoustic guitars and basses, line signals such as guitar preamps, keyboards, multi-effects, computers, etc.) in balanced signals with XLR connections. This allows not only to attenuate the interferences that normally the unbalanced cables collect in the medium-long distances, but also acts as a splitter with a maximum of 3 outputs for Channel1 (2 XLR outputs + 1 balanced 1/4" TRS Jack). It can be powered either by the supplied power adapter, or through the + 48V Phantom power coming from the mixer. It is equipped with a 3-position input attenuator (0dB, 20dB, 40dB) - to adapt the preamp stage to all types of signals - and the lift ground switch, very useful in case of ground loop. ADX-800 LINK is essentially an indispensable tool on stage, in the rehearsal room and recording studio to solve problems for musicians, DJs and sound engineers.



## KEY FEATURES

2 Channels DI-Box Operation

1 Channel Splitter function with max 3 Outputs

TRS 1/4" Jack Outputs

Balanced XLR Outputs

0/20/40dB Attenuation

Operable via external Power Adapter (supplied) or external Phantom Power

Ground Loop selector

## MORE SPECIFICATIONS

Frequency Response 10Hz-30KHz  $\pm 1$ dB

Max Input Level 15 dBu  $\pm 1$ dB

Noise Level -65dBu

Attenuation Pad 0dB/-20dB/-40dB

Modes 2-Channel/Link

Phantom Power (In case of power from balanced XLR connection) +48Vdc

Power Adapter (included) 12Vdc/100mA min.

Consumption 2.3mA

Unit Size 112x65x36 mm

Unit Weight 260g

Carton Size 130x150x40 mm

Carton Gross Weight 400g (including DI-Box and Power Adapter)