# +4dBi Adhesive Flexible

4G GSM & GPS Combo Antenna

## Features

- Mini Self Adhesive Patch Antenna
- 700/960 1800/2700MHz/1575.42MHz
- Gain: +4dBi
- Linear Polarization
- VSWR = < 1.5
- 50ohm Impedance
- Max Power 10w
- 15cm 1.13 mini Coax to UFL
- Flexi PCB Thickness 0.3mm
- 3M adhesive sticker on Rear
- Operating temp -10 to  $+70^{\circ}C$



## Applications

- Embedded GSM/GPS
- Space Saving Applications

## Description

A compact PCB Antenna for applications requiring GSM Cellular and GPS combined where high performance is required from a small size.

## **Part Number**

CE


Part Number	Description	Cable Length
ANT-GP4G-FPCB7219-2UFL	4G and GPS Combo Flexi Adhesive PCB antenna 72x19mm +4dBi	15cm



# ANT-GP4GFPCB7219-2UFL



## Performance Data - GSM



## Performance Data - GPS




www.rfsolutions.co.uk

0





### **Mechanical Details**



### **RF Solutions Ltd. Recycling Notice**

Meets the following EC Directives:

#### DO NOT

Discard with normal waste, please recycle.



#### ROHS Directive 2011/65/EU and amendment 2015/863/EU

Specifies certain limits for hazardous substances.

#### WEEE Directive 2012/19/EU

Waste electrical & electronic equipment. This product must be disposed of through a licensed WEEE collection point. RF Solutions Ltd., fulfills its WEEE obligations by membership of an approved compliance scheme. **Environment Agency producer registration number:** WEE/JB0104WV.

#### **Disclaimer:**

Whilst the information in this document is believed to be correct at the time of issue, RF Solutions Ltd does not accept any liability whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use RF Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

**RF Solutions Ltd** 

William Alexander House, William Way, Burgess Hill, West Sussex, RH15 9AG Sales: +44 (0)1444 227900 | Support: +44 (0)1444 227909

# www.rfsolutions.co.uk