

# Bullet Security Camera

**multicomp**<sup>PRO</sup>



## Specification Table

Camera	
Image Sensor	1/2.9" Progressive Scan CMOS Sensor
Resolution	2MP 1080P
Effective Pixels	1920(H)×1080(V)
Compression	H.264/H.264+/H.265/H.265+/JPEG/AVI
TV System	PAL/NTSC
Electronic Shutter Time	Auto: PAL 1/25-1/10000Sec; NTSC 1/30-1/10000Sec
Minimum Illumination	0.01Lux
S/N Ratio	60dB
Scanning System	Progressive
Video Output	Network
Reset Button	Optional
Lens	
Focus Length	3.6mm
Focus Control	Fixed
Lens Type	Fixed
Pixels	2MP
Night Vision	
Infrared LED	42μ × 2PCS
Infrared Distance	25M
IR Status	Auto Control
IR Power On	Smart, Manual & Timed mode
Network	
Ethernet	RJ-45 (10/100Base-T)
Wireless	-
Protocol	TCP/IP,ICMP,HTTP,HTTPS,FTP,DHCP,DNS,DDNS,RTP,RTSP,RTCP, NTP

# Bullet Security Camera

**multicomp**PRO

ONVIF	Support ONVIF 2.4(Profile S/T)
P2P	YES
POE	Optional, Support IEEE 802.3af
Video Delay	0.3S (Within the Lan)
Main Stream 1	2304×1296@20fps
Main Stream 2	1920×1080@30fps
Main Stream 3	1280×720@30fps
Sub Stream 1	720×480@20fps 720×480@30fps
Sub Stream 2	640×480@20fps 640×480@30fps
Sub Stream 3	-
Tri Stream	-
IE Brower	IE8-11, Google Chrome, Firefox
Smart Phone	iPhone, Android
<b>AI Function</b>	
Intelligent Analysis	Intrusion Detection,motion detection based on human detection
<b>Camera Features</b>	
Day/Night	Colour/ B&W (IR-CUT )
Image Config	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control)
Full Color	-
Corridor Pattern	-
Defog Mode	Support
ROI	-
BLC	Support
WDR	DWDR: 50dB
Motion Detection	Support (support enable the detection based on human movement only)
Privacy Masking	3 Rectangular Zone
Recording Mode	NVR/CMS/Web
Language	Chinese Simplified, Chinese Traditional, English, Bulgarian, Polish, Arabic, German, Russian, French, Korean, Portuguese, Japanese, Turkish, Spanish, Hebrew, Italian, Netherlands, Czech, Vietnamese
<b>Interface</b>	
Audio	Optional 1 Built-in MIC/Optional Audio IN/OUT/ Optional Audio In
Alarm	-
SD Card Slot	-
RS485	-

General	
Housing	IP67
Anti-cut Bracket	YES
IR Cut Filter	YES
Operation Temperature	-20°C to +60°C RH95% Max
Storage Temperature	-20°C to +60°C RH95% Max
Power Source	DC12V ±10%, 700mA
Dimension	169.5mm(L)×70mm(W)×67.5mm(H)
Weight	600g

## Part Number Table

Description	Part Number
Bullet Security Camera, 1/2.9" Prog Scan CMOS, F1.6 HD Lens, w/IR-CUT, 3.6mm fixed, 2MP, with plastic junction box (B300), internal POE	MP008909

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.