


User Manual

Capillary Thermostats



Part Number: TS-200S R

It is called "Mechanical or Capillary thermostat" which maintains the desired temperature for the various heating or cooling appliances. It consists of a sensing bulb to detect temperature and a switch to cut in and cut off the electric power. Be sure to mind this manual for the most suitable application and for your safety.

Features

Temperature range to be controlled covers from - 30°C to 320°C.

The electric rating (30A/250V AC, 20A/250V AC is shown on each label of the part.

Max. ambient temperature of the thermostat body is 120°C


Not over 120% from high end temperature is allowed on the bulb temperature.

(Not over 1.05% is recommended for thermostat higher than 300°C for safety)


Caution & Notice

1. Please mind this instructions before installing a thermostat to your equipment and contact the supplier for any question or doubt.
2. Use it in allowed electric rating for your safety.
3. Carefulness is required to handle bulb and capillary to prevent breaking.
4. Do not bend the capillary less than 5mm radius
5. A damaged bulb can make fail the desired temperature.
6. Thermostat body should be installed away from heating source. The higher ambient temperature can affect its normal function.
7. Sensing bulb should be installed in or close to heating source. Otherwise it can be out of the allowed tolerance.
8. Install the thermostat so that no pressure is applied to the body of the thermostat. Excessive pressure on the body may cause malfunction.
9. Terminals deformation is not allowed for safety.
10. Refund or replacement is not accepted for voluntary fixing or modifying.
11. Applying the supplied parts with the thermostat.

Diagram



Installation



Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.