

PRIME B450-PLUS

Note: The specifications are subject to change without notice.

CPU	AM4 socket for AMD Ryzen™ 2nd Generation/ Ryzen™ with Radeon™ Vega Graphics/ Ryzen™ 1st Generation Processors Supports CPU up to 8 cores* * Due to CPU limitation, CPU cores supported varies by processor. ** Refer to www.asus.com for the AMD CPU support list.
Chipset	AMD B450 Chipset
Memory	AMD Ryzen™ 2nd Generation Processors/AMD Ryzen™ with Radeon™ Vega Graphics/ Ryzen™ 1st Generation Processors 4 x DIMM, max. 64GB, DDR4 3200(O.C.)/3000(O.C.)/2800(O.C.)/2666/2400/2133 MHz, unbuffered memory Dual Channel memory architecture * ECC memory(ECC mode) support varies by CPU. ** Refer to www.asus.com for the Memory QVL (Qualified Vendors List).
Expansion Slots	AMD Ryzen™ 2nd Generation/ Ryzen™ 1st Generation Processors 1 x PCI Express 3.0 x16 slot(max.@x16 mode) AMD Ryzen™ with Radeon™ Vega Graphics Processors 1 x PCI Express 3.0 x16 slot(max.@x8 mode) AMD B450 Chipset: 1 x PCI Express 2.0 x 16 slots (max. at x4 mode) 3 x PCI Express 2.0 x1 slots
Multi-GPU support	Supports AMD CrossFireX™ Technology
VGA	Integrated Graphics in the AMD Ryzen™ with Radeon™ Vega Graphics Processors Multi-VGA output support: DVI, HDMI port - Supports DVI with a maximum resolution of 1920 x 1200 @60Hz - Supports HDMI 2.0b with a maximum resolution of 4096 x 2160 @60Hz - Maximum shared memory of 2048 MB
Storage	AMD B450 Chipset - 4 x Serial ATA 6.0 Gb/s connectors with RAID 0, RAID 1 and RAID 10 support AMD Ryzen™ 2nd Generation/ Ryzen™ with Radeon™ Vega Graphics/ Ryzen™ 1st Generation Processors -2 x Serial ATA 6.0 Gb/s connectors with RAID 0, RAID 1 and RAID 10 support AMD Ryzen™ 2nd Generation/ Ryzen™ with Radeon™ Vega Graphics/ Ryzen™ 1st Generation Processors - 1 x M.2 socket 3 with M Key, Type 2242/2260/2280/22110(PCIe 3.0 x4 and SATA modes)storage devices support* *The M.2 Socket shares bandwidth with the SATA_5/6 ports, and therefore the SATA_5/6 ports cannot be used when an M.2 device is installed.
LAN	Realtek® 8111H Gigabit LAN Controller
Audio	Realtek® ALC 887-VD2 8-Channel High Definition Audio CODEC - LED-illuminated design: Brighten up your build with the gorgeous illuminated audio trace path. - Audio Shielding: Ensures precision analog/digital separation and greatly reduces multi-lateral interference - Dedicated audio PCB layers: Separate layers for left and right channels to guard the quality of the sensitive audio signals - Premium Japanese audio capacitors: Provide warm, natural and immersive sound with exceptional clarity and fidelity

	<ul style="list-style-type: none"> - Supports jack-detection and front panel jack-retasking <p>*Use a chassis with HD audio module in the front panel to support an 8-channel audio output.</p>
USB	<p>AMD Ryzen™ 2nd Generation/ Ryzen™ with Radeon™ Vega Graphics/ Ryzen™ 1st</p> <ul style="list-style-type: none"> - 3 x USB 3.1 Gen1 (up to 5Gbps) ports (2 Type A at back+ 1 Type C at back) <p>AMD B450 Chipset:</p> <ul style="list-style-type: none"> - 2 x USB 3.1 Gen 2 (up to 10 Gbps) ports (2 ports at back) - 2 x USB 3.1 Gen 1 (up to 5Gbps) ports (2 ports at mid-board) - 6 x USB 2.0 ports (2 ports at back,4 ports at mid-board)
ASUS Unique Features	<p>Dependable Stability</p> <p>ASUS 5X PROTECTION III</p> <ul style="list-style-type: none"> - ASUS SafeSlot Core - Fortified PCIe Slot prevents damage - ASUS LANGuard: Protects against LAN surges, lightning strikes and static-electricity discharges - ASUS Overvoltage Protection: World-class circuit-protecting power design - ASUS Stainless-Steel Back I/O: 3X corrosion-resistance for greater durability! - ASUS DIGI+ VRM: 6 Phase digital power design <p>Superb performance</p> <p>UEFI BIOS</p> <ul style="list-style-type: none"> - Most advanced options with fast response time <p>ASUS Fan Xpert 4 Core</p> <ul style="list-style-type: none"> - Advanced fan and liquid controls for ultimate cooling and quietness <p>Gaming Scenario</p> <p>Audio Features</p> <ul style="list-style-type: none"> - Audio that roars on the battlefield <p>ASUS Exclusive Features</p> <ul style="list-style-type: none"> - ASUS AI Charger - ASUS File Transfer - ASUS AI Suite 3 - ASUS PC Cleaner <p>Easy PC DIY</p> <p>Safe motherboard mounting</p> <ul style="list-style-type: none"> - Component-free areas to minimize damage risk <p>Q-Design</p> <ul style="list-style-type: none"> - ASUS Q-DIMM - ASUS Q-Slot <p>UEFI BIOS EZ Mode</p> <ul style="list-style-type: none"> - featuring friendly graphics user interface - ASUS CrashFree BIOS 3 - ASUS EZ Flash 3
ASUS Quiet Thermal Solution	<p>Quiet Thermal Design:</p> <ul style="list-style-type: none"> - Stylish Fanless Design: MOS Heat-sink & Chipset Heat-sink solution - ASUS Fan Xpert 4 core
Back Panel I/O Ports	<ul style="list-style-type: none"> 1 x PS/2 Keyboard/Mouse Combo port 1 x DVI port 1 x HDMI 2.0 port 1 x LAN (RJ-45) port 2 x USB 3.1 Gen 2 (up to 10 Gbps) ports(Type A, teal blue) 1 x USB 3.1 Gen 1 (up to 5 Gbps) port (Type C)

	<p>2 x USB 3.1 Gen 1 (up to 5 Gbps) ports(Type A, blue)</p> <p>2 x USB 2.0/1.1 ports</p> <p>3 x Audio jacks support 8-channel audio output</p>
Internal I/O Connectors	<p>1 x USB 3.1 Gen 1 (up to 5Gbps) connector supports additional 2 USB 3.1 Gen 1 ports</p> <p>2 x USB 2.0/1.1 connectors support additional 4 USB 2.0/1.1 ports</p> <p>6 x SATA 6.0 Gb/s connectors</p> <p>1 x M.2 Socket 3 for M Key, type 2242/2260/2280 devices support(both SATA & PCIE mode)</p> <p>1 x COM connector</p> <p>1 x Aura RGB Strip header</p> <p>1 x CPU Fan connector</p> <p>3 x 4-pin Chassis Fan connectors for both 3-pin(DC mode) and 4-pin(PWM mode) coolers control</p> <p>1 x Front panel audio connector</p> <p>1 x 24-pin EATX Power connector</p> <p>1 x 8-pin EATX 12V Power connector</p> <p>1 x 2-pin Clear CMOS</p> <p>1 x System Panel connector</p> <p>1 x S/PDIF out header</p> <p>1 x AIO pump header</p>
BIOS	<p>128 Mb Flash ROM, UEFI AMI BIOS, PnP, SM BIOS 3.1, ACPI 6.1, Multi-language BIOS, ASUS EZ Flash 3, ASUS CrashFree BIOS 3, F3 My Favorite, Last Modified log, F12 PrintScreen, F4 AURA ON/OFF, F9 Search and ASUS DRAM SPD (Serial Presence Detect) memory information</p>
Manageability	<p>WOL by PME, PXE</p>
Accessories	<p>2 x Serial ATA 6.0Gb/s cables</p> <p>1 x I/O shield</p> <p>1 x M.2 screw package</p> <p>1 x User's manual</p> <p>1 x Support DVD</p>
Support DVD	<p>Drivers</p> <p>ASUS Utilities</p> <p>ASUS Update</p> <p>Anti-virus software (OEM version)</p>
Operating System Support	<p>Windows® 10 (64-bit)</p>
Form Factor	<p>ATX Form Factor, 12"x 9.2" (30.5cm x 23.4cm)</p>