


Continuity Tester



Specifications

Power Supply	: 9 Volt Battery
Battery Life	: Approx. 12 months with normal use.
Continuity Confirmation	: Equal to or less than 1kΩ
Wire Verification Distance	: 10,000 Ft, 3,000m (26 Gage min)
Fuse	: 250V, 0.5A fast blow
Operating Temperature	: -12°C to +45°C (10°F to 113°F)
Storage Temperature	: -20°C to +80°C (-4°F to 176°F)
Operating Humidity	: 10 to 90%RH (non-condensing)
Dimensions	: 96mm×47mm×33mm (3.8"×1.8"×1.32")
Weight	: 135g (4.8oz)

Diagram



Description

1. Local Continuity Tester (main pulsing unit)
2. Power On/Off
3. Local Continuity Indicator (flashing red LED)
4. Power "On" Indicator (steady green LED)
5. Remote Probe Holder (side mounted plastic piece)
6. Red and Black Tester Leads w/alligator
7. 9 Volt Battery Compartment (removable cover on rear)
8. Remote Probe Continuity Indicator (red/green bi-color LED)
9. Red and Black Remote Probe Leads w/alligator clips
10. Local Continuity Beeper

Part Number Table

Description	Part Number
Continuity Tester, Auto Ranging, 4000 Count Display	72-9170

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

