



# SAFETY DATA SHEET

according to 1907/2006/EC, Article 31

Page 1/4

## QSW-NC600-SN100

Revision 6  
Revision date 2013-03-06

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product name QSW-NC600-SN100

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Description Soldering.

#### 1.3. Details of the supplier of the safety data sheet

Company	Qualitek Europe Ltd
Address	Unit 9 Apex Court Bassendale Road Bromborough Wirral CH62 3RE
Web	www.qualitek.com
Telephone	+ 44(0)151 334 0888
Fax	+ 44(0)151 334 1408
Email address of the competent person	sales@qualitek-europe.com

#### 1.4. Emergency telephone number

Emergency telephone number	+ 44(0)151 334 0888
	9.00 am - 5.00 pm Mon -Fri

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

Main hazards No Significant Hazard

#### 2.3. Other hazards

Other hazards CAUTION CONTAINS ROSIN: Exposure to this material may cause certain sensitive individuals to develop eczema and/or asthma. Sensitised persons may subsequently show asthmatic symptoms when exposed to atmospheric concentrations well below the OEL. Persons with a history of asthma allergies or chronic or recurrent respiratory disease should not be employed in any process in which this product is used. May cause allergic skin reactions with repeated exposure. Persons with a history of skin sensitization problems should not be employed in any process in which this product is used..

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

## QSW-NC600-SN100

Revision 6

Revision date 2013-03-06

## 3.2. Mixtures

67/548/EEC / 1999/45/EC

Chemical Name	Index No.	CAS No.	EC No.	REACH Registration Number	Conc. (%w/w)	Classification
Tin		7440-31-5	231-141-8		90 - 100%	
Mod Rosin		65997-05-9	500-163-2		1 - 5%	Xi; R43
Copper		7440-50-8			0.3 - 1%	Xn; R22 R53
Cobalt	027-001-00-9	7440-48-4	231-158-0			R42/43 R53

## SECTION 4: First aid measures

## 4.1. Description of first aid measures

Inhalation	May cause irritation to mucous membranes. Move the exposed person to fresh air.
Eye contact	May cause irritation to eyes. Rinse immediately with plenty of water for 15 minutes holding the eyelids open. Seek medical attention if irritation or symptoms persist.
Skin contact	May cause irritation to skin. Wash off immediately with plenty of soap and water. Remove contaminated clothing. Seek medical attention if irritation or symptoms persist.
Ingestion	May cause irritation to mucous membranes. DO NOT INDUCE VOMITING. Seek medical attention if irritation or symptoms persist.

## SECTION 5: Firefighting measures

## 5.1. Extinguishing media

	Use extinguishing media appropriate to the surrounding fire conditions.
--	---

## 5.2. Special hazards arising from the substance or mixture

	Burning produces irritating, toxic and obnoxious fumes.
--	---

## 5.3. Advice for firefighters

	Wear suitable respiratory equipment when necessary.
--	---

## SECTION 6: Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

	Ensure adequate ventilation of the working area.
--	--

## 6.2. Environmental precautions

	Do not allow product to enter drains. Prevent further spillage if safe.
--	---

## 6.3. Methods and material for containment and cleaning up

	Sweep up. Transfer to suitable, labelled containers for disposal. Clean spillage area thoroughly with plenty of water.
--	--

## SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

	Avoid contact with eyes and skin. Ensure adequate ventilation of the working area. Adopt best Manual Handling considerations when handling, carrying and dispensing.
--	--

## 7.2. Conditions for safe storage, including any incompatibilities

	Keep in a cool, dry, well ventilated area. Keep containers tightly closed. Store in correctly labelled containers.
--	--

## SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

## 8.1.1. Exposure Limit Values

## QSW-NC600-SN100

Revision 6

Revision date 2013-03-06

## 8.1.1. Exposure Limit Values

Copper	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 0.2
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: -
	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 1
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: 2
Mod Rosin	WEL 8-hr limit ppm: -	WEL 8-hr limit mg/m3: 0.05
	WEL 15 min limit ppm: -	WEL 15 min limit mg/m3: 0.15

## 8.2. Exposure controls

8.2.1. Appropriate engineering controls	Ensure adequate ventilation of the working area. Appropriate local exhaust ventilation is required. P285 - In case of inadequate ventilation wear respiratory protection.
8.2.2. Individual protection measures	Wear protective clothing.
Eye / face protection	In case of splashing, wear: . Approved safety goggles.
Skin protection - Handprotection	Chemical resistant gloves (PVC).

## SECTION 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

State	Solid
Colour	Grey
Melting point	228 °C
Relative density	8 (Water = 1 @ 20 °C)
Solubility	Slightly soluble in water

## SECTION 10: Stability and reactivity

## 10.2. Chemical stability

	Stable under normal conditions.
--	---------------------------------

## SECTION 11: Toxicological information

## 11.1. Information on toxicological effects

Skin corrosion/irritation	May cause irritation to skin.
Serious eye damage/irritation	Irritating to eyes.
Respiratory or skin sensitisation	May cause sensitisation by inhalation and skin contact.

## SECTION 12: Ecological information

## 12.1. Toxicity

Mod Rosin	Daphnia EC50/48h: 0.009 mg/l	Fish LC50/96h: 0.003 mg/l
-----------	------------------------------	---------------------------

## 12.2. Persistence and degradability

	Not readily biodegradable.
--	----------------------------

## 12.3. Bioaccumulative potential

	Not determined.
--	-----------------

## SECTION 13: Disposal considerations

## General information

	Dispose of in compliance with all local and national regulations.
--	---

## SECTION 14: Transport information

## Further information

	The product is not classified as dangerous for carriage.
--	--

## QSW-NC600-SN100

Revision 6

Revision date 2013-03-06

**SECTION 15: Regulatory information****Labelling**

<b>Risk phrases</b>	No Significant Hazard.
---------------------	------------------------

**SECTION 16: Other information****Other information**

<b>Revision</b>	This document differs from the previous version in the following areas: 2 - Other hazards. 2 - Further information.
-----------------	---

<b>Text of risk phrases in Section 3</b>	R22 - Harmful if swallowed. R42/43 - May cause sensitisation by inhalation and skin contact. R43 - May cause sensitisation by skin contact. R53 - May cause long-term adverse effects in the aquatic environment.
--	--

**Further information**

	The information supplied in this Safety Data Sheet is designed only as guidance for the safe use, storage and handling of the product. This information is correct to the best of our knowledge and belief at the date of publication however no guarantee is made to its accuracy. This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process.
--	--