



# Ledinaire floodlights gen3

## BVP164 LED60/840 PSU 50W SWB CE

-- 840 neutral white -- -- Symmetrical

This Ledinaire floodlights range contains a selection of popular off-the-shelf LED luminaires that comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

### Product data

General Information		Photobiological risk	
Lamp family code	-	Number of products on MCB (16 A type B)	44
Light source colour	840 neutral white	Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
Light source replaceable	No	Photobiological risk specification	0.2 m
Number of gear units	1 unit	EU RoHS compliant	Yes
Driver/power unit/transformer	No [-]	Light source engine type	LED
Driver included	Yes	<b>Light Technical</b>	
Optical cover/lens type	G [ Glass]	Upward light output ratio	0
Luminaire light beam spread	110° x 110°	Standard tilt angle post-top	-
Control interface	-	Standard tilt angle side entry	-
Connection	Flying leads/cables	<b>Operating and Electrical</b>	
Cable	Cable 1.0 m without plug (C1K)	Input Voltage	220 to 240 V
Protection class IEC	Safety class I	Input frequency	50 or 60 Hz
Flammability mark	NO [-]	Initial CLO power consumption	- W
CE mark	CE mark	Average CLO power consumption	50 W
ENEC mark	-	End CLO power consumption	- W
Warranty period	3 years	Inrush current	1.68 A
Optic type outdoor	Symmetrical		
Constant light output	No		

## Ledinaire floodlights gen3

Inrush time	0.0082 ms
Power factor (min.)	0.95

### Controls and Dimming

Dimmable	No
----------	----

### Mechanical and Housing

Housing material	Aluminium die-cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover/lens material	Tempered glass
Fixation material	Steel
Mounting device	MBA [ Mounting bracket adjustable]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	173 mm
Overall width	232 mm
Overall height	26.1 mm
Effective projected area	0.028 m <sup>2</sup>
Colour	grey
Dimensions (height x width x depth)	26 x 232 x 173 mm (1 x 9.1 x 6.8 in)

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [ 2 J reinforced]
Surge protection (common/differential)	2/2 kV

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	6000 lm
Luminous flux tolerance	+/-10%

Initial LED luminaire efficacy	120 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80
Initial chromaticity	(0.380, 0.380) SDCM <5
Initial input power	50 W
Power consumption tolerance	+/-10%
Init. colour rendering index tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	80

### Application Conditions


Ambient temperature range	-25 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

### Product Data

Full product code	871951453353099
Order product name	BVP164 LED60/840 PSU 50W SWB CE
EAN/UPC – product	8719514533530
Order code	53353099
SAP numerator – quantity per pack	1
Numerator – packs per outer box	16
SAP material	911401854483
SAP net weight (piece)	0.910 kg



## Dimensional drawing



BVP164 LED60/840 PSU 50W SWB CE

## Ledinaire floodlights gen3

