


+ 10dBi Gain 4G GSM/868MHz

Features:

- 698-900/1710/1800/2600/2700MHz
- +10dBi Gain
- F/B > 15dB
- VSWR < 2.5
- Omni Directional (360°)
- Vertical Beamwidth 45°
- Dimensions $\Phi 63 \times 410$ mm
- Vertical or Horizontal Polarisation
- Internal or External Use
- 30cm RG58 Coax to N(f) Connector
- 50 Ω Impedance
- Max Power 100W
- Fibre Glass Construction

Included:

- Antenna
- U Bolt Fixing
- Wall Mount Bracket



Applications

- GSM Applications
- 868MHz M2M
- 3G / 4G Applications



Ordering Information

Part No	Description
ANT-MOD10-N	+10dBi Omni Directional Antenna with Cable Assy

+10dBi Omni Directional Antenna



Radiation Pattern




+10dBi Omni Directional Antenna



Smith Chart




Return Loss



+ 10dBi Omni Directional Antenna



VSWR



RF Solutions Ltd. Recycling Notice
Meets the following EC Directives:

DO NOT

Discard with normal waste, please recycle.



ROHS Directive 2011/65/EU and amendment 2015/863/EU
Specifies certain limits for hazardous substances.

WEEE Directive 2012/19/EU

Waste electrical & electronic equipment. This product must be disposed of through a licensed WEEE collection point. RF Solutions Ltd., fulfils its WEEE obligations by membership of an approved compliance scheme, Environment Agency producer registration number: **WEE/JB0104WV**.

Disclaimer:

Whilst the information in this document is believed to be correct at the time of issue, RF Solutions Ltd does not accept any liability whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use RF Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

www.rfsolutions.co.uk

RF Solutions Ltd

William Alexander House, William Way, Burgess Hill, West Sussex, RH15 9AG

Sales: +44 (0)1444 227900

Tech Support: +44 (0)1444 227909

