

PRODUCT DATASHEET

SMART+ WiFi Classic 60 9 W/2700...6500 K B22d

SMART+ WiFi Classic Tunable White | Classic bulb shape with WiFi technology



Areas of application

- General illumination
- Residential interiors
- Professional (hotels, bars, boutiques etc.)
- Outdoor applications only in suitable luminaires

Product benefits

- Wireless control via app
- Easy to install and use
- Contains no mercury

Product features

- Controllable via LEDVANCE SMART+ WiFi App (with minimum Android 4.4 or iOS 9.0)
- Controllable via Google Assistant and Amazon Alexa possible
- Network protocol: WiFi
- Adjustable light color via Tunable White: Warm White to Cool White (2,700 K...6,500 K)
- Dimmable
- Lifetime: up to 15,000 h




TECHNICAL DATA

Electrical data

Nominal wattage	9 W
Construction wattage	9.00 W
Nominal voltage	230 V
Nominal current	52 mA
Operating frequency	50...60 Hz
Mains frequency	50...60 Hz
Power factor λ	> 0.5
Claimed equiv. conventional lamp power	60 W

Photometrical data


Light color (designation)	Tunable White
Lumen main.fact.at end of nom.life time	0.70
Standard deviation of color matching	≤ 6 sdcm
Nominal luminous flux	806 lm
Luminous flux	806 lm
Luminous efficacy	89 lm/W
Adjustable color temperature	2700...6500 K
Color temperature	2700...6500 K
Color rendering index Ra	80
Flickering metric (Pst LM)	1.0
Stroboscope effect metric (SVM)	0.9



Light technical data

Beam angle	215 °
------------	-------

Dimensions & Weight



Product weight	50.00 g
Diameter	60.00 mm
Length	112.00 mm
Width	60.00 mm
Height	60.00 mm
Outer bulb [PICOS]	A60

Lifespan

Lifespan	15000 h
----------	---------

Colors & materials

Housing color	White
---------------	-------

Temperatures & operating conditions

Ambient temperature range	-20...+40 °C
---------------------------	--------------

Additional product data

Mercury-free	Yes
Product remark	All technical parameters apply to the entire lamp / Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value
Base (standard designation)	B22d

Capabilities

Dimmable	Yes
Compatible smart home technology	Amazon Alexa / Google Assistant

Certificates & Standards


Energy efficiency class	F ¹⁾
Energy consumption	9.00 kWh/1000h
Standards	CE
Type of protection	IP20

¹⁾ Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	NDLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	B22d
Connected light source (CLS)	yes
Color-tuneable light source	yes
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	RANGE
Standby power	0.50
Networked standby power for CLS	0.50
Claim of equivalent power	Yes
Chromaticity coordinate x	0.463
Chromaticity coordinate y	0.420
R9 Colour rendering index	0.00
Beam angle	SPHERE_360
Survival factor	0,9
Displacement factor	0.50
LED light source replaces a fluorescent light source	not applicable
EPREL ID	528197,528197
Model number	AC33910,AC33910

DOWNLOAD DATA

DOWNLOAD DATA	
	Declarations of conformity CE SMART WIFI A60 9W 230V RGBW FR E27

DOWNLOAD DATA



Declarations of conformity
EC Declaration of Conformity SMART+ WIFI CLA HS



Installation guide
SMART+ WIFI INSTALLATION GUIDE

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075515642	Folding box 1	61 mm x 96 mm x 154 mm	124.00 g	0.90 dm ³
4058075515659	Shipping box 4	210 mm x 165 mm x 135 mm	629.00 g	4.68 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.