



Capture Lite 1100
And
Capture Lite 3000
Available to Order now
Call (+44) 01483894476



New Product Information

Rugged, robust, lineside torque tester with simple and easy to use functionality.

- Two new Capture Lite models CL1100 and CL3000 –

Stock code	Model	Range	Price
3297934	CL1100	80 -1100Nm (60-810lbf.ft)	£1400
3420523	CL3000	200- 3000Nm (148-2210lbf.ft)	£1700

- Design details
 - High quality one piece construction of the aluminium body, machined from solid billet.
 - Robust powder coating that looks good and stands up to tough industrial environments.
 - High strength stainless steel torsion shaft with 36mm Hex
 - Same footprint and mounting hole positions as other Capture Lite models. Mounting kit available separately
 - Easy to read laser marking of required product information
 - Fully compliant with UKCA and CE marking

- Function details
 - Similar to other Capture models
 - Simple one-button operation.
 - Peak, First Peak and track mode available
 - Multiple units available: N·m, lbf·ft & lbf·in

- Box and contents
 - WAG euro box with custom foam cut-out. (Same box as Capture sensors)
 - CL unit
 - 2 x bolt down bolts
 - USB cable
 - Socket 3/4" FS to 36mm FH (Product Code: 6272830)
 - Socket 1" FS to 36mm FH (Product Code: 6174900)
 - Calibration certificate
 - Quick start guide
 - User Instructions
 - Register my tool

- Newest members of the Capture Lite Family



Abbreviation	Order Code/Article Number	range	Drive		adaptor
			Size	Type	
CL1	038110	.02-1Nm	¼"	male hex	
CL10H	038120	.25-10Nm	¼"	Male hex	FH to FS (FSHA) A35640
CL10S	038130	.25-10Nm	¼"	Female sq	MS to MH 029200
CL150	038140	5-150Nm	3/8"	Female sq	¼" adaptor 031320
CL350	038150	10-350Nm	½"	Female sq	3/8" adaptor 031340
CL 1100	3297934	80-1100	36mm	male hex	¾" & 1" Socket
CL 3000	3420523	200-3000	36mm	male hex	¾" & 1" Socket