

E13 EMHV series

Series/Type: B78308*A003

Ordering code:

Date: May 2022

© TDK Electronics AG 2022. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



B78308*A003

E13 EMHV series

Construction

- Ferrite core MnZn
- SMD gullwing pins
- Triple insulated wire class F (155 °C)
- Non-conductive pick-and-place cap on top



- Height: 11.6 mm max
- Footprint: 16.2 mm x 13.4 mm
- Plastic Bobbin CTI IIIa class material
- Wide temperature range from -40 °C up to +150 °C
- Qualified to AEC-Q200
- RoHS compatible

Applications

Isolated DC/DC converters

Insulation characteristics

- PRI / SEC (Cumulative): Creepage ≥ 11.2 mm, Clearance ≥ 8.14 mm
- Core / Top surface: Creepage and Clearance ≥ 3.25 mm
- PRI / core: Creepage ≥ 7.5 mm, Clearance ≥ 5.1 mm
- SEC / core: Creepage ≥ 3.7 mm, Clearance ≥ 3.05 mm
- Insulation distances sufficient for basic insulation according to IEC 60664-1, 61558-2-16 for working voltage 1000 V DC, Transient over voltage 2500 V_{Peak}, P2, CTI IIIa, 5000 m altitude.
- Insulation distances sufficient for reinforced insulation according to IEC 60664-1, 61558-2-16 for working voltage 300 V, P2, OVC II, CTI IIIa, 2000 m altitude.

Marking

Product brand, middle block of ordering code, date code, pin 1 marker, production place identification code

Delivery mode


- Tape and reel 13" diameter
- Packing unit: 190 pcs per reel




E13 EMHV series

Dimensional drawing and recommendation

Dimensions in mm



Recommended PCB layout (Top View)





E13 EMHV series

Flyback Topology applicable Transformer Product parameters


Characteristics and ordering code: specified at +25 °C if not mentioned otherwise, all values without tolerances are typical values.


	Units	Ordering codes			
		B78308A2461A003	B78308A2462A003		
Reference Schematic		F1	F2		
Turns ratio		1:0.22:0.78	1:0.33:0.67		
Typical operational frequency	kHz	100 400 kHz			
L _{N1} (1-4)	μH	4.1 ±10%	4.1 ±10%		
at 100 kHz, 10 mV					
LL, N1 (1-4)	nH	330	300		
at 100 kHz, 10 mV		short 5, 6, 8	short 5, 6, 8		
R _{DC} , N1	mΩ	100	100		
R _{DC} , N2	mΩ	50	75		
R _{DC} , N3	mΩ	150	130		
Saturation Current I _{SAT} , N1	Α	4	4		
at T ≤+150 °C, L=Lo-20%					
Typical diagram for L _{N1}		G1			
saturation					
High Voltage Test	V AC	3000			
Routine test: 50 Hz, 1 sec		(N1) / (N2,N3)			
High Voltage Test	V AC	3750			
Type test: 50 Hz, 1 min		(N1) / (N2,N3)			
Partial discharge inception	V_{PEAK}	1:	1500		
voltage, Type test		(N1) / (N2,N3)			
Partial discharge extinction	V_{PEAK}	1200			
voltage, Type test		(N1) / (N2,N3)			
Surge voltage Test		6 kV peak; 1.2/50 μs,			
Type test		(N1) / (N2,N3)			
Recommonded IC		L9502 - STM	L9502 – STMicroelectronics		

E13 EMHV series


B78308*A003

Schematics and saturation graph





B78308A2461A003 and B78308A2462A003 - Saturation at different temperatures (typical curves)



G1



E13 EMHV series

Push Pull / Half Bridge topology applicable Transformer Product parameters

Characteristics and ordering codes: specified at +25 °C if not mentioned otherwise, all values without tolerance are typical values.

	Units	Orderin					
		B78308A2387A003	B78308A2484A003	B78308A2485A003			
Reference Schematic		F3	F3	F4			
Turns ratio		1:1.07 1:1.07		1:1:0.57:2.14			
Typical operational	kHz	100 400 kHz					
frequency							
L _{N1} (min)	μΗ	100	90	90			
at 100 kHz, 100 mV				short (2, 3)			
LL, N1	μΗ	0.8	2.6	1.1			
at 100 kHz, 100 mV		short 8-5	short 8-5	short (2, 3) &			
				5, 6, 7, 8			
C _P	pF	9	2	6			
at 20 kHz, 1 V		(N1 / N2)	(N1 / N2)	(N1,N2) / (N3,N4)			
R _{DC} , N1	mΩ	260	260	175			
R _{DC} , N2	mΩ	350	350	175			
R _{DC} , N3	mΩ	_	_	85			
R _{DC} , N4	mΩ	_	_	280			
Voltage Time Product V x	μVs	15	15	25			
Unipolar, $B_{max} = 220 \text{ mT}$							
Voltage Time Product V x	μVs	30	30	50			
Unipolar, $B_{max} = 440 \text{ mT}$							
High Voltage test	V AC	3000	3000	3000			
Routine test: 50 Hz, 1 sec		(N1 / N2)	(N1 / N2)	(N1,N2) / (N3,N4)			
High Voltage Test	V AC	3750		3750			
Type test: 50 Hz, 1 min		(N1 / N2)		(N1,N2) / (N3,N4)			
Partial discharge incep-	V_{PEAK}	1500		1500			
voltage, type test		(N1 / N2)		(N1,N2) / (N3,N4)			
Partial discharge extinc-	V_{PEAK}	1200		1200			
voltage, type test		(N1	(N1,N2) / (N3,N4)				





SMD Transformers	B78308*A003
E13 EMHV series	

Other characteristics

Storage conditions	–25 °C +40 °C, humidity ≤75% RH	
Climatic category	40/150/56 (to IEC 60068)	
Resistance to reflow	In accordance with JEDEC J-STD-020D T _{peak} = +245 °C	
soldering heat	(T _{peak} –5 °C for 30 seconds)	
Operating temperature range	-40 °C +150 °C (component)	
Weight	Approx. 2.5 g	

Referenced Schematics







E13 EMHV series

B78308*A003

Blister tape



Reel






E13 EMHV series

Recommended reflow soldering curve

Pb-free solder material (based on JEDEC J-STD 020E)



T ₁	T ₂	T ₃	T ₄	t ₁	t ₂	t ₃
°C	°C	°C	°C	s	s	s
150	200	217	245	60 – 120	60 – 150	< 30 at T ₄ –5 °C

Time from +24 °C to T_4 : max. 480 s

Maximal numbers of reflow cycles: 3



E13 EMHV series

Cautions and warnings

- Please note the recommendations in our Inductors data book (latest edition) and in the data sheets.
 - Particular attention should be paid to the derating curves given there.
 - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.
 - Washing processes may damage the product due to the possible static or cyclic mechanical loads (e.g. ultrasonic cleaning). They may cause cracks to develop on the product and its parts, which might lead to reduced reliability or lifetime.
- The following points must be observed if the components are potted in customer applications:
 - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
 - It is necessary to check whether the potting material used attacks or destroys the wire, wire insulation, plastics or glue.
 - The effect of the potting material can change the high-frequency behaviour of the components.
 - Many coating materials have a negative effect (chemically and mechanically) on the winding wires, insulation materials and connecting points. Customers are always obligated to determine whether and to what extent their coating materials influence the component. Customers are responsible and bear all risk for the use of the coating material. TDK Electronics does not assume any liability for failures of our components that are caused by the coating material.
- Ceramics / ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP. CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks

Release 2020-06