

Stereo microscope sets KERN OSE-4 · OZL-9 · OZM-9



OSE 409



OZL 961/963



OZM 902/903



OZM 922/923

Predefined stereo microscope sets with ECO universal stand and illumination for your functional workplace

**Features**

- Sets which have already been defined (except OSE 409), consisting of a stereo microscope head (p. 74), a universal stand (p. 79/80), a holder (p. 83), a ring illumination (p. 83) and a dust cover (p. 81) from our range
- Simple – convenient – affordable
- This saves you spending time on configuration and being spoilt for choice in the combination of different components. In this way you get an expensive and highly-flexible solution for your microscope workplace

Model	Microscope head		Stand	Holder	Illumination
	Tube	Objective Zoom			
<b>OSE 409</b>	Binocular (WF 10×/ø 20 mm)	1x (WD: 230 mm)	Swivel arm with block pedestal	With coarse focusing knob Adjustable torque of the hand wheels	3W LED goose neck (integrated)
<b>OZL 961</b>	Binocular (OZL 461)	0,7× - 4,5×	Telescopic arm with plate	With coarse focusing knob Adjustable torque of the hand wheels	4,5 W LED ring light (OBB-A6102)
<b>OZL 963</b>	Trinocular (OZL 462)	0,7× - 4,5×	Telescopic arm with plate	With coarse focusing knob Adjustable torque of the hand wheels	4,5 W LED ring light (OBB-A6102)
<b>OZM 902</b>	Binocular (OZM 546)	0,7× - 4,5×	Telescopic arm with plate (OZB-A1201)	With coarse focusing knob Adjustable torque of the hand wheels (OZB-A5301)	4,5 W LED ring light (OBB-A6102)
<b>OZM 903</b>	Trinocular (OZM 547)	0,7× - 4,5×	Telescopic arm with plate (OZB-A1201)	With coarse focusing knob Adjustable torque of the hand wheels (OZB-A5301)	4,5 W LED ring light (OBB-A6102)
<b>OZM 922</b>	Binocular (OZM 546)	0,7× - 4,5×	ball-bearing double telescopic arm with plate (OZB-A1203)	With coarse focusing knob Adjustable torque of the hand wheels (OZB-A5301)	4,5 W LED ring light (OBB-A6102)
<b>OZM 923</b>	Trinocular (OZM 547)	0,7× - 4,5×	ball-bearing double telescopic arm with plate (OZB-A1203)	With coarse focusing knob Adjustable torque of the hand wheels (OZB-A5301)	4,5 W LED ring light (OBB-A6102)

## Pictograms

<b>360° rotatable microscope head</b>	<b>Fluorescence illumination for compound microscopes</b> With 3 W LED illumination and filter	<b>USB 3.0 digital camera</b> For direct transmitting of the picture to a PC
<b>Monocular Microscope</b> For the inspection with one eye	<b>Phase contrast unit</b> For a higher contrast	<b>WLAN data interface</b> For transmitting of the picture to a mobile display device
<b>Binocular Microscope</b> For the inspection with both eyes	<b>Darkfield condenser/unit</b> For a higher contrast due to indirect illumination	<b>HDMI digital camera</b> For direct transmitting of the picture to a display device
<b>Trinocular Microscope</b> For the inspection with both eyes and the additional option for the connection of a camera	<b>Polarising unit</b> To polarise the light	<b>PC software</b> To transfer the measurements from the device to a PC
<b>Abbe Condenser</b> With high numerical aperture for the concentration and the focusing of light	<b>Infinity system</b> Infinity corrected optical system	<b>Automatic temperature compensation</b> For measurements between 10 °C and 30 °C
<b>Halogen illumination</b> For pictures bright and rich in contrast	<b>Zoom magnification</b> For stereomicroscopes	<b>Protection against dust and water splashes IPxx:</b> The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013
<b>LED illumination</b> Cold, energy-saving and especially long-life illumination	<b>Auto-focus</b> For automatic control of the focus level	<b>Battery operation</b> Ready for battery operation. The battery type is specified for each device.
<b>Incident illumination</b> For non-transparent objects	<b>Parallel optical system</b> For stereomicroscopes, enables fatigue-proof working	<b>Battery operation rechargeable</b> Prepared for a rechargeable battery operation
<b>Transmitting illumination</b> For transparent objects	<b>Integrated scale</b> In the eyepiece	<b>Plug-in power supply</b> 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
<b>Fluorescence illumination</b> For stereomicroscopes	<b>SD card</b> For data storage	<b>Integrated power supply unit</b> Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
<b>Fluorescence illumination for compound microscopes</b> With 100 W mercury lamp and filter	<b>USB 2.0 digital camera</b> For direct transmitting of the picture to a PC	<b>Package shipment</b> The time required to manufacture the product internally is shown in days in the pictogram.

## Abbreviations

<b>C-Mount</b> Adapter for the connection of a camera to a trinocular microscope	<b>LWD</b> Long Working Distance	<b>SWF</b> Super Wide Field (Field number at least $\varnothing$ 23 mm for 10 $\times$ eyepiece)
<b>FPS</b> Frames per second	<b>N.A.</b> Numerical Aperture	<b>W.D.</b> Working Distance
<b>H(S)WF</b> High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	<b>SLR camera</b> Single-Lens Reflex camera	<b>WF</b> Wide Field (Field number up to $\varnothing$ 22 mm for 10 $\times$ eyepiece)

Your KERN specialist dealer: