

## Eaton H-Max variable frequency drive

**HMX34AG07221-N**

**UPC:**786685468426

### **Dimensions:**

- **Height:** 25.98 IN
- **Length:** 10.49 IN
- **Width:** 9.06 IN

**Weight:**82.6 LB

**Notes:**All boards are varnished. Corrosion resistant. Battery included in all drives for real-time clock. Keypad kit includes HOA bypass. Keypad kit includes HOA, back reset for Europe application. EMI/RFI filters included. DC link choke included.

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Brake Chopper:** No brake chopper
- **Input:** EMC C2
- **Keypad:** Graphical panel
- **Amperage Rating:** 72A
- **Enclosure:** Open NEMA Type 1 IP21
- **Frame Size:** FR7
- **Horsepower:** 50 hp
- **Phase:** Three-phase
- **Software:** A
- **Voltage Rating:** 380-480 V

### **Supporting documents:**

- [Variable frequency drive - Product overview](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [HMX\\_\(FR7\) AutoCAD 2D Footprint \(mm\)](#)
- [HMX\\_\(FR7\) 3D Inventor](#)

- [HMX\\_\(FR7\) 3D Model Xchange](#)
- [HMX\\_\(FR7\) AutoCAD 2D Footprint](#)
- [HMX\\_\(FR7\)2D PDF](#)
- [HMX\\_\(FR7\) 2D Drawing Xchange](#)
- [H-Max Series Adjustable Frequency Drive Installation Manual](#)
- [Eaton H-Max HVAC Drives](#)
- [Eaton Specification Sheet - HMX34AG07221-N](#)

**Certifications:**

- UL 508C
- EN 61800-5-1
- cUL Certified
- IEC 61800-5-1

**Product compliance:**

- CE Marked