

# FALC-NVR-4K-4BB

4CH HD NVR



## SuperLive Plus Setup



Scan to download our SuperLive Plus App.



\*Requires minimum 3G internet connection. Watching footage on 3G/4G connection will incur data charges.





## SPECIFICATIONS

This series supports 4CH 8MP/6MP/5MP/4MP/3MP/1080P/1280×1024/960P/720P high definition IP video input, which adopts the most advanced SOC technique to ensure high definition recording in each channel and realize outstanding robustness of the system.


This series integrates with 4 PoE network ports and supports 4CH IPC direct connection to NVR, simultaneous 4CH playback and 4K ultra high definition display. The series of product can meet different security requirements of home, financial, commerce, enterprise, transportation and government, etc.

- Support 4CH 8MP/6MP/5MP/4MP/3MP/1080P/1280×1024/960P/720P/960H/DI/CIF IP video input
- Adopt standard H.265 and H.264 high profile compression format to get high-quality video at much lower bit rate
- Intuitive and user-friendly Graphic User Interface ( GUI ), Windows style operation by mouse
- Multi-mode recording: manual / timed / motion / sensor / POS / AI recording
- Playback : 4CH simultaneous playback
- Search : time slice, time, event, tag, smart search
- Support multiple VCA (Video Content Analytics) events, such as object abandoned/missing, region intrusion, tripwire, video exception, etc. Support
- POS information overlay on live view and playback
- Express and flexible backup via USB, network and so on
- Pentaplex : preview, record, playback, backup and remote access
- DHCP, DDNS, PPPoE network protocol
- Remote control via Web or CMS : preview, playback, backup, PTZ and configuration
- 4 PoE network ports; IPC can be directly connected to NVR; PoE power supply supported
- Dual stream technology for local storage with high definition, remote network transmission and remote surveillance with mobile device
- Multi-user online simultaneously
- Authorization management, log view and device status view
- 4K output, true high resolution display
- Support NAT function and QRCode scanning by mobile phones
- Powerful mobile surveillance by smart phones with iOS and Android OS

## DIAGRAMS



## FALC-NVR-4K-4BB



# FALC-NVR-4K-4BB

4CH HD NVR



Model		FALC-NVR-4K-4BB
System	OS	Embedded Linux
Video	Network Input	4 CH IPC input
	Network Input Resolution	8MP/6MP/5MP/4MP/3MP/1080P/1280×1024/960P/720P/960H/D1/CIF
	Output	HDMI × 1 : 3840 × 2160 / 1920 × 1080 / 1280× 1024/ 1024 × 768 VGA : 1920 × 1080/ 1280 × 1024/ 1024 × 768
	Compression	Standard H.265 / H.264
Audio	Network Input	4 CH IPC audio input
	2-way Audio	RCA × 1
	Local Output	RCA × 1
	Compression	G.711(U/A)
Record	Record Stream	Dual stream recording
	Resolution	8MP/6MP/5MP/4MP/3MP/1080P/1280×1024/960P/720P/960H/D1/CIF
	Frame Rate	NTSC:30fps; PAL:25fps
Playback	Simultaneous Playback	Max. 4 CH
	Search	Time slice / time / event / tag / smart search
	Smart Search	Highlighted color to display the camera record in a certain period of time, different colors refers to different record events
	Function	Play, pause, FF, FB, digital zoom, etc.
Decoding Capability	Live View/ Playback	1CH 8MP; 4CH 1080P
Alarm	Mode	Manual, sensor, motion, exception, smart events
	Input	Supports IPC alarm input
	Output	Supports IPC alarm output
	Triggering	Record, snap, preset, e-mail, etc.
Network	Interface	RJ 45 × 1 (10/100/1000Mbps)
	Protocol	TCP / IP, PPPoE/DHCP, DNS, DDNS, UPnP, NTP, SMTP, HTTP, HTTPS, 802.1x, ONVIF, etc.
	Incoming/ Outgoing Bandwidth	40/40 (Mbps)
	Client Connection	Max. 10 users access

# FALC-NVR-4K-4BB

4CH HD NVR



Mobile Device	OS	iOS, Andriod
Storage	HDD Interface	SATA3.0 × 1, max 8T
Backup	Local Backup	U disk, USB mobile HDD
	Network Backup	Yes
Port	USB	USB 2.0 × 2
	Remote Controller	Optional
PoE	PoE Ports	100M RJ45 × 4
	Standards	IEEE802.3af
	Output Power	Unlimited
Others	Power Supply	DC 48V/1.25A
	Consumption	≤ 10W ( without HDD )
	Dimensions (mm)	300 × 249 × 45( W × D × H )
	Working Environment	-10 ~ 50 °C, 10% ~ 90% humidity
	Certificate	CE, FCC
	Environmental Protection	Complies with Directive EU RoHS, REACH and WEEE