



SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture COPPER PASTE

Registration number -

Synonyms None.

Product code BDS001991BU

Issue date 04-July-2022

Version number 1.0

Revision date 04-July-2022

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Lubricants

Uses advised against None known.

1.3. Details of the supplier of the safety data sheet

Company name CRC Industries Europe bv

Address Touwslagerstraat 1
9240 Zele
Belgium

Telephone +32(0)52/45.60.11

Fax +32(0)52/45.00.34

E-mail hse@crcind.com

Website www.crcind.com

1.4. Emergency telephone number Tel.: +32(0)52/45.60.11 (office hours: 9-17h CET)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

This mixture does not meet the criteria for classification according to Regulation (EC) 1272/2008 as amended.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms None.

Signal word None.

Hazard statements The mixture does not meet the criteria for classification.

Precautionary statements

Prevention Not assigned.

Response Not assigned.

Storage Not assigned.

Disposal Not assigned.

Supplemental label information EUH208 - Contains C14-16-18 Alkyl phenol. May produce an allergic reaction.
EUH210 - Safety data sheet available on request.

2.3. Other hazards

This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

Mixture

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
granulated copper; [particle length: from 0,9 mm to 6,0 mm; particle width: from 0,494 to 0,949 mm]	10 - <25	7440-50-8 231-159-6	01-2119480154-42	029-024-00-X	#
Classification: Acute Tox. 4;H302, Acute Tox. 3;H331, Aquatic Acute 1;H400(M=10)					
C14-16-18 Alkyl phenol	<1	- 931-468-2	01-2119498288-19	-	
Classification: -					

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).

ATE: Acute toxicity estimate.

M: M-factor

PBT: persistent, bioaccumulative and toxic substance.

vPvB: very persistent and very bioaccumulative substance.

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Exposure may cause temporary irritation, redness, or discomfort.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards No unusual fire or explosion hazards noted.

5.1. Extinguishing media

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Special fire fighting procedures Move containers from fire area if you can do so without risk.

Specific methods Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel Wear appropriate personal protective equipment.

For emergency responders Keep unnecessary personnel away. For personal protection, see section 8 of the SDS.

6.2. Environmental precautions Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

The product is immiscible with water and will spread on the water surface.

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use.

6.4. Reference to other sections

For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Observe good industrial hygiene practices.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

Storage class (TRGS 510): 11 (Combustible solids that cannot be assigned to any of the above storage classes)

7.3. Specific end use(s)

Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value	Form
granulated copper; [particle length: from 0,9 mm to 6,0 mm; particle width: from 0,494 to 0,949 mm] (CAS 7440-50-8)	STEL	2 mg/m ³	Inhalable dusts and mists.
	TWA	1 mg/m ³	Inhalable dusts and mists.
		0.2 mg/m ³	Fume.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures

Follow standard monitoring procedures.

Derived no effect levels (DNELs)

Not available.

Predicted no effect concentrations (PNECs)

Not available.

8.2. Exposure controls

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information

Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.

Eye/face protection

Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.

Skin protection

- Hand protection

For incidental contact with the product wear chemical-resistant gloves (standard EN 374). The use of disposable gloves is acceptable provided that they are changed immediately after a splash or spill. Nitrile gloves are recommended.

- Other

Wear suitable protective clothing.

Respiratory protection

Not necessary in normal use. In case of insufficient ventilation, wear suitable respiratory equipment.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

Hygiene measures

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

Environmental exposure controls Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state Solid.
Form Paste.
Colour Copper.

Odour Characteristic odor.

Odour threshold Not available.

pH Not applicable.

Melting point/freezing point > 280 °C (> 536 °F)

Initial boiling point and boiling range > 250 °C (> 482 °F)

Flash point > 250.0 °C (> 482.0 °F) Open cup

Evaporation rate Not available.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Vapour pressure Not available.

Vapour density Not available.

Relative density 0.99 g/cm³ at 20°C

Solubility(ies)

Solubility (water) Insoluble in water

Auto-ignition temperature > 200 °C (> 392 °F)

Decomposition temperature Not available.

Viscosity Not available.

Explosive properties Not explosive.

Oxidising properties Not oxidising.

9.2. Other information

VOC 0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability Material is stable under normal conditions.

10.3. Possibility of hazardous reactions No dangerous reaction known under conditions of normal use.

10.4. Conditions to avoid Contact with incompatible materials.

10.5. Incompatible materials Strong oxidising agents.

10.6. Hazardous decomposition products Not available.

SECTION 11: Toxicological information

General information Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of exposure

Inhalation May cause allergy or asthma symptoms or breathing difficulties if inhaled.

Eye contact Based on available data, the classification criteria are not met.

Skin contact May cause an allergic skin reaction.

Ingestion May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.

Symptoms Exposure may cause temporary irritation, redness, or discomfort.

11.1. Information on toxicological effects

Acute toxicity	Based on available data, the classification criteria are not met.
Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory sensitisation	Based on available data, the classification criteria are not met.
Skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	Not available.
Other information	May cause allergic respiratory and skin reactions.

SECTION 12: Ecological information

12.1. Toxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Product	Species	Test Results
COPPER PASTE		
Aquatic		
<i>Acute</i>		
Algae	EC50	Algae > 100 mg/l, 72 hours
Crustacea	EC50	Daphnia > 100 mg/l, 48 hours
Fish	LC50	Fish > 100 mg/l, 96 hours
<i>Chronic</i>		
Algae	NOEC	Algae > 100 mg/l

12.2. Persistence and degradability No data is available on the degradability of any ingredients in the mixture.

12.3. Bioaccumulative potential No data available.

Partition coefficient n-octanol/water (log Kow) Not available.

Bioconcentration factor (BCF) Not available.

12.4. Mobility in soil No data available.

12.5. Results of PBT and vPvB assessment This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.

12.6. Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. - 14.6.: Not regulated as dangerous goods.

RID

14.1. - 14.6.: Not regulated as dangerous goods.

ADN

14.1. - 14.6.: Not regulated as dangerous goods.

IATA

14.1. - 14.6.: Not regulated as dangerous goods.

IMDG

14.1. - 14.6.: Not regulated as dangerous goods.

14.7. Transport in bulk Not established.
according to Annex II of
MARPOL 73/78 and the IBC
Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

granulated copper; [particle length: from 0,9 mm to 6,0 mm; particle width: from 0,494 to 0,949 mm] (CAS 7440-50-8)

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

granulated copper; [particle length: from 0,9 mm to 6,0 mm; particle width: from 0,494 to 0,949 mm] (CAS 7440-50-8)

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.

ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.

AGW: Occupational threshold limit value (Arbeitsplatzgrenzwert – Germany).

ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).

CAS: Chemical Abstract Service.

Ceiling: Short Term Exposure Limit Ceiling value.
CEN: European Committee for Standardization.
CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.
GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.
IMDG: International Maritime Dangerous Goods.
MAC: Maximum Allowed Concentration.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative and toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VLE: Exposure Limit Value.
VME: Exposure Average Value.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

Not available.

References

Information on evaluation method leading to the classification of mixture

The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any H-statements not written out in full under Sections 2 to 15

H302 Harmful if swallowed.
H331 Toxic if inhaled.
H400 Very toxic to aquatic life.

Revision information

None.

Training information

Follow training instructions when handling this material.

Disclaimer

CRC Industries Europe bvba cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.