I. A Safety information

Read the following safety information carefully before attempting to operate or service the meter.

Use the meter only as specified in this manual; otherwise, the protection provided by the meter may be impaired.

• Environment conditions

- 1 Altitude up to 2000 meters
- 2 Relatively humidity 90% max.
- 3 Operation Ambient 0~40℃

Maintenance & Clearing

- 1 Repairs or servicing not covered in this manual should only be performed by qualified personnel.
- 2 Periodically wipe the case with a dry cloth. Do not use abrasives or solvents on this instruments.

• Safety symbols

Meter is protected throughout by double insulation or reinforced insulation.

When servicing, use only specified replacement parts.

(€ Comply with EMC

II. General Description

Thank you for using our Sound Level Meter. To ensure that you can get the most from it, we recommend that you read and follow the manual carefully before use. This unit conforms to the IEC61672-1 type 2, ANSI S1.4 type 2 for Sound Level Meters.

This Sound Level Meter has been designed to meet the measurement requirements of safety Engineers, Health, Industrial safety offices and sound quality control in various environments.

- Ranges from 30dB to 130dB at frequencies between 31.5Hz and 8 KHz.
- Display with 0.1dB steps on a 4-digits LCD.
- With two equivalent weighted sound pressure levels, A and C.

III. Specifications

Standard appli	ed : IEC6	1672-1 type	2, ANSI S1.	4	
type 2					
Frequency rang	e : 31.5Hz	z~8KHz			
Measuring leve	range : 30~13	0dB			
Frequency weight	hting : A/C				
Microphone	: 1/2 inch electre	t condenser r	microphone		
Calibration	: Electrical calib	oration with	the interna	d	
	oscillator (1kHz	sine wave)			
Display	: LCD				
Digital display	: 4 digits				
	Resolution: 0.1	dB			
	Display Up data	a: 0.5 sec.			
Time weighting : FAST(125mS), SLOW(1 sec.)					

1

Level ranges	: Lo: 30-100dB					
Hi	: 60-130dB					
Accuracy	: <u>+</u> 2dB (under reference conditions)					
Alarm function	: "OVER" is show when input is out of range					
Maximum hold	: Hold readings the Maximum Value,					
	with decay < 1dB/3minutes.					
Auto power off	: Meter automatically shuts down after					
	approx. 15 minutes of inactivity.					
Power supply	: One 9V battery, 006P or IEC 6F22 or					
	NEDA 1604.					
Power life	: About 50hrs(alkaline Battery)					
Operation temperature : 0 to 40° C(32 to 104°F)						
Operation humidity	: 10 to 90%RH					
Storage temperature	: -10 to 60℃(14 to 140 °F)					
Storage humidity	: 10 to 75%RH					
Dimensions	: 210(L)X55(W)X32(H)mm					
	230g(including battery)					
Weight	: 9V battery, carrying case, Instruction					
	manual					

V. Name and Functions



(\mathbf{I}) Windscreen

If you operate at wind speed over 10m/sec, please put protective accessories in front of the microphone.

(2) Display



SYMBOL	FUNCTION
LCD	4digits
MAX	Maximum Value hold
OVER	Over range
F	Fast response
S	Slow response
A	A-Weighting
C	C-Weighting
Lo	Low Range (30~100dB)
Hi	High Range (60~130dB)
BAT	Low-Battery

③ Power ON/OFF button

Turn the meter power ON/OFF

hold and allow a further measurement.

(4) MAX button





continuously. Press once again the button, will release the

(5) A-weighting / C-weighting select button (A/C

level of sounds. The maximum measured level is up dated

A: A – Weighting. For general sound level measurements. C: C – Weighting. For checking the low- frequency content of noise.

(If the C-Weighted level is much higher than the A-Weighted level, then there is a large amount of low-frequency noise)

(F/S 6 Time weighting select button

F (fast response): for normal measurements (fast varying noise)

S (slow response): for checking average level of fluctuating noise

⑦ Level range select button (Lo/Hi) Lo: 30~100dB; Hi: 60~130dB

When "OVER" is indicated, the ranges switch to another range for measurement.

8 Hold button



The hold function freezes the reading in the display.

9 Microphone

1/2 inch Electret Condenser microphone

Battery Cover

V. Measurement Preparation

(1) Battery loading

Remove the battery cover on the back and put in one 9V Battery.

(2) Battery Replacement

When the battery voltage drops below the operating voltage, mark "BAT" appears. If it appears, battery should be replaced with new one.

VI. Operating Precautions

(1) Wind blowing across the microphone would bring additional extraneous noise.

Once using the instrument in the presence of wind, it is a must to mount the windscreen to not pick up undesirable signals.

- (2) To achieve more accurate measurement, use an extension cable to separate the Microphone from the main body so that the effect of unexpected sound reflection can be eliminated.
- (3) Calibrate the instrument before operation if the instrument was not in use for a long time or operated at

bad environment.

- (4) Do not store or operate the instrument at high temperature and high humidity environment.
- (5) Keep microphone dry and avoid severe vibration.
- (6) Please take the battery and keep the instrument in low humidity environment. When not in use.

VII. Measurement

- (1) Open battery cover and install a 9-volt battery in the battery compartment.
- (2) Turn on power and select the desired response Time and weighting. If the sound source consists of short bursts or only catching sound peak, set response to FAST. To measure average sound, use the slow setting.
 Select A- weighting for general noise sound level and C-weighting for measuring sound level of acoustic
- (3) Select desired Level

material.

- (4) Hold the instrument comfortably in hand or fix on tripod and point the microphone at the suspected noise source, the sound pressure level will be displayed.
- (5) When MAX (maximum hold) mode is chosen. The instrument captures and holds the maximum noise level for a long period using any of the time weightings and

ranges.

- (6) When HOLD (data hold)mode is chosen. The hold function freezes the reading in the display. Press the HOLD button momentarily to activate or to exit the HOLD function
- (7) Turn OFF the instrument and remove and remove battery when not in use.

VIII. Calibration Procedures

Using a standard Acoustic Calibrator (94dB, 1kHz Sine wave)



(1)Make the following buttons and function switch settings.

Display: dB, A, Hi or Lo, F Function: A-Weighting

Response Time: FAST Level range: 30 to 100dB(Lo) or 60 to 130dB(Hi) Measurement mode: MAX Hold and Data Hold Mode function disable.

- (2) Insert the microphone housing carefully into the insertion hole of the calibrator.
- (3) Open battery cover and remove the battery to adjust the CAL94dB potentiometer of the unit. The level display will indicate the desired level.

Our products are all well calibrated before shipment. Recommended Recalibration cycle:1 year.



Sound Level Meter TEN01073



Contents

Title		Page
I.	Safety Information	1
II.	General Description	1
III.	Specifications	2
IV.	Name And Functions	4
۷.	Measurement Preparation	7
VI.	Operating Precautions	7
VII.	Measurement	8
VIII	. Calibration Procedures	10



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

> Made in China PR2 9PP PO Box 13362 Dublin 2